

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1059792

Luminaire Tested: S123RDRP-H775D935-X4F0-XX-UDD-SVL-W

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2024
Report Number: P1059792
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2406-143-65)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDRP-H775D935-X4F0-XX-UDD-SVL-W
Description: DEFINE 3 WHITE REGRESSED DIRECT RECESSED HOUSING WITH SILVER STRAIGHT BLADE LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 861.7 lumens
Efficiency: N/A
Efficacy: 36.7 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 1.08 / 0.98
Luminous Opening: Rectangular (W 0.23' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 23.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1059792

CATALOG NUMBER: S123RDRP-H775D935-X4F0-XX-UDD-SVL-W

Luminous Intensity Polar Plot





TEST NUMBER: P1059792

CATALOG NUMBER: S123RDRP-H775D935-X4F0-XX-UDD-SVL-W

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	89
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	66	64
5	85	74	67	61	83	73	66	61	71	65	60	69	64	60	68	63	59	58
6	79	68	61	55	78	67	60	55	66	59	55	64	59	54	63	58	54	52
7	74	63	56	51	73	62	55	50	61	55	50	60	54	50	58	53	49	48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44
9	66	54	47	43	65	54	47	43	53	47	42	52	46	42	51	46	42	40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7537	7537	7537
5°	7293	7406	7557
10°	6807	7064	7425
15°	6204	6601	7231
20°	5520	6038	6925
25°	4783	5403	6529
30°	4011	4713	6141
35°	3178	4012	5773
40°	2249	3300	5414
45°	1324	2609	4872
50°	990	1980	4267
55°	833	1339	3427
60°	674	1141	2435
65°	531	975	1284
70°	467	848	793
75°	436	794	758
80°	433	866	757
85°	539	1293	970

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 4872 cd/sqm



TEST NUMBER: P1059792

CATALOG NUMBER: S123RDRP-H775D935-X4F0-XX-UDD-SVL-W

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.1	6.9
10°-20°	153.5	17.8
20°-30°	195.5	22.7
30°-40°	183.9	21.3
40°-50°	132.5	15.4
50°-60°	76.5	8.9
60°-70°	35.0	4.1
70°-80°	17.5	2.0
80°-90°	8.3	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	408.1	47.4
0°-40°	592.0	68.7
0°-60°	801.0	93.0
0°-90°	861.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	861.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	642	642	642	642	642	
5°	619	629	628	635	641	58
15°	510	529	543	573	595	142
25°	369	388	417	463	504	169
35°	222	241	280	344	403	137
45°	80	100	157	236	293	67
55°	41	42	65	124	167	36
65°	19	27	35	39	46	20
75°	10	18	18	17	17	10
85°	4	9	10	9	7	4
90°	0	0	0	0	0	



TEST NUMBER: P1059792

CATALOG NUMBER: S123RDRP-H775D935-X4F0-XX-UDD-SVL-W

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	641.9	641.9	641.9	641.9	641.9
2.5°	634.7	642.7	637.1	637.9	639.5
5°	618.7	629.1	628.3	634.7	641.1
7.5°	596.4	608.4	614.8	624.3	633.1
10°	570.9	584.5	592.4	610.0	622.7
12.5°	541.4	558.9	569.3	592.4	610.8
15°	510.3	528.6	543.0	573.3	594.8
17.5°	475.2	495.2	513.5	549.4	575.7
20°	441.7	460.9	483.2	522.3	554.2
22.5°	405.1	425.8	451.3	492.8	528.6
25°	369.2	388.3	417.0	463.3	503.9
27.5°	333.3	352.4	382.7	433.8	478.4
30°	295.8	315.7	347.6	404.3	452.9
32.5°	259.1	278.3	314.2	375.6	426.6
35°	221.7	240.8	279.9	344.5	402.7
37.5°	185.0	204.9	246.4	318.9	378.7
40°	146.7	168.2	215.3	292.6	353.2
42.5°	110.8	134.0	184.2	265.5	325.3
45°	79.7	99.7	157.1	236.0	293.4
47.5°	62.2	72.6	132.4	205.7	263.9
50°	54.2	55.8	108.4	177.8	233.6
52.5°	47.0	48.6	85.3	151.5	201.7
55°	40.7	42.3	65.4	124.4	167.4
57.5°	34.3	36.7	54.2	98.9	134.8
60°	28.7	31.9	48.6	75.7	103.7
62.5°	23.1	28.7	41.5	55.8	74.2
65°	19.1	27.1	35.1	39.1	46.2
67.5°	15.9	24.7	29.5	27.9	27.1
70°	13.6	22.3	24.7	22.3	23.1
72.5°	11.2	20.7	20.7	19.1	19.1
75°	9.6	18.3	17.5	16.7	16.7
77.5°	8.0	15.9	15.1	14.4	13.6
80°	6.4	12.8	12.8	12.0	11.2
82.5°	5.6	10.4	10.4	10.4	8.8
85°	4.0	8.8	9.6	8.8	7.2
87.5°	3.2	8.0	8.0	7.2	4.8
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1059792
 CATALOG NUMBER: S123RDRP-H775D935-X4F0-XX-UDD-SVL-W

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.99	8.31	7.36	8.62	8.94	14.35	15.67	14.72	15.98	16.30
	3H	8.38	9.55	8.76	9.88	10.24	14.58	15.75	14.96	16.08	16.45
	4H	8.93	10.02	9.33	10.37	10.76	14.70	15.79	15.10	16.14	16.52
	6H	9.37	10.37	9.78	10.74	11.13	14.81	15.81	15.23	16.18	16.58
	8H	9.54	10.49	9.97	10.88	11.29	14.86	15.81	15.29	16.20	16.61
	12H	9.70	10.61	10.13	10.99	11.42	14.92	15.83	15.36	16.22	16.65
4H	2H	8.09	9.18	8.49	9.53	9.92	14.31	15.40	14.71	15.75	16.14
	3H	9.75	10.64	10.16	11.05	11.45	14.67	15.56	15.08	15.97	16.37
	4H	10.56	11.36	10.99	11.78	12.22	14.87	15.67	15.30	16.08	16.53
	6H	11.20	11.89	11.66	12.33	12.80	15.10	15.79	15.56	16.23	16.70
	8H	11.43	12.08	11.90	12.53	13.00	15.20	15.85	15.67	16.29	16.76
	12H	11.65	12.22	12.13	12.70	13.18	15.33	15.90	15.82	16.38	16.86
8H	4H	11.00	11.65	11.47	12.09	12.56	14.90	15.55	15.37	16.00	16.47
	6H	11.91	12.44	12.42	12.94	13.42	15.23	15.76	15.74	16.26	16.74
	8H	12.34	12.81	12.86	13.33	13.82	15.42	15.90	15.95	16.42	16.91
	12H	12.76	13.18	13.27	13.67	14.24	15.68	16.10	16.19	16.59	17.16
12H	4H	11.06	11.63	11.54	12.11	12.59	14.89	15.46	15.38	15.95	16.42
	6H	12.05	12.53	12.57	13.04	13.53	15.25	15.73	15.77	16.24	16.73
	8H	12.59	13.01	13.11	13.51	14.08	15.51	15.93	16.02	16.43	17.00