

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1059139

Luminaire Tested: S123RDRP-S1165D935-X4F0-XX-UDD-BVL-B

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2024
Report Number: P1059139
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2406-143-30)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDRP-S1165D935-X4F0-XX-UDD-BVL-B
Description: DEFINE 3 BLACK REGRESSED DIRECT RECESSED HOUSING WITH BLACK STRAIGHT BLADE
LOUVER WITH DIFFUSER
CORE LIGHT ENGINE
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 878.7 lumens
Efficiency: N/A
Efficacy: 21.0 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 0.81 / 0.94
Luminous Opening: Rectangular (W 0.23' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 41.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1059139

CATALOG NUMBER: S123RDRP-S1165D935-X4F0-XX-UDD-BVL-B

Luminous Intensity Polar Plot





TEST NUMBER: P1059139

CATALOG NUMBER: S123RDRP-S1165D935-X4F0-XX-UDD-BVL-B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	87	85	84
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	83	80	78	76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63
6	83	73	66	61	81	72	66	61	70	65	60	69	64	60	67	63	60	58
7	78	68	61	56	77	67	60	56	66	60	56	64	59	55	63	58	55	53
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49
9	70	59	52	48	68	58	52	48	57	52	47	56	51	47	55	51	47	46
10	66	55	49	44	65	55	48	44	54	48	44	53	48	44	52	47	44	42

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9043	9043	9043
5°	9018	8858	8872
10°	8916	8443	8236
15°	8653	7854	7402
20°	8275	7113	6478
25°	7792	6283	5479
30°	7230	5398	4473
35°	6631	4462	3324
40°	5949	3498	2129
45°	5189	2554	885
50°	4304	1518	340
55°	3173	635	254
60°	1921	233	146
65°	517	139	69
70°	0	41	41
75°	0	0	54
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5189 cd/sqm



TEST NUMBER: P1059139

CATALOG NUMBER: S123RDRP-S1165D935-X4F0-XX-UDD-BVL-B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.9	8.1
10°-20°	183.0	20.8
20°-30°	228.0	25.9
30°-40°	203.9	23.2
40°-50°	128.7	14.6
50°-60°	53.8	6.1
60°-70°	10.1	1.2
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	481.9	54.8
0°-40°	685.8	78.0
0°-60°	868.3	98.8
0°-90°	878.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	878.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	770	770	770	770	770	
5°	765	764	752	754	753	72
15°	712	694	646	619	609	200
25°	601	553	485	443	423	275
35°	463	396	311	256	232	288
45°	312	243	154	82	53	241
55°	155	107	31	12	12	139
65°	19	14	5	2	2	26
75°	0	0	0	0	1	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P1059139

CATALOG NUMBER: S123RDRP-S1165D935-X4F0-XX-UDD-BVL-B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	770.1	770.1	770.1	770.1	770.1
2.5°	768.9	770.1	762.7	770.1	771.3
5°	765.1	763.9	751.5	754.0	752.7
7.5°	757.7	754.0	731.7	726.7	724.2
10°	747.8	737.9	708.1	695.7	690.7
12.5°	731.7	718.0	679.6	659.7	652.3
15°	711.8	694.5	646.1	618.8	608.9
17.5°	688.2	663.4	608.9	579.1	564.2
20°	662.2	627.5	569.2	533.2	518.4
22.5°	631.2	592.8	527.0	488.6	472.5
25°	601.4	553.1	484.9	442.7	422.9
27.5°	564.2	513.4	440.2	396.8	375.7
30°	533.2	475.0	398.1	349.7	329.9
32.5°	496.0	435.3	354.7	301.3	282.7
35°	462.6	395.6	311.3	255.5	231.9
37.5°	426.6	357.1	267.9	209.6	187.3
40°	388.1	318.7	228.2	163.7	138.9
42.5°	353.4	280.3	188.5	121.5	96.7
45°	312.5	243.1	153.8	81.8	53.3
47.5°	275.3	208.3	116.6	45.9	28.5
50°	235.6	172.4	83.1	23.6	18.6
52.5°	194.7	137.6	54.6	16.1	14.9
55°	155.0	106.6	31.0	12.4	12.4
57.5°	116.6	76.9	16.1	9.9	8.7
60°	81.8	50.8	9.9	7.4	6.2
62.5°	47.1	29.8	7.4	5.0	5.0
65°	18.6	13.6	5.0	2.5	2.5
67.5°	1.2	3.7	2.5	1.2	1.2
70°	0.0	0.0	1.2	1.2	1.2
72.5°	0.0	0.0	1.2	1.2	1.2
75°	0.0	0.0	0.0	0.0	1.2
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1059139
 CATALOG NUMBER: S123RDRP-S1165D935-X4F0-XX-UDD-BVL-B

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.84	14.02	13.21	14.33	14.65	0.00	0.00	0.00	0.00	0.00
	3H	12.68	13.71	13.06	14.05	14.41	0.00	0.00	0.00	0.00	0.00
	4H	12.60	13.55	13.00	13.90	14.29	0.00	0.00	0.00	0.00	0.00
	6H	12.50	13.38	12.92	13.75	14.14	0.00	0.00	0.00	0.00	0.00
	8H	12.45	13.28	12.89	13.67	14.08	0.00	0.00	0.00	0.00	0.00
	12H	12.40	13.19	12.84	13.57	14.00	0.00	0.00	0.00	0.00	0.00
4H	2H	12.60	13.56	13.01	13.91	14.29	0.00	0.00	0.00	0.00	0.00
	3H	12.44	13.20	12.85	13.61	14.02	0.00	0.00	0.00	0.00	0.00
	4H	12.33	13.01	12.77	13.44	13.88	0.00	0.00	0.00	0.00	0.00
	6H	12.24	12.82	12.70	13.27	13.74	0.00	0.00	0.00	0.00	0.00
	8H	12.17	12.71	12.64	13.16	13.64	0.00	0.00	0.00	0.00	0.00
	12H	12.11	12.59	12.60	13.08	13.55	0.00	0.00	0.00	0.00	0.00
8H	4H	12.17	12.71	12.64	13.16	13.64	0.00	0.00	0.00	0.00	0.00
	6H	12.05	12.49	12.56	12.99	13.48	0.00	0.00	0.00	0.00	0.00
	8H	11.98	12.38	12.51	12.90	13.39	0.00	0.00	0.00	0.00	0.00
	12H	11.93	12.28	12.45	12.77	13.35	0.00	0.00	0.00	0.00	0.00
12H	4H	12.11	12.59	12.60	13.08	13.55	0.00	0.00	0.00	0.00	0.00
	6H	11.98	12.38	12.51	12.90	13.39	0.00	0.00	0.00	0.00	0.00
	8H	11.93	12.28	12.45	12.77	13.35	0.00	0.00	0.00	0.00	0.00