

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1059474

Luminaire Tested: S123RDRP-H1000D940-X4F0-XX-UDD-BVL-W

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2024
Report Number: P1059474
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2406-143-66)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDRP-H1000D940-X4F0-XX-UDD-BVL-W
Description: DEFINE 3 WHITE REGRESSED DIRECT RECESSED HOUSING WITH BLACK STRAIGHT BLADE
LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 973.2 lumens
Efficiency: N/A
Efficacy: 31.2 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 1.06 / 0.94
Luminous Opening: Rectangular (W 0.23' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1059474

CATALOG NUMBER: S123RDRP-H1000D940-X4F0-XX-UDD-BVL-W

Luminous Intensity Polar Plot



TEST NUMBER: P1059474

CATALOG NUMBER: S123RDRP-H1000D940-X4F0-XX-UDD-BVL-W

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90																												
2	105	99	94	90	102	97	92	88	94	90	86	91	87	85	88	85	83	81																												
3	98	90	84	79	96	89	83	79	86	81	77	83	79	76	81	78	75	73																												
4	92	83	76	71	90	81	75	70	79	74	70	77	72	69	75	71	68	66																												
5	86	76	69	64	84	75	69	64	73	67	63	71	66	62	70	65	62	60																												
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	57	55																												
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50																												
8	72	61	54	49	70	60	53	49	59	53	49	58	52	48	57	52	48	47																												
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43																												
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	42	40																												

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9518	9518	9518
5°	9191	9341	9543
10°	8485	8878	9386
15°	7615	8211	9104
20°	6642	7401	8666
25°	5604	6487	8129
30°	4506	5546	7597
35°	3298	4566	7100
40°	2057	3559	6613
45°	779	2654	5890
50°	369	1829	5020
55°	283	1003	3882
60°	200	850	2553
65°	147	739	1064
70°	148	694	694
75°	195	726	726
80°	291	866	791
85°	579	1442	1145

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 5890 cd/sqm

TEST NUMBER: P1059474

CATALOG NUMBER: S123RDRP-H1000D940-X4F0-XX-UDD-BVL-W

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.4	7.6
10°-20°	190.8	19.6
20°-30°	236.2	24.3
30°-40°	211.7	21.8
40°-50°	138.8	14.3
50°-60°	69.5	7.1
60°-70°	27.1	2.8
70°-80°	15.3	1.6
80°-90°	9.4	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	501.4	51.5
0°-40°	713.2	73.3
0°-60°	921.5	94.7
0°-90°	973.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	973.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	811	811	811	811	811	
5°	780	792	792	801	810	72
15°	626	652	675	720	749	174
25°	432	459	501	572	627	197
35°	230	261	318	414	495	143
45°	47	76	160	274	355	45
55°	14	17	49	134	190	13
65°	5	16	27	35	38	6
75°	4	16	16	16	16	5
85°	4	11	11	11	8	4
90°	0	0	0	0	0	



TEST NUMBER: P1059474

CATALOG NUMBER: S123RDRP-H1000D940-X4F0-XX-UDD-BVL-W

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	810.6	810.6	810.6	810.6	810.6
2.5°	800.0	811.7	804.2	805.3	806.4
5°	779.7	792.5	792.5	801.0	809.6
7.5°	748.9	763.8	774.4	789.3	801.0
10°	711.6	729.7	744.6	771.2	787.2
12.5°	671.1	693.5	712.6	747.8	770.2
15°	626.4	651.9	675.4	720.1	748.9
17.5°	578.4	604.0	634.9	687.1	722.2
20°	531.5	557.1	592.3	650.9	693.5
22.5°	482.5	509.2	546.5	611.4	661.5
25°	432.5	459.1	500.7	572.0	627.4
27.5°	382.4	409.0	455.9	533.7	594.4
30°	332.3	359.0	409.0	492.1	560.3
32.5°	282.3	311.0	363.2	453.8	526.2
35°	230.1	261.0	318.5	414.4	495.3
37.5°	182.2	210.9	275.9	380.3	464.4
40°	134.2	165.1	232.2	347.3	431.4
42.5°	87.3	120.4	192.8	311.0	394.1
45°	46.9	75.6	159.8	273.8	354.7
47.5°	25.6	41.5	128.9	234.3	314.2
50°	20.2	23.4	100.1	200.3	274.8
52.5°	17.0	19.2	71.4	168.3	231.2
55°	13.8	17.0	49.0	134.2	189.6
57.5°	11.7	14.9	38.3	104.4	148.1
60°	8.5	12.8	36.2	76.7	108.7
62.5°	6.4	13.8	32.0	53.3	71.4
65°	5.3	16.0	26.6	35.2	38.3
67.5°	4.3	17.0	23.4	22.4	22.4
70°	4.3	16.0	20.2	19.2	20.2
72.5°	4.3	17.0	18.1	17.0	18.1
75°	4.3	16.0	16.0	16.0	16.0
77.5°	4.3	14.9	14.9	13.8	13.8
80°	4.3	12.8	12.8	12.8	11.7
82.5°	4.3	11.7	11.7	11.7	9.6
85°	4.3	10.7	10.7	10.7	8.5
87.5°	3.2	9.6	10.7	9.6	6.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1059474

CATALOG NUMBER: S123RDRP-H1000D940-X4F0-XX-UDD-BVL-W

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.18	1.44	0.54	1.75	2.06	14.43	15.69	14.80	16.00	16.32
	3H	2.52	3.63	2.90	3.96	4.33	14.51	15.63	14.90	15.96	16.32
	4H	3.63	4.66	4.03	5.01	5.40	14.59	15.63	15.00	15.98	16.36
	6H	4.62	5.57	5.04	5.94	6.34	14.70	15.64	15.11	16.02	16.41
	8H	5.11	6.01	5.54	6.40	6.80	14.75	15.65	15.18	16.04	16.45
	12H	5.67	6.53	6.11	6.91	7.34	14.83	15.69	15.27	16.08	16.51
4H	2H	3.43	4.46	3.83	4.81	5.20	14.29	15.32	14.69	15.67	16.06
	3H	5.75	6.59	6.16	7.00	7.40	14.46	15.31	14.88	15.71	16.12
	4H	7.13	7.88	7.56	8.30	8.75	14.62	15.37	15.05	15.79	16.24
	6H	8.22	8.87	8.68	9.31	9.78	14.84	15.49	15.30	15.94	16.41
	8H	8.67	9.28	9.15	9.73	10.20	14.96	15.57	15.43	16.02	16.49
	12H	9.17	9.71	9.66	10.20	10.67	15.14	15.68	15.63	16.16	16.64
8H	4H	8.10	8.71	8.57	9.16	9.63	14.61	15.22	15.08	15.67	16.14
	6H	9.62	10.12	10.13	10.62	11.10	14.95	15.45	15.45	15.95	16.43
	8H	10.40	10.85	10.92	11.36	11.86	15.18	15.63	15.70	16.15	16.64
	12H	11.21	11.60	11.72	12.10	12.67	15.52	15.91	16.03	16.41	16.98
12H	4H	8.28	8.81	8.76	9.30	9.77	14.60	15.14	15.08	15.62	16.09
	6H	9.94	10.39	10.46	10.90	11.40	14.97	15.42	15.49	15.93	16.43
	8H	10.89	11.29	11.41	11.79	12.36	15.28	15.68	15.79	16.17	16.74