

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1059477

Luminaire Tested: S123RDRP-H1000D940-X4F0-XX-UDD-SVL-W

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2024
Report Number: P1059477
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2406-143-65)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDRP-H1000D940-X4F0-XX-UDD-SVL-W
Description: DEFINE 3 WHITE REGRESSED DIRECT RECESSED HOUSING WITH SILVER STRAIGHT BLADE LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1150.8 lumens
Efficiency: N/A
Efficacy: 36.9 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 1.08 / 0.98
Luminous Opening: Rectangular (W 0.23' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1059477

CATALOG NUMBER: S123RDRP-H1000D940-X4F0-XX-UDD-SVL-W

Luminous Intensity Polar Plot





TEST NUMBER: P1059477

CATALOG NUMBER: S123RDRP-H1000D940-X4F0-XX-UDD-SVL-W

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	89
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	66	64
5	85	74	67	61	83	73	66	61	71	65	60	69	64	60	68	63	59	58
6	79	68	61	55	78	67	60	55	66	59	55	64	59	54	63	58	54	52
7	74	63	56	51	73	62	55	50	61	55	50	60	54	50	58	53	49	48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44
9	66	54	47	43	65	54	47	43	53	47	42	52	46	42	51	46	42	40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10067	10067	10067
5°	9741	9892	10092
10°	9092	9435	9917
15°	8286	8816	9658
20°	7373	8065	9250
25°	6389	7217	8721
30°	5357	6295	8202
35°	4245	5358	7709
40°	3004	4407	7232
45°	1769	3484	6508
50°	1323	2645	5700
55°	1112	1787	4578
60°	899	1527	3250
65°	711	1303	1717
70°	621	1133	1061
75°	581	1062	1016
80°	575	1150	1008
85°	714	1725	1293

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 6508 cd/sqm



TEST NUMBER: P1059477

CATALOG NUMBER: S123RDRP-H1000D940-X4F0-XX-UDD-SVL-W

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.9	6.9
10°-20°	205.1	17.8
20°-30°	261.1	22.7
30°-40°	245.6	21.3
40°-50°	176.9	15.4
50°-60°	102.2	8.9
60°-70°	46.7	4.1
70°-80°	23.3	2.0
80°-90°	11.0	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	545.1	47.4
0°-40°	790.7	68.7
0°-60°	1069.8	93.0
0°-90°	1150.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1150.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	857	857	857	857	857	
5°	826	840	839	848	856	77
15°	682	706	725	766	794	190
25°	493	519	557	619	673	226
35°	296	322	374	460	538	184
45°	106	133	210	315	392	90
55°	54	56	87	166	224	49
65°	26	36	47	52	62	26
75°	13	24	23	22	22	14
85°	5	12	13	12	10	6
90°	0	0	0	0	0	

TEST NUMBER: P1059477

CATALOG NUMBER: S123RDRP-H1000D940-X4F0-XX-UDD-SVL-W

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	857.3	857.3	857.3	857.3	857.3
2.5°	847.7	858.4	850.9	852.0	854.1
5°	826.4	840.3	839.2	847.7	856.2
7.5°	796.6	812.6	821.1	833.9	845.6
10°	762.5	780.6	791.3	814.7	831.7
12.5°	723.1	746.5	760.4	791.3	815.8
15°	681.6	706.1	725.2	765.7	794.5
17.5°	634.7	661.3	685.8	733.8	768.9
20°	590.0	615.6	645.4	697.6	740.2
22.5°	541.0	568.7	602.8	658.2	706.1
25°	493.1	518.6	557.0	618.7	673.1
27.5°	445.2	470.7	511.2	579.3	639.0
30°	395.1	421.7	464.3	539.9	604.9
32.5°	346.1	371.7	419.6	501.6	569.8
35°	296.1	321.6	373.8	460.1	537.8
37.5°	247.1	273.7	329.1	426.0	505.9
40°	196.0	224.7	287.5	390.8	471.8
42.5°	148.0	178.9	246.0	354.6	434.5
45°	106.5	133.1	209.8	315.2	391.9
47.5°	83.1	96.9	176.8	274.8	352.5
50°	72.4	74.5	144.8	237.5	312.0
52.5°	62.8	65.0	114.0	202.3	269.4
55°	54.3	56.4	87.3	166.1	223.6
57.5°	45.8	49.0	72.4	132.1	180.0
60°	38.3	42.6	65.0	101.2	138.4
62.5°	30.9	38.3	55.4	74.5	99.0
65°	25.6	36.2	46.9	52.2	61.8
67.5°	21.3	33.0	39.4	37.3	36.2
70°	18.1	29.8	33.0	29.8	30.9
72.5°	14.9	27.7	27.7	25.6	25.6
75°	12.8	24.5	23.4	22.4	22.4
77.5°	10.6	21.3	20.2	19.2	18.1
80°	8.5	17.0	17.0	16.0	14.9
82.5°	7.5	13.8	13.8	13.8	11.7
85°	5.3	11.7	12.8	11.7	9.6
87.5°	4.3	10.6	10.6	9.6	6.4
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1059477

CATALOG NUMBER: S123RDRP-H1000D940-X4F0-XX-UDD-SVL-W

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.00	9.31	8.36	9.63	9.94	15.36	16.68	15.72	16.99	17.31
	3H	9.38	10.55	9.76	10.88	11.25	15.59	16.76	15.97	17.09	17.45
	4H	9.94	11.03	10.34	11.38	11.76	15.70	16.79	16.11	17.15	17.53
	6H	10.37	11.37	10.78	11.74	12.13	15.82	16.82	16.23	17.19	17.58
	8H	10.55	11.49	10.98	11.89	12.29	15.87	16.82	16.30	17.21	17.62
	12H	10.70	11.61	11.13	11.99	12.42	15.93	16.84	16.36	17.22	17.65
4H	2H	9.10	10.19	9.50	10.54	10.92	15.32	16.41	15.72	16.76	17.14
	3H	10.76	11.65	11.17	12.05	12.46	15.68	16.57	16.09	16.97	17.38
	4H	11.57	12.37	12.00	12.79	13.23	15.87	16.67	16.31	17.09	17.54
	6H	12.20	12.89	12.66	13.34	13.80	16.10	16.79	16.56	17.24	17.71
	8H	12.44	13.08	12.90	13.53	14.00	16.21	16.85	16.67	17.30	17.77
	12H	12.65	13.22	13.13	13.70	14.18	16.33	16.91	16.82	17.39	17.86
8H	4H	12.01	12.65	12.48	13.10	13.57	15.91	16.56	16.38	17.00	17.48
	6H	12.92	13.45	13.42	13.94	14.42	16.24	16.77	16.74	17.27	17.75
	8H	13.33	13.81	13.86	14.33	14.82	16.43	16.91	16.95	17.42	17.91
	12H	13.75	14.17	14.27	14.67	15.24	16.68	17.10	17.19	17.59	18.17
12H	4H	12.07	12.64	12.55	13.12	13.59	15.90	16.47	16.39	16.96	17.43
	6H	13.05	13.53	13.57	14.04	14.53	16.26	16.73	16.78	17.25	17.74
	8H	13.59	14.01	14.10	14.50	15.08	16.51	16.93	17.03	17.43	18.00