

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1059635

Luminaire Tested: S123RDRP-H340D940-X4F0-XX-UDD-BVL-S

Issue Date: 8/7/2025

**Test Information**

Test Method: LM-79-2024  
Report Number: P1059635  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2406-143-69)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/7/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123RDRP-H340D940-X4F0-XX-UDD-BVL-S  
Description: DEFINE 3 SILVER REGRESSED DIRECT RECESSED HOUSING WITH BLACK STRAIGHT BLADE  
LOUVER WITH DIFFUSER  
HIGH PERFORMANCE LIGHT ENGINE  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 290.9 lumens  
Efficiency: N/A  
Efficacy: 24.9 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 1.06 / 0.94  
Luminous Opening: Rectangular (W 0.23' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1059635

CATALOG NUMBER: S123RDRP-H340D940-X4F0-XX-UDD-BVL-S

### Luminous Intensity Polar Plot





TEST NUMBER: P1059635

CATALOG NUMBER: S123RDRP-H340D940-X4F0-XX-UDD-BVL-S

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90
2	105	99	94	89	102	97	92	88	94	90	86	90	87	85	88	85	83	81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73
4	92	83	76	71	90	81	75	70	79	74	69	77	72	69	75	71	68	66
5	86	76	69	64	84	75	68	64	73	67	63	71	66	62	70	65	62	60
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	57	55
7	76	65	58	53	75	64	58	53	63	57	53	62	56	52	61	56	52	50
8	72	61	54	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2843	2843	2843
5°	2745	2794	2837
10°	2534	2648	2790
15°	2273	2448	2710
20°	1984	2207	2582
25°	1669	1943	2423
30°	1341	1657	2270
35°	982	1365	2123
40°	607	1061	1974
45°	234	799	1759
50°	115	548	1489
55°	90	303	1167
60°	61	251	782
65°	53	225	350
70°	51	203	203
75°	68	218	200
80°	101	277	223
85°	148	445	296

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 1759 cd/sqm



TEST NUMBER: P1059635

CATALOG NUMBER: S123RDRP-H340D940-X4F0-XX-UDD-BVL-S

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	22.2	7.6
10°-20°	56.8	19.5
20°-30°	70.5	24.3
30°-40°	63.2	21.7
40°-50°	41.5	14.3
50°-60°	20.8	7.2
60°-70°	8.2	2.8
70°-80°	4.6	1.6
80°-90°	2.9	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	149.6	51.4
0°-40°	212.8	73.2
0°-60°	275.1	94.6
0°-90°	290.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	290.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	242	242	242	242	242	
5°	233	237	237	238	241	22
15°	187	193	201	215	223	52
25°	129	137	150	171	187	59
35°	68	78	95	124	148	42
45°	14	23	48	81	106	13
55°	4	5	15	40	57	4
65°	2	5	8	10	13	2
75°	2	5	5	4	4	2
85°	1	3	3	3	2	1
90°	0	0	0	0	0	



TEST NUMBER: P1059635

CATALOG NUMBER: S123RDRP-H340D940-X4F0-XX-UDD-BVL-S

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	242.1	242.1	242.1	242.1	242.1
2.5°	239.2	242.5	240.7	240.7	241.0
5°	232.9	236.6	237.0	238.4	240.7
7.5°	223.6	228.4	230.7	235.1	238.4
10°	212.5	217.7	222.1	229.9	234.0
12.5°	200.3	205.5	212.2	222.9	229.2
15°	187.0	192.9	201.4	215.1	222.9
17.5°	173.3	179.2	189.6	205.1	215.1
20°	158.8	165.5	176.6	194.4	206.6
22.5°	144.4	151.8	163.6	182.9	197.0
25°	128.8	137.0	150.0	171.1	187.0
27.5°	114.0	122.6	136.3	159.2	177.3
30°	98.9	107.4	122.2	147.0	167.4
32.5°	83.3	92.9	108.5	135.5	157.4
35°	68.5	77.8	95.2	124.4	148.1
37.5°	54.1	63.3	81.5	113.7	138.8
40°	39.6	49.2	69.2	103.3	128.8
42.5°	25.9	35.9	58.5	92.9	117.7
45°	14.1	23.3	48.1	81.1	105.9
47.5°	7.8	12.6	38.9	70.0	94.4
50°	6.3	7.0	30.0	59.6	81.5
52.5°	5.2	5.9	21.5	49.6	69.6
55°	4.4	5.2	14.8	40.0	57.0
57.5°	3.7	4.4	11.8	30.7	44.8
60°	2.6	4.4	10.7	22.6	33.3
62.5°	2.2	4.4	9.3	15.6	22.2
65°	1.9	5.2	8.1	10.4	12.6
67.5°	1.5	5.2	7.0	6.7	6.7
70°	1.5	5.2	5.9	5.6	5.9
72.5°	1.5	5.6	5.6	5.2	5.2
75°	1.5	4.8	4.8	4.4	4.4
77.5°	1.5	4.4	4.4	4.1	4.1
80°	1.5	4.1	4.1	3.7	3.3
82.5°	1.5	3.7	3.7	3.3	3.0
85°	1.1	3.3	3.3	3.3	2.2
87.5°	1.1	3.0	3.3	3.0	1.9
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1059635  
 CATALOG NUMBER: S123RDRP-H340D940-X4F0-XX-UDD-BVL-S

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	10.17	11.43	10.54	11.74	12.06
	3H	0.00	0.00	0.00	0.05	0.41	10.25	11.37	10.63	11.70	12.06
	4H	0.00	0.82	0.19	1.17	1.56	10.32	11.35	10.72	11.70	12.09
	6H	0.84	1.79	1.26	2.17	2.56	10.41	11.36	10.83	11.74	12.13
	8H	1.39	2.29	1.82	2.68	3.09	10.48	11.37	10.91	11.77	12.17
	12H	1.87	2.73	2.30	3.11	3.54	10.54	11.40	10.98	11.79	12.22
4H	2H	0.00	0.34	0.00	0.70	1.08	10.03	11.07	10.44	11.42	11.80
	3H	1.81	2.66	2.22	3.06	3.46	10.21	11.05	10.62	11.46	11.86
	4H	3.15	3.91	3.59	4.33	4.77	10.33	11.09	10.77	11.51	11.96
	6H	4.29	4.94	4.75	5.39	5.86	10.55	11.20	11.01	11.65	12.12
	8H	4.81	5.42	5.28	5.86	6.34	10.68	11.29	11.15	11.73	12.21
	12H	5.26	5.80	5.75	6.28	6.76	10.83	11.37	11.32	11.86	12.33
8H	4H	4.07	4.68	4.54	5.12	5.60	10.34	10.95	10.81	11.40	11.87
	6H	5.68	6.18	6.18	6.67	7.16	10.67	11.17	11.17	11.67	12.15
	8H	6.50	6.96	7.03	7.47	7.96	10.90	11.35	11.42	11.86	12.36
	12H	7.27	7.67	7.79	8.17	8.74	11.22	11.62	11.73	12.11	12.68
12H	4H	4.23	4.77	4.72	5.26	5.73	10.33	10.87	10.81	11.35	11.82
	6H	5.99	6.44	6.52	6.96	7.45	10.70	11.15	11.22	11.67	12.16
	8H	7.00	7.40	7.52	7.90	8.47	11.01	11.41	11.52	11.90	12.47