

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1055967

Luminaire Tested: S124R3DRP-S1020D927-X4F0-XX-UDD-F-W

Issue Date: 7/25/2025

**Test Information**

Test Method: LM-79-2024  
Report Number: P1055967  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2503-402-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/25/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S124R3DRP-S1020D927-X4F0-XX-UDD-F-W  
Description: DEFINE 4, WHITE 3-INCH REGRESSED DIRECT RECESSED HOUSING WITH FROSTED LENS  
CORE LIGHT ENGINE  
Light Source: 2700K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2755.5 lumens  
Efficiency: N/A  
Efficacy: 79.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.95 / 1.12  
Luminous Opening: Rectangular (W 0.31' x L: 3.9' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 34.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1055967

CATALOG NUMBER: S124R3DRP-S1020D927-X4F0-XX-UDD-F-W

### Luminous Intensity Polar Plot





TEST NUMBER: P1055967

CATALOG NUMBER: S124R3DRP-S1020D927-X4F0-XX-UDD-F-W

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	110	105	102	98	107	103	100	97	99	96	93	95	93	91	92	90	88	86				
2	101	93	87	82	98	91	86	81	88	83	79	85	81	77	82	78	76	73				
3	93	83	75	69	90	81	74	69	79	73	68	76	71	67	73	69	65	63				
4	85	74	66	60	83	73	65	60	71	64	59	68	63	58	66	61	57	55				
5	79	67	59	53	77	66	58	52	64	57	52	62	56	51	60	55	51	49				
6	73	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43				
7	68	56	47	42	67	55	47	42	53	46	41	52	46	41	51	45	41	39				
8	64	51	43	38	62	51	43	38	49	42	37	48	42	37	47	41	37	35				
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32				
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	41	35	31	29				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	12232	12232	12232
5°	12134	12107	12098
10°	12064	11744	11597
15°	11937	11302	10958
20°	11781	10766	10162
25°	11589	10149	9235
30°	11360	9448	8294
35°	11119	8713	7384
40°	10869	7954	6533
45°	10603	7217	5740
50°	10278	6441	4957
55°	9964	5665	4504
60°	9612	4861	4177
65°	9180	4408	3897
70°	8525	4079	3684
75°	7720	3754	3478
80°	6736	3472	3264
85°	5163	3206	2993

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 10603 cd/sqm



TEST NUMBER: P1055967

CATALOG NUMBER: S124R3DRP-S1020D927-X4F0-XX-UDD-F-W

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	128.8	4.7
10°-20°	349.4	12.7
20°-30°	483.8	17.6
30°-40°	519.2	18.8
40°-50°	472.2	17.1
50°-60°	371.8	13.5
60°-70°	254.5	9.2
70°-80°	137.0	5.0
80°-90°	38.8	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	961.9	34.9
0°-40°	1481.2	53.8
0°-60°	2325.2	84.4
0°-90°	2755.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2755.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1384	1384	1384	1384	1384	
5°	1367	1382	1364	1357	1363	130
15°	1304	1290	1235	1201	1197	368
25°	1188	1139	1040	965	947	547
35°	1030	950	807	710	684	644
45°	848	740	577	477	459	654
55°	646	523	368	296	292	578
65°	439	314	211	187	186	433
75°	226	137	110	101	102	241
85°	51	35	32	30	30	61
90°	0	0	0	0	0	



TEST NUMBER: P1055967

CATALOG NUMBER: S124R3DRP-S1020D927-X4F0-XX-UDD-F-W

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1383.5	1383.5	1383.5	1383.5	1383.5
2.5°	1373.3	1389.6	1377.4	1379.4	1381.4
5°	1367.2	1382.5	1364.1	1357.0	1363.1
7.5°	1357.0	1367.2	1338.7	1325.4	1331.6
10°	1343.8	1345.8	1308.1	1288.8	1291.8
12.5°	1325.4	1320.4	1274.5	1247.1	1249.1
15°	1304.1	1289.8	1234.8	1201.2	1197.2
17.5°	1279.6	1256.2	1191.1	1148.3	1140.2
20°	1252.1	1220.6	1144.2	1089.3	1080.1
22.5°	1221.6	1180.9	1093.3	1028.2	1015.0
25°	1188.0	1139.1	1040.4	965.1	946.7
27.5°	1151.4	1094.4	983.4	900.9	877.5
30°	1112.7	1047.5	925.4	836.8	812.4
32.5°	1073.0	999.7	866.3	772.7	747.2
35°	1030.2	949.8	807.3	709.6	684.1
37.5°	986.4	897.9	747.2	648.5	622.0
40°	941.7	846.0	689.2	587.4	566.0
42.5°	895.8	793.0	632.2	530.4	511.0
45°	848.0	740.1	577.2	477.4	459.1
47.5°	799.1	686.1	521.2	427.6	410.3
50°	747.2	632.2	468.3	378.7	360.4
52.5°	697.3	577.2	417.4	330.9	321.7
55°	646.4	523.3	367.5	296.2	292.2
57.5°	595.5	469.3	321.7	268.8	264.7
60°	543.6	416.4	274.9	240.2	236.2
62.5°	491.7	364.4	240.2	212.8	210.7
65°	438.8	313.5	210.7	187.3	186.3
67.5°	382.8	264.7	184.3	164.9	163.9
70°	329.8	215.8	157.8	142.5	142.5
72.5°	280.0	171.0	133.4	121.1	121.1
75°	226.0	137.4	109.9	100.8	101.8
77.5°	178.2	107.9	88.6	82.5	82.5
80°	132.3	80.4	68.2	63.1	64.1
82.5°	89.6	56.0	48.9	45.8	45.8
85°	50.9	34.6	31.6	29.5	29.5
87.5°	18.3	16.3	15.3	13.2	14.3
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1055967  
 CATALOG NUMBER: S124R3DRP-S1020D927-X4F0-XX-UDD-F-W

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.84	21.37	20.21	21.68	21.99	15.62	17.14	15.98	17.46	17.77
	3H	21.62	22.99	21.99	23.31	23.68	17.23	18.60	17.61	18.93	19.29
	4H	22.29	23.57	22.69	23.92	24.30	17.86	19.15	18.26	19.50	19.87
	6H	22.80	23.99	23.21	24.35	24.74	18.36	19.55	18.77	19.92	20.31
	8H	22.96	24.09	23.39	24.48	24.88	18.53	19.66	18.96	20.05	20.45
	12H	23.06	24.14	23.49	24.53	24.96	18.65	19.74	19.08	20.12	20.55
4H	2H	19.94	21.22	20.34	21.57	21.95	16.34	17.62	16.74	17.97	18.35
	3H	21.88	22.95	22.29	23.35	23.75	18.15	19.21	18.56	19.61	20.02
	4H	22.64	23.60	23.07	24.02	24.45	18.88	19.85	19.31	20.26	20.70
	6H	23.27	24.11	23.73	24.55	25.01	19.50	20.34	19.96	20.78	21.24
	8H	23.49	24.28	23.95	24.72	25.19	19.71	20.50	20.18	20.94	21.41
	12H	23.65	24.35	24.13	24.83	25.30	19.88	20.58	20.36	21.06	21.53
8H	4H	22.69	23.48	23.16	23.92	24.39	19.27	20.06	19.73	20.50	20.97
	6H	23.39	24.04	23.89	24.53	25.01	20.00	20.65	20.50	21.14	21.62
	8H	23.66	24.24	24.17	24.75	25.24	20.29	20.87	20.80	21.38	21.87
	12H	23.88	24.39	24.39	24.89	25.45	20.54	21.05	21.04	21.54	22.11
12H	4H	22.69	23.39	23.17	23.87	24.34	19.33	20.03	19.81	20.51	20.98
	6H	23.39	23.97	23.90	24.48	24.97	20.09	20.67	20.60	21.18	21.67
	8H	23.70	24.21	24.20	24.70	25.27	20.43	20.95	20.94	21.44	22.01