

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1056158

Luminaire Tested: S124R3DRP-H350D930-X4F0-XX-UDD-F-S

Issue Date: 7/25/2025

Test Information

Test Method: LM-79-2024
Report Number: P1056158
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2503-402-9)
Test Lab: INNOVATION CENTER
Issue Date: 7/25/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124R3DRP-H350D930-X4F0-XX-UDD-F-S
Description: DEFINE 4, SILVER 3-INCH REGRESSED DIRECT RECESSED HOUSING WITH FROSTED LENS
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 614.7 lumens
Efficiency: N/A
Efficacy: 52.5 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 0.87 / 1.03
Luminous Opening: Rectangular (W 0.31' x L: 3.9' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1056158

CATALOG NUMBER: S124R3DRP-H350D930-X4F0-XX-UDD-F-S

Luminous Intensity Polar Plot



TEST NUMBER: P1056158

CATALOG NUMBER: S124R3DRP-H350D930-X4F0-XX-UDD-F-S

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89					89			
2	103	96	91	86	101	94	89	85	91	87	83	88	84	81	85	82	79	78					78			
3	95	87	80	74	93	85	79	74	82	77	73	80	75	71	77	73	70	68					68			
4	89	78	71	65	86	77	70	65	75	69	64	73	67	63	71	66	62	60					60			
5	82	71	64	58	80	70	63	58	68	62	57	66	61	56	65	60	56	54					54			
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	48					48			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44					44			
8	67	55	48	42	66	55	47	42	53	47	42	52	46	42	51	46	42	40					40			
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37					37			
10	60	48	41	36	59	47	40	36	46	40	36	45	40	35	45	39	35	34					34			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3361	3361	3361
5°	3327	3315	3315
10°	3302	3207	3147
15°	3263	3053	2910
20°	3211	2857	2608
25°	3146	2628	2265
30°	3079	2368	1908
35°	2999	2090	1570
40°	2913	1794	1238
45°	2823	1492	925
50°	2726	1173	677
55°	2619	868	540
60°	2504	601	414
65°	2356	467	303
70°	2133	328	238
75°	1862	229	181
80°	1497	178	163
85°	822	142	142

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2823 cd/sqm



TEST NUMBER: P1056158

CATALOG NUMBER: S124R3DRP-H350D930-X4F0-XX-UDD-F-S

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.3	5.7
10°-20°	94.2	15.3
20°-30°	125.7	20.4
30°-40°	126.5	20.6
40°-50°	103.8	16.9
50°-60°	70.9	11.5
60°-70°	39.6	6.4
70°-80°	15.7	2.6
80°-90°	3.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	255.2	41.5
0°-40°	381.7	62.1
0°-60°	556.4	90.5
0°-90°	614.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	614.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	380	380	380	380	380	
5°	375	379	374	372	374	36
15°	356	353	334	322	318	100
25°	322	307	269	242	232	149
35°	278	248	194	157	146	174
45°	226	184	119	84	74	174
55°	170	119	56	38	35	152
65°	113	57	22	16	14	111
75°	54	15	7	6	5	58
85°	8	1	1	1	1	11
90°	0	0	0	0	0	



TEST NUMBER: P1056158

CATALOG NUMBER: S124R3DRP-H350D930-X4F0-XX-UDD-F-S

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	380.2	380.2	380.2	380.2	380.2
2.5°	376.7	381.3	378.1	378.4	379.1
5°	374.9	379.1	373.5	371.7	373.5
7.5°	371.7	374.9	366.4	362.8	363.6
10°	367.8	368.9	357.2	351.2	350.5
12.5°	362.8	361.4	346.2	337.4	335.2
15°	356.5	352.6	333.5	321.8	317.9
17.5°	349.0	342.3	319.3	304.1	298.4
20°	341.3	331.3	303.7	284.3	277.2
22.5°	332.0	319.7	287.1	263.4	255.2
25°	322.5	306.6	269.4	242.1	232.2
27.5°	312.6	293.1	251.0	220.5	210.6
30°	301.6	278.6	231.9	198.9	186.9
32.5°	289.9	263.7	212.8	177.7	166.4
35°	277.9	248.5	193.6	156.8	145.5
37.5°	265.5	232.9	174.5	137.0	125.7
40°	252.4	217.0	155.4	118.2	107.3
42.5°	238.9	200.7	137.0	100.5	90.3
45°	225.8	184.4	119.3	83.9	74.0
47.5°	212.0	168.1	102.0	68.3	59.8
50°	198.2	151.9	85.3	54.9	49.2
52.5°	184.1	135.6	70.1	45.0	41.1
55°	169.9	119.3	56.3	37.5	35.0
57.5°	155.8	103.0	43.5	31.9	29.0
60°	141.6	87.1	34.0	25.8	23.4
62.5°	127.1	71.2	28.0	20.5	18.4
65°	112.6	56.6	22.3	15.9	14.5
67.5°	98.1	43.2	17.0	12.4	11.3
70°	82.5	30.8	12.7	9.6	9.2
72.5°	69.0	20.9	9.2	7.4	7.1
75°	54.5	14.9	6.7	5.7	5.3
77.5°	42.1	9.6	5.0	4.6	4.2
80°	29.4	5.3	3.5	3.2	3.2
82.5°	18.1	2.8	2.5	2.1	2.1
85°	8.1	1.4	1.4	1.4	1.4
87.5°	1.4	0.7	0.7	0.7	0.7
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1056158
 CATALOG NUMBER: S124R3DRP-H350D930-X4F0-XX-UDD-F-S

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.94	16.34	15.30	16.66	16.97	6.03	7.44	6.40	7.75	8.07
	3H	16.52	17.77	16.90	18.10	18.47	6.62	7.87	7.00	8.20	8.57
	4H	17.12	18.29	17.52	18.64	19.02	6.78	7.95	7.18	8.30	8.68
	6H	17.55	18.62	17.96	18.99	19.39	6.89	7.96	7.30	8.33	8.72
	8H	17.66	18.68	18.09	19.07	19.48	6.90	7.93	7.33	8.32	8.72
	12H	17.71	18.68	18.14	19.06	19.49	6.91	7.89	7.34	8.27	8.70
4H	2H	14.79	15.96	15.19	16.31	16.69	6.61	7.78	7.02	8.13	8.51
	3H	16.44	17.40	16.85	17.80	18.20	7.33	8.28	7.74	8.69	9.09
	4H	17.04	17.90	17.48	18.32	18.76	7.53	8.39	7.96	8.81	9.25
	6H	17.54	18.28	18.00	18.72	19.19	7.70	8.44	8.16	8.88	9.35
	8H	17.68	18.37	18.15	18.82	19.29	7.73	8.42	8.19	8.87	9.33
	12H	17.75	18.37	18.24	18.85	19.32	7.75	8.36	8.24	8.85	9.32
8H	4H	16.94	17.63	17.40	18.08	18.54	7.80	8.49	8.27	8.94	9.41
	6H	17.42	17.99	17.92	18.48	18.96	8.00	8.57	8.50	9.07	9.55
	8H	17.56	18.07	18.08	18.58	19.08	8.06	8.57	8.58	9.08	9.57
	12H	17.65	18.10	18.17	18.60	19.17	8.12	8.57	8.63	9.06	9.63
12H	4H	16.90	17.51	17.38	17.99	18.47	7.83	8.44	8.31	8.92	9.40
	6H	17.36	17.87	17.88	18.39	18.88	8.03	8.54	8.55	9.06	9.55
	8H	17.53	17.98	18.04	18.47	19.04	8.12	8.57	8.64	9.07	9.64