

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1056050

Luminaire Tested: S124R3DRP-S575D930-X4F0-XX-UDD-F-S

Issue Date: 7/25/2025

Test Information

Test Method: LM-79-2024
Report Number: P1056050
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2503-402-9)
Test Lab: INNOVATION CENTER
Issue Date: 7/25/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124R3DRP-S575D930-X4F0-XX-UDD-F-S
Description: DEFINE 4, SILVER 3-INCH REGRESSED DIRECT RECESSED HOUSING WITH FROSTED LENS
CORE LIGHT ENGINE
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1022.5 lumens
Efficiency: N/A
Efficacy: 53.5 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 0.87 / 1.03
Luminous Opening: Rectangular (W 0.31' x L: 3.9' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1056050

CATALOG NUMBER: S124R3DRP-S575D930-X4F0-XX-UDD-F-S

Luminous Intensity Polar Plot





TEST NUMBER: P1056050

CATALOG NUMBER: S124R3DRP-S575D930-X4F0-XX-UDD-F-S

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89
2	103	96	91	86	101	94	89	85	91	87	83	88	84	81	85	82	79	78
3	95	87	80	74	93	85	79	74	82	77	73	80	75	71	77	73	70	68
4	89	78	71	65	86	77	70	65	75	69	64	73	67	63	71	66	62	60
5	82	71	64	58	80	70	63	58	68	62	57	66	61	56	65	60	56	54
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	48
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44
8	67	55	48	42	66	55	47	42	53	47	42	52	46	42	51	46	42	40
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37
10	60	48	41	36	59	47	40	36	46	40	36	45	40	35	45	39	35	34

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5590	5590	5590
5°	5534	5512	5512
10°	5492	5334	5233
15°	5427	5076	4839
20°	5340	4753	4337
25°	5233	4370	3768
30°	5121	3937	3174
35°	4989	3477	2612
40°	4845	2984	2059
45°	4696	2481	1539
50°	4535	1952	1125
55°	4356	1443	899
60°	4164	999	688
65°	3916	776	504
70°	3547	548	396
75°	3098	383	301
80°	2490	300	270
85°	1369	243	243

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4696 cd/sqm



TEST NUMBER: P1056050

CATALOG NUMBER: S124R3DRP-S575D930-X4F0-XX-UDD-F-S

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.7	5.7
10°-20°	156.7	15.3
20°-30°	209.0	20.4
30°-40°	210.5	20.6
40°-50°	172.6	16.9
50°-60°	118.0	11.5
60°-70°	65.9	6.4
70°-80°	26.1	2.6
80°-90°	5.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	424.4	41.5
0°-40°	634.9	62.1
0°-60°	925.4	90.5
0°-90°	1022.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1022.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	632	632	632	632	632	
5°	624	631	621	618	621	59
15°	593	586	555	535	529	167
25°	536	510	448	403	386	247
35°	462	413	322	261	242	289
45°	376	307	198	140	123	290
55°	283	198	94	62	58	253
65°	187	94	37	26	24	185
75°	91	25	11	9	9	97
85°	14	2	2	2	2	19
90°	0	0	0	0	0	



TEST NUMBER: P1056050

CATALOG NUMBER: S124R3DRP-S575D930-X4F0-XX-UDD-F-S

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	632.3	632.3	632.3	632.3	632.3
2.5°	626.4	634.1	628.8	629.4	630.6
5°	623.5	630.6	621.1	618.2	621.1
7.5°	618.2	623.5	609.4	603.5	604.7
10°	611.7	613.5	594.1	584.1	582.9
12.5°	603.5	601.1	575.8	561.1	557.6
15°	592.9	586.4	554.6	535.2	528.7
17.5°	580.5	569.3	531.1	505.7	496.3
20°	567.6	551.1	505.2	472.8	461.0
22.5°	552.3	531.7	477.5	438.0	424.5
25°	536.4	509.9	448.0	402.7	386.2
27.5°	519.9	487.5	417.4	366.8	350.3
30°	501.6	463.4	385.6	330.9	310.9
32.5°	482.2	438.6	353.8	295.6	276.7
35°	462.2	413.3	322.1	260.8	242.0
37.5°	441.6	387.4	290.3	227.9	209.0
40°	419.8	360.9	258.5	196.6	178.4
42.5°	397.4	333.8	227.9	167.2	150.1
45°	375.6	306.7	198.4	139.5	123.1
47.5°	352.7	279.7	169.6	113.6	99.5
50°	329.7	252.6	141.9	91.3	81.8
52.5°	306.2	225.5	116.6	74.8	68.3
55°	282.6	198.4	93.6	62.4	58.3
57.5°	259.1	171.3	72.4	53.0	48.3
60°	235.5	144.8	56.5	43.0	38.9
62.5°	211.4	118.3	46.5	34.1	30.6
65°	187.2	94.2	37.1	26.5	24.1
67.5°	163.1	71.8	28.3	20.6	18.8
70°	137.2	51.2	21.2	15.9	15.3
72.5°	114.8	34.7	15.3	12.4	11.8
75°	90.7	24.7	11.2	9.4	8.8
77.5°	70.1	15.9	8.2	7.7	7.1
80°	48.9	8.8	5.9	5.3	5.3
82.5°	30.0	4.7	4.1	3.5	3.5
85°	13.5	2.4	2.4	2.4	2.4
87.5°	2.4	1.2	1.2	1.2	1.2
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1056050
 CATALOG NUMBER: S124R3DRP-S575D930-X4F0-XX-UDD-F-S

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.70	18.11	17.07	18.42	18.74	7.80	9.20	8.16	9.52	9.83
	3H	18.29	19.54	18.67	19.87	20.23	8.39	9.64	8.76	9.97	10.33
	4H	18.88	20.05	19.29	20.40	20.78	8.54	9.71	8.94	10.06	10.44
	6H	19.32	20.39	19.73	20.76	21.15	8.65	9.73	9.06	10.10	10.49
	8H	19.43	20.45	19.86	20.84	21.24	8.67	9.69	9.10	10.08	10.48
	12H	19.47	20.45	19.90	20.83	21.26	8.68	9.65	9.11	10.04	10.47
4H	2H	16.56	17.73	16.96	18.08	18.46	8.38	9.55	8.78	9.90	10.28
	3H	18.20	19.16	18.62	19.57	19.97	9.09	10.05	9.50	10.45	10.85
	4H	18.81	19.67	19.24	20.09	20.53	9.29	10.15	9.73	10.57	11.01
	6H	19.30	20.04	19.76	20.49	20.95	9.46	10.20	9.92	10.65	11.11
	8H	19.45	20.14	19.91	20.58	21.05	9.49	10.19	9.96	10.63	11.10
	12H	19.52	20.13	20.00	20.61	21.09	9.52	10.13	10.00	10.61	11.09
8H	4H	18.70	19.40	19.17	19.84	20.31	9.56	10.26	10.03	10.70	11.17
	6H	19.19	19.75	19.69	20.25	20.73	9.77	10.34	10.27	10.83	11.31
	8H	19.33	19.84	19.85	20.35	20.84	9.83	10.33	10.34	10.85	11.34
	12H	19.42	19.87	19.93	20.36	20.93	9.89	10.33	10.40	10.83	11.40
12H	4H	18.66	19.28	19.15	19.76	20.23	9.59	10.20	10.08	10.69	11.16
	6H	19.13	19.64	19.65	20.15	20.64	9.80	10.31	10.32	10.82	11.31
	8H	19.29	19.74	19.81	20.24	20.81	9.89	10.34	10.40	10.83	11.40