

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1060671

Luminaire Tested: S124RDRP-H1020D930-X4F0-XX-UDD-BVL-W

Issue Date: 8/7/2025

**Test Information**

Test Method: LM-79-2024  
Report Number: P1060671  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2406-143-75)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/7/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S124RDRP-H1020D930-X4F0-XX-UDD-BVL-W  
Description: DEFINE 4 WHITE REGRESSED DIRECT RECESSED HOUSING WITH BLACK STRAIGHT BLADE  
LOUVER WITH DIFFUSER  
HIGH PERFORMANCE LIGHT ENGINE  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1029.2 lumens  
Efficiency: N/A  
Efficacy: 33.0 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 1.11 / 0.96  
Luminous Opening: Rectangular (W 0.31' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 31.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1060671

CATALOG NUMBER: S124RDRP-H1020D930-X4F0-XX-UDD-BVL-W

### Luminous Intensity Polar Plot





TEST NUMBER: P1060671

CATALOG NUMBER: S124RDRP-H1020D930-X4F0-XX-UDD-BVL-W

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90
2	105	98	93	89	102	97	92	88	93	89	86	90	87	84	87	85	82	81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	75	81	77	74	72
4	91	82	75	70	89	81	75	70	79	73	69	76	72	68	74	70	67	65
5	86	75	68	63	84	74	68	63	72	67	62	71	66	62	69	65	61	59
6	80	70	62	57	79	69	62	57	67	61	56	66	60	56	64	59	56	54
7	75	64	57	52	74	64	57	52	62	56	52	61	55	51	60	55	51	49
8	71	60	53	48	70	59	52	48	58	52	48	57	51	47	56	51	47	45
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42
10	63	52	45	41	62	52	45	41	51	45	41	50	44	41	49	44	40	39

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7032	7032	7032
5°	6794	6894	7026
10°	6261	6554	6948
15°	5623	6092	6793
20°	4901	5542	6561
25°	4135	4918	6275
30°	3336	4251	5947
35°	2468	3556	5612
40°	1530	2834	5280
45°	606	2067	4972
50°	269	1297	4520
55°	216	676	3957
60°	148	512	3153
65°	98	507	2168
70°	96	458	1015
75°	126	446	446
80°	188	521	521
85°	375	1037	761

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 4972 cd/sqm



TEST NUMBER: P1060671

CATALOG NUMBER: S124RDRP-H1020D930-X4F0-XX-UDD-BVL-W

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	74.9	7.3
10°-20°	193.3	18.8
20°-30°	244.0	23.7
30°-40°	223.9	21.8
40°-50°	152.5	14.8
50°-60°	83.1	8.1
60°-70°	35.9	3.5
70°-80°	13.1	1.3
80°-90°	8.4	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	512.3	49.8
0°-40°	736.2	71.5
0°-60°	971.7	94.4
0°-90°	1029.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1029.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	817	817	817	817	817	
5°	786	796	798	806	813	73
15°	631	653	683	732	762	175
25°	435	466	518	600	660	199
35°	235	269	338	446	534	145
45°	50	83	170	301	408	46
55°	14	15	45	166	264	13
65°	5	7	25	52	106	6
75°	4	12	13	13	13	4
85°	4	9	10	10	8	3
90°	0	0	0	0	0	

TEST NUMBER: P1060671

CATALOG NUMBER: S124RDRP-H1020D930-X4F0-XX-UDD-BVL-W

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	816.6	816.6	816.6	816.6	816.6
2.5°	807.1	816.6	809.9	811.8	811.8
5°	786.0	796.5	797.5	806.1	812.8
7.5°	754.3	769.7	777.3	794.6	806.1
10°	716.0	734.2	749.5	779.3	794.6
12.5°	674.8	695.9	718.9	758.2	780.2
15°	630.7	652.7	683.4	732.3	762.0
17.5°	581.8	608.6	646.0	704.5	740.9
20°	534.8	561.7	604.8	670.9	716.0
22.5°	486.0	513.8	561.7	635.5	689.2
25°	435.2	465.8	517.6	600.0	660.4
27.5°	385.3	417.9	472.5	562.6	629.7
30°	335.5	368.1	427.5	524.3	598.1
32.5°	284.7	318.2	382.4	484.0	565.5
35°	234.8	269.3	338.3	445.7	533.9
37.5°	184.0	220.5	294.3	408.3	502.3
40°	136.1	172.5	252.1	370.9	469.7
42.5°	91.1	127.5	209.0	334.5	439.0
45°	49.8	83.4	169.7	301.0	408.3
47.5°	26.8	46.0	131.3	268.4	373.8
50°	20.1	24.9	96.8	233.9	337.4
52.5°	17.3	19.2	67.1	197.5	301.0
55°	14.4	15.3	45.0	165.8	263.6
57.5°	11.5	12.5	33.5	134.2	223.3
60°	8.6	10.5	29.7	103.5	183.1
62.5°	6.7	8.6	27.8	75.7	144.7
65°	4.8	6.7	24.9	51.8	106.4
67.5°	4.8	7.7	21.1	33.5	71.9
70°	3.8	10.5	18.2	22.0	40.3
72.5°	3.8	11.5	15.3	15.3	15.3
75°	3.8	12.5	13.4	13.4	13.4
77.5°	3.8	11.5	12.5	11.5	11.5
80°	3.8	10.5	10.5	10.5	10.5
82.5°	3.8	9.6	10.5	10.5	8.6
85°	3.8	8.6	10.5	10.5	7.7
87.5°	2.9	8.6	9.6	9.6	5.8
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1060671

CATALOG NUMBER: S124RDRP-H1020D930-X4F0-XX-UDD-BVL-W

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	15.19	16.46	15.55	16.78	17.09
	3H	0.00	0.38	0.00	0.71	1.08	15.56	16.69	15.94	17.02	17.39
	4H	0.46	1.51	0.87	1.87	2.25	15.54	16.59	15.94	16.94	17.33
	6H	1.63	2.60	2.05	2.97	3.36	15.53	16.49	15.94	16.86	17.26
	8H	2.22	3.13	2.65	3.52	3.93	15.53	16.44	15.96	16.83	17.24
	12H	2.88	3.76	3.32	4.14	4.57	15.54	16.41	15.97	16.80	17.23
4H	2H	1.43	2.48	1.84	2.84	3.22	15.00	16.05	15.40	16.40	16.78
	3H	3.01	3.87	3.42	4.27	4.68	15.42	16.27	15.83	16.68	17.08
	4H	4.31	5.08	4.74	5.50	5.94	15.41	16.18	15.85	16.60	17.04
	6H	5.43	6.09	5.89	6.54	7.01	15.45	16.12	15.92	16.56	17.03
	8H	5.94	6.55	6.41	7.00	7.47	15.48	16.10	15.95	16.55	17.02
	12H	6.48	7.03	6.97	7.51	7.99	15.55	16.09	16.03	16.57	17.05
8H	4H	5.39	6.01	5.86	6.46	6.93	15.32	15.94	15.79	16.39	16.86
	6H	6.93	7.43	7.43	7.93	8.41	15.40	15.91	15.90	16.40	16.89
	8H	7.74	8.19	8.26	8.71	9.20	15.48	15.94	16.01	16.45	16.95
	12H	8.56	8.97	9.08	9.46	10.03	15.65	16.06	16.17	16.55	17.12
12H	4H	5.58	6.13	6.07	6.61	7.09	15.29	15.83	15.77	16.32	16.79
	6H	7.28	7.74	7.81	8.25	8.75	15.37	15.83	15.90	16.35	16.84
	8H	8.29	8.69	8.81	9.19	9.76	15.51	15.91	16.03	16.41	16.98