

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1060678

Luminaire Tested: S124RDRP-H1020D935-X4F0-XX-UDD-BVL-B

Issue Date: 8/7/2025

**Test Information**

Test Method: LM-79-2024  
Report Number: P1060678  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2406-143-39)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/7/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S124RDRP-H1020D935-X4F0-XX-UDD-BVL-B  
Description: DEFINE 4 BLACK REGRESSED DIRECT RECESSED HOUSING WITH BLACK STRAIGHT BLADE  
LOUVER WITH DIFFUSER  
HIGH PERFORMANCE LIGHT ENGINE  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 913.4 lumens  
Efficiency: N/A  
Efficacy: 29.3 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 0.83 / 0.98  
Luminous Opening: Rectangular (W 0.31' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 31.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1060678

CATALOG NUMBER: S124RDRP-H1020D935-X4F0-XX-UDD-BVL-B

### Luminous Intensity Polar Plot





TEST NUMBER: P1060678

CATALOG NUMBER: S124RDRP-H1020D935-X4F0-XX-UDD-BVL-B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	99	95	90	103	98	93	89	94	91	87	91	88	86	88	86	84	82
3	98	91	85	80	96	89	84	79	86	82	78	84	80	77	82	78	75	74
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66
5	86	76	69	64	84	75	69	64	73	67	63	71	66	62	70	65	62	60
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	56	55
7	76	65	58	53	74	64	57	53	63	57	52	61	56	52	60	55	52	50
8	71	60	53	48	70	60	53	48	58	52	48	57	52	48	56	51	47	46
9	67	56	49	44	66	56	49	44	54	48	44	54	48	44	53	48	44	42
10	64	52	46	41	63	52	45	41	51	45	41	50	45	41	49	44	41	39

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6023	6023	6023
5°	6003	5916	5907
10°	5976	5684	5507
15°	5894	5336	4983
20°	5735	4901	4419
25°	5542	4437	3813
30°	5308	3890	3156
35°	5015	3337	2455
40°	4727	2738	1715
45°	4383	2106	850
50°	3955	1421	284
55°	3415	728	197
60°	2733	262	140
65°	1875	145	61
70°	841	76	50
75°	0	33	33
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 4383 cd/sqm



TEST NUMBER: P1060678

CATALOG NUMBER: S124RDRP-H1020D935-X4F0-XX-UDD-BVL-B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	64.6	7.1
10°-20°	169.3	18.5
20°-30°	219.2	24.0
30°-40°	208.3	22.8
40°-50°	147.5	16.1
50°-60°	75.7	8.3
60°-70°	26.5	2.9
70°-80°	2.3	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	453.2	49.6
0°-40°	661.5	72.4
0°-60°	884.7	96.9
0°-90°	913.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	913.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	700	700	700	700	700	
5°	694	696	684	684	683	66
15°	661	641	598	570	559	186
25°	583	538	467	418	401	268
35°	477	407	317	256	234	299
45°	360	277	173	99	70	277
55°	228	150	48	14	13	203
65°	92	44	7	4	3	92
75°	0	1	1	1	1	7
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1060678

CATALOG NUMBER: S124RDRP-H1020D935-X4F0-XX-UDD-BVL-B

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	699.5	699.5	699.5	699.5	699.5
2.5°	697.5	699.5	693.5	698.5	699.5
5°	694.5	695.5	684.4	684.4	683.4
7.5°	689.4	687.4	669.2	662.1	661.1
10°	683.4	676.3	650.0	634.8	629.8
12.5°	674.3	661.1	625.8	603.5	597.4
15°	661.1	640.9	598.5	570.2	559.0
17.5°	645.0	618.7	568.1	533.8	522.6
20°	625.8	592.4	534.8	496.4	482.2
22.5°	605.5	567.1	500.4	456.9	442.8
25°	583.3	537.8	467.0	417.5	401.3
27.5°	560.0	506.5	430.6	379.1	357.9
30°	533.8	475.1	391.2	337.6	317.4
32.5°	505.5	440.8	355.8	298.2	274.0
35°	477.1	407.4	317.4	255.8	233.5
37.5°	449.9	376.1	279.0	214.3	193.1
40°	420.5	341.7	243.6	176.9	152.6
42.5°	390.2	308.3	207.2	138.5	112.2
45°	359.9	277.0	172.9	99.1	69.8
47.5°	329.6	243.6	139.5	62.7	37.4
50°	295.2	211.3	106.1	33.4	21.2
52.5°	262.8	181.0	75.8	19.2	16.2
55°	227.5	149.6	48.5	14.2	13.1
57.5°	194.1	119.3	27.3	11.1	10.1
60°	158.7	92.0	15.2	9.1	8.1
62.5°	123.3	66.7	10.1	6.1	5.1
65°	92.0	44.5	7.1	4.0	3.0
67.5°	60.7	25.3	5.1	2.0	2.0
70°	33.4	12.1	3.0	2.0	2.0
72.5°	12.1	4.0	2.0	1.0	1.0
75°	0.0	1.0	1.0	1.0	1.0
77.5°	0.0	0.0	0.0	0.0	1.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1060678  
 CATALOG NUMBER: S124RDRP-H1020D935-X4F0-XX-UDD-BVL-B

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.77	16.02	15.13	16.34	16.65	0.00	0.00	0.00	0.00	0.00
	3H	15.05	16.15	15.43	16.48	16.85	0.00	0.00	0.00	0.00	0.00
	4H	14.97	15.99	15.37	16.35	16.73	0.00	0.00	0.00	0.00	0.00
	6H	14.88	15.82	15.30	16.19	16.59	0.00	0.00	0.00	0.00	0.00
	8H	14.84	15.72	15.27	16.11	16.52	0.00	0.00	0.00	0.00	0.00
	12H	14.79	15.64	15.22	16.02	16.45	0.00	0.00	0.00	0.00	0.00
4H	2H	14.54	15.57	14.95	15.92	16.30	0.00	0.00	0.00	0.00	0.00
	3H	14.83	15.65	15.24	16.06	16.46	0.00	0.00	0.00	0.00	0.00
	4H	14.73	15.47	15.17	15.89	16.33	0.00	0.00	0.00	0.00	0.00
	6H	14.64	15.28	15.11	15.72	16.19	0.00	0.00	0.00	0.00	0.00
	8H	14.58	15.17	15.06	15.62	16.09	0.00	0.00	0.00	0.00	0.00
	12H	14.53	15.05	15.02	15.53	16.01	0.00	0.00	0.00	0.00	0.00
8H	4H	14.58	15.17	15.06	15.62	16.09	0.00	0.00	0.00	0.00	0.00
	6H	14.48	14.95	14.98	15.45	15.93	0.00	0.00	0.00	0.00	0.00
	8H	14.41	14.84	14.93	15.35	15.85	0.00	0.00	0.00	0.00	0.00
	12H	14.36	14.74	14.88	15.23	15.81	0.00	0.00	0.00	0.00	0.00
12H	4H	14.53	15.05	15.02	15.53	16.01	0.00	0.00	0.00	0.00	0.00
	6H	14.41	14.84	14.93	15.35	15.85	0.00	0.00	0.00	0.00	0.00
	8H	14.36	14.74	14.88	15.23	15.81	0.00	0.00	0.00	0.00	0.00