

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1058275

Luminaire Tested: S122RDRP-H290D830-X4F0-XX-UDD-BVL-B

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2024
Report Number: P1058275
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2406-143-21)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDRP-H290D830-X4F0-XX-UDD-BVL-B
Description: DEFINE 2 BLACK REGRESSED DIRECT RECESSED HOUSING WITH BLACK STRAIGHT BLADE
LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 178.3 lumens
Efficiency: N/A
Efficacy: 15.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.8 / 0.88
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1058275

CATALOG NUMBER: S122RDRP-H290D830-X4F0-XX-UDD-BVL-B

Luminous Intensity Polar Plot





TEST NUMBER: P1058275

CATALOG NUMBER: S122RDRP-H290D830-X4F0-XX-UDD-BVL-B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100		
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93	93	93	93		
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86	86	86	86	86	86	86		
3	101	95	90	85	99	93	89	85	91	87	83	88	85	82	86	83	81	79	79	79	79	79	79	79		
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73	73	73	73	73	73	73		
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67	67	67	67	67	67	67		
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62	62	62	62	62	62	62		
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58	58	58	58	58	58	58		
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	56	54	54	54	54	54	54	54		
9	73	63	57	53	72	62	57	52	61	56	52	61	56	52	60	55	52	51	51	51	51	51	51	51		
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47	47	47	47	47	47	47		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3499	3499	3499
5°	3475	3423	3438
10°	3403	3260	3178
15°	3202	2978	2856
20°	2857	2645	2496
25°	2498	2236	2122
30°	2143	1828	1709
35°	1789	1426	1282
40°	1390	1053	821
45°	973	702	355
50°	528	367	126
55°	77	129	90
60°	15	30	59
65°	0	17	35
70°	0	0	22
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 973 cd/sqm



TEST NUMBER: P1058275

CATALOG NUMBER: S122RDRP-H290D830-X4F0-XX-UDD-BVL-B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.4	9.8
10°-20°	43.9	24.6
20°-30°	51.2	28.7
30°-40°	41.0	23.0
40°-50°	20.4	11.4
50°-60°	4.0	2.2
60°-70°	0.4	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	112.5	63.1
0°-40°	153.5	86.1
0°-60°	177.9	99.8
0°-90°	178.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	178.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	190	190	190	190	190	
5°	188	188	185	185	186	18
15°	168	164	156	152	150	47
25°	123	117	110	107	104	56
35°	79	71	63	60	57	49
45°	37	33	27	18	14	29
55°	2	5	4	2	3	5
65°	0	0	0	0	1	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1058275

CATALOG NUMBER: S122RDRP-H290D830-X4F0-XX-UDD-BVL-B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	189.6	189.6	189.6	189.6	189.6
2.5°	188.8	189.6	187.6	189.6	190.0
5°	187.6	187.6	184.8	185.2	185.6
7.5°	185.6	184.8	180.0	179.2	178.4
10°	181.6	180.0	174.0	170.8	169.6
12.5°	176.0	173.6	165.6	162.0	160.0
15°	167.6	164.4	155.9	151.9	149.5
17.5°	156.7	153.9	145.9	141.5	139.1
20°	145.5	141.5	134.7	130.3	127.1
22.5°	134.7	129.5	122.3	119.1	115.9
25°	122.7	116.7	109.8	107.4	104.2
27.5°	112.7	105.0	97.0	95.4	92.6
30°	100.6	93.4	85.8	83.4	80.2
32.5°	90.2	82.2	74.6	71.8	69.0
35°	79.4	71.4	63.3	60.5	56.9
37.5°	69.0	61.3	53.3	48.9	45.7
40°	57.7	51.3	43.7	38.1	34.1
42.5°	47.7	42.1	34.9	27.7	23.7
45°	37.3	32.9	26.9	18.0	13.6
47.5°	27.7	24.5	19.6	10.4	7.2
50°	18.4	17.2	12.8	5.2	4.4
52.5°	10.0	10.8	7.6	3.2	3.6
55°	2.4	4.8	4.0	2.4	2.8
57.5°	0.4	0.8	2.0	2.0	2.0
60°	0.4	0.4	0.8	1.2	1.6
62.5°	0.4	0.0	0.4	0.8	1.2
65°	0.0	0.0	0.4	0.4	0.8
67.5°	0.0	0.0	0.0	0.4	0.4
70°	0.0	0.0	0.0	0.4	0.4
72.5°	0.0	0.0	0.0	0.0	0.4
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1058275
 CATALOG NUMBER: S122RDRP-H290D830-X4F0-XX-UDD-BVL-B

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00