

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1060771

Luminaire Tested: S124RDRP-H1195D940-X4F0-XX-UDD-SVL-B

Issue Date: 8/7/2025

**Test Information**

Test Method: LM-79-2024  
Report Number: P1060771  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2406-143-38)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/7/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S124RDRP-H1195D940-X4F0-XX-UDD-SVL-B  
Description: DEFINE 4 BLACK REGRESSED DIRECT RECESSED HOUSING WITH SILVER STRAIGHT BLADE  
LOUVER WITH DIFFUSER  
HIGH PERFORMANCE LIGHT ENGINE  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1280.3 lumens  
Efficiency: N/A  
Efficacy: 35.1 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 0.87 / 1.02  
Luminous Opening: Rectangular (W 0.31' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 36.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1060771

CATALOG NUMBER: S124RDRP-H1195D940-X4F0-XX-UDD-SVL-B

### Luminous Intensity Polar Plot





TEST NUMBER: P1060771

CATALOG NUMBER: S124RDRP-H1195D940-X4F0-XX-UDD-SVL-B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90					90			
2	104	98	93	88	102	96	91	87	93	89	85	90	86	83	87	84	82	80					80			
3	97	89	82	77	95	87	81	76	84	79	75	82	78	74	79	76	73	71					71			
4	90	81	74	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63					63			
5	84	74	66	61	82	73	66	60	71	65	60	69	63	59	67	62	59	57					57			
6	79	68	60	55	77	67	60	54	65	59	54	63	58	54	62	57	53	51					51			
7	74	62	55	50	72	62	54	49	60	54	49	59	53	49	58	52	48	47					47			
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	54	48	44	43					43			
9	65	53	46	41	64	53	46	41	52	46	41	51	45	41	50	45	41	39					39			
10	62	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36					36			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7478	7478	7478
5°	7453	7358	7347
10°	7422	7101	6930
15°	7316	6716	6379
20°	7129	6276	5783
25°	6938	5729	5090
30°	6652	5132	4390
35°	6364	4538	3626
40°	6035	3864	2750
45°	5644	3158	1847
50°	5162	2393	1147
55°	4535	1579	973
60°	3749	970	801
65°	2716	748	648
70°	1478	554	493
75°	326	406	449
80°	243	302	362
85°	237	237	366

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 5644 cd/sqm



TEST NUMBER: P1060771

CATALOG NUMBER: S124RDRP-H1195D940-X4F0-XX-UDD-SVL-B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	80.4	6.3
10°-20°	213.7	16.7
20°-30°	283.1	22.1
30°-40°	280.9	21.9
40°-50°	216.2	16.9
50°-60°	128.9	10.1
60°-70°	58.6	4.6
70°-80°	15.2	1.2
80°-90°	3.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	577.2	45.1
0°-40°	858.1	67.0
0°-60°	1203.2	94.0
0°-90°	1280.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1280.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	868	868	868	868	868	
5°	862	864	851	851	850	82
15°	821	800	753	728	716	231
25°	730	678	603	553	536	335
35°	605	530	432	366	345	378
45°	464	373	259	181	152	357
55°	302	215	105	66	65	269
65°	133	80	37	32	32	134
75°	10	12	12	14	14	21
85°	2	2	2	4	4	3
90°	0	0	0	0	0	



TEST NUMBER: P1060771

CATALOG NUMBER: S124RDRP-H1195D940-X4F0-XX-UDD-SVL-B

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	868.4	868.4	868.4	868.4	868.4
2.5°	867.1	868.4	861.0	867.1	869.6
5°	862.2	863.5	851.2	851.2	850.0
7.5°	856.1	853.7	834.1	826.8	824.3
10°	848.8	840.2	812.1	797.4	792.5
12.5°	836.6	823.1	785.2	764.4	755.8
15°	820.7	799.9	753.4	727.7	715.5
17.5°	801.1	775.4	720.4	687.3	673.9
20°	777.9	743.6	684.9	643.3	631.1
22.5°	755.8	713.0	645.8	598.1	584.6
25°	730.2	677.6	603.0	552.8	535.7
27.5°	699.6	643.3	560.2	508.8	491.7
30°	669.0	606.6	516.1	462.3	441.5
32.5°	637.2	568.7	475.8	414.6	395.0
35°	605.4	529.6	431.7	365.7	344.9
37.5°	571.2	490.4	387.7	319.2	296.0
40°	536.9	452.5	343.7	274.0	244.6
42.5°	501.4	413.4	300.9	227.5	198.1
45°	463.5	373.0	259.3	181.0	151.7
47.5°	425.6	335.1	217.7	135.8	108.9
50°	385.3	294.8	178.6	99.1	85.6
52.5°	344.9	255.6	139.4	77.1	73.4
55°	302.1	215.3	105.2	66.0	64.8
57.5°	258.1	178.6	75.8	57.5	55.0
60°	217.7	144.3	56.3	48.9	46.5
62.5°	176.1	108.9	46.5	40.4	37.9
65°	133.3	79.5	36.7	31.8	31.8
67.5°	96.6	53.8	29.4	25.7	24.5
70°	58.7	33.0	22.0	20.8	19.6
72.5°	29.4	19.6	17.1	15.9	15.9
75°	9.8	12.2	12.2	13.5	13.5
77.5°	7.3	8.6	8.6	9.8	9.8
80°	4.9	6.1	6.1	7.3	7.3
82.5°	3.7	3.7	4.9	4.9	6.1
85°	2.4	2.4	2.4	3.7	3.7
87.5°	1.2	1.2	1.2	2.4	2.4
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1060771

CATALOG NUMBER: S124RDRP-H1195D940-X4F0-XX-UDD-SVL-B

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.11	17.44	16.47	17.76	18.07	7.66	8.99	8.02	9.31	9.62
	3H	16.62	17.80	17.00	18.13	18.49	8.48	9.66	8.86	9.99	10.35
	4H	16.58	17.68	16.99	18.03	18.42	8.76	9.86	9.16	10.21	10.59
	6H	16.52	17.53	16.93	17.90	18.29	8.93	9.94	9.35	10.31	10.70
	8H	16.48	17.44	16.91	17.83	18.23	9.00	9.95	9.43	10.34	10.75
	12H	16.44	17.36	16.88	17.74	18.17	9.04	9.95	9.47	10.34	10.77
4H	2H	15.95	17.05	16.35	17.40	17.78	8.10	9.20	8.50	9.55	9.93
	3H	16.51	17.40	16.92	17.80	18.21	9.07	9.96	9.48	10.36	10.77
	4H	16.47	17.27	16.91	17.69	18.13	9.43	10.23	9.87	10.65	11.09
	6H	16.42	17.11	16.88	17.55	18.02	9.68	10.37	10.14	10.81	11.28
	8H	16.38	17.01	16.84	17.46	17.93	9.77	10.41	10.24	10.86	11.33
	12H	16.34	16.90	16.82	17.38	17.86	9.85	10.41	10.33	10.89	11.37
8H	4H	16.36	17.00	16.83	17.45	17.92	9.52	10.16	9.99	10.61	11.08
	6H	16.30	16.82	16.81	17.32	17.80	9.83	10.35	10.33	10.85	11.33
	8H	16.26	16.72	16.78	17.24	17.73	9.96	10.43	10.48	10.94	11.44
	12H	16.22	16.64	16.74	17.13	17.70	10.10	10.51	10.61	11.01	11.58
12H	4H	16.32	16.89	16.81	17.37	17.84	9.49	10.06	9.98	10.54	11.02
	6H	16.25	16.72	16.77	17.23	17.72	9.81	10.28	10.33	10.79	11.29
	8H	16.22	16.63	16.74	17.13	17.70	9.98	10.39	10.49	10.89	11.46