

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1058281

Luminaire Tested: S122RDRP-H290D830-X4F0-XX-UDD-WVL-B

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2024
Report Number: P1058281
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2406-143-19)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDRP-H290D830-X4F0-XX-UDD-WVL-B
Description: DEFINE 2 BLACK REGRESSED DIRECT RECESSED HOUSING WITH WHITE STRAIGHT BLADE
LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 382.3 lumens
Efficiency: N/A
Efficacy: 32.7 lumens/watt
Spacing Criteria (0/90/45): 1 / 0.92 / 1.02
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1058281

CATALOG NUMBER: S122RDRP-H290D830-X4F0-XX-UDD-WVL-B

Luminous Intensity Polar Plot



TEST NUMBER: P1058281

CATALOG NUMBER: S122RDRP-H290D830-X4F0-XX-UDD-WVL-B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77					77			
3	95	87	80	74	93	85	79	74	82	77	73	80	75	71	77	73	70	68					68			
4	89	79	71	65	87	77	70	65	75	69	64	73	68	63	71	66	63	61					61			
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54					54			
6	77	66	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49					49			
7	72	60	53	47	71	60	52	47	58	52	47	57	51	47	56	50	46	44					44			
8	68	56	48	43	66	55	48	43	54	47	43	53	47	43	52	46	42	41					41			
9	64	52	45	40	63	51	44	39	50	44	39	49	43	39	48	43	39	37					37			
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34					34			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4646	4646	4646
5°	4620	4553	4583
10°	4536	4379	4341
15°	4373	4144	4059
20°	4047	3841	3755
25°	3714	3469	3404
30°	3392	3092	3058
35°	3070	2737	2674
40°	2734	2385	2259
45°	2354	2051	1811
50°	1946	1725	1519
55°	1406	1432	1367
60°	1170	1229	1244
65°	1000	1070	1140
70°	820	950	1036
75°	684	799	941
80°	510	638	850
85°	169	339	762

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2354 cd/sqm

TEST NUMBER: P1058281

CATALOG NUMBER: S122RDRP-H290D830-X4F0-XX-UDD-WVL-B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	23.3	6.1
10°-20°	61.3	16.0
20°-30°	79.3	20.7
30°-40°	77.8	20.3
40°-50°	61.3	16.0
50°-60°	40.2	10.5
60°-70°	24.5	6.4
70°-80°	12.2	3.2
80°-90°	2.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	163.9	42.9
0°-40°	241.7	63.2
0°-60°	343.1	89.7
0°-90°	382.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	382.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	252	252	252	252	252	
5°	249	249	246	247	247	24
15°	229	226	217	214	212	64
25°	182	176	170	170	167	84
35°	136	129	122	121	119	85
45°	90	85	79	73	69	70
55°	44	46	44	43	42	42
65°	23	23	24	26	26	23
75°	10	10	11	13	13	10
85°	1	1	2	3	4	2
90°	0	0	0	0	0	



TEST NUMBER: P1058281

CATALOG NUMBER: S122RDRP-H290D830-X4F0-XX-UDD-WVL-B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	251.8	251.8	251.8	251.8	251.8
2.5°	251.0	251.4	249.0	251.4	252.2
5°	249.4	249.4	245.8	247.4	247.4
7.5°	246.6	246.2	240.5	240.5	240.1
10°	242.1	240.5	233.7	232.5	231.7
12.5°	236.5	233.7	225.7	223.7	222.5
15°	228.9	225.7	216.9	214.1	212.5
17.5°	217.7	214.5	206.9	203.7	202.1
20°	206.1	201.3	195.6	192.8	191.2
22.5°	194.0	188.4	183.2	181.2	179.6
25°	182.4	176.4	170.4	169.6	167.2
27.5°	171.2	164.0	158.0	157.6	155.6
30°	159.2	151.5	145.1	145.5	143.5
32.5°	147.9	140.7	133.1	133.5	131.1
35°	136.3	128.7	121.5	121.1	118.7
37.5°	124.3	117.1	110.2	108.6	106.2
40°	113.5	106.2	99.0	96.2	93.8
42.5°	101.8	95.4	89.0	84.6	81.4
45°	90.2	84.6	78.6	73.0	69.4
47.5°	79.0	74.6	69.4	62.5	60.1
50°	67.8	64.5	60.1	54.1	52.9
52.5°	56.1	54.9	52.1	48.1	47.7
55°	43.7	46.1	44.5	42.9	42.5
57.5°	36.9	37.3	38.5	38.1	38.1
60°	31.7	31.7	33.3	33.7	33.7
62.5°	26.9	27.3	28.9	29.7	29.7
65°	22.9	23.3	24.5	25.7	26.1
67.5°	18.8	19.6	20.8	22.0	22.5
70°	15.2	16.0	17.6	18.8	19.2
72.5°	12.4	12.8	14.4	15.6	16.0
75°	9.6	10.0	11.2	12.8	13.2
77.5°	6.8	7.6	8.8	10.0	10.8
80°	4.8	5.2	6.0	7.6	8.0
82.5°	2.8	3.2	4.0	5.2	5.6
85°	0.8	1.2	1.6	2.8	3.6
87.5°	0.0	0.0	0.0	0.8	1.6
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1058281
 CATALOG NUMBER: S122RDRP-H290D830-X4F0-XX-UDD-WVL-B

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.46	12.86	11.83	13.17	13.49	11.64	13.04	12.01	13.35	13.67
	3H	12.59	13.83	12.97	14.16	14.53	13.10	14.34	13.48	14.67	15.04
	4H	12.94	14.10	13.34	14.45	14.83	13.64	14.80	14.04	15.15	15.53
	6H	13.12	14.19	13.54	14.56	14.96	14.05	15.12	14.46	15.49	15.88
	8H	13.15	14.17	13.58	14.56	14.96	14.18	15.19	14.60	15.58	15.99
	12H	13.13	14.11	13.57	14.49	14.92	14.26	15.23	14.69	15.61	16.04
4H	2H	11.92	13.09	12.32	13.44	13.82	12.07	13.23	12.47	13.58	13.96
	3H	13.25	14.21	13.67	14.61	15.02	13.74	14.69	14.15	15.10	15.50
	4H	13.70	14.55	14.13	14.97	15.41	14.40	15.26	14.83	15.68	16.12
	6H	13.97	14.71	14.43	15.16	15.62	14.93	15.67	15.39	16.12	16.58
	8H	14.01	14.70	14.48	15.15	15.62	15.10	15.79	15.57	16.24	16.71
	12H	14.01	14.62	14.49	15.10	15.58	15.22	15.84	15.70	16.32	16.79
8H	4H	13.91	14.60	14.38	15.05	15.52	14.55	15.24	15.01	15.69	16.16
	6H	14.25	14.82	14.75	15.32	15.80	15.18	15.74	15.68	16.24	16.72
	8H	14.33	14.84	14.85	15.36	15.85	15.41	15.92	15.93	16.43	16.92
	12H	14.35	14.80	14.86	15.29	15.86	15.59	16.04	16.11	16.54	17.11
12H	4H	13.92	14.54	14.41	15.02	15.49	14.53	15.15	15.02	15.63	16.10
	6H	14.28	14.79	14.80	15.30	15.79	15.17	15.68	15.69	16.19	16.68
	8H	14.40	14.85	14.91	15.34	15.91	15.44	15.89	15.96	16.39	16.96