

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1061013

Luminaire Tested: S124RDRP-H795D940-X4F0-XX-UDD-BVL-W

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2024
Report Number: P1061013
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2406-143-75)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDRP-H795D940-X4F0-XX-UDD-BVL-W
Description: DEFINE 4 WHITE REGRESSED DIRECT RECESSED HOUSING WITH BLACK STRAIGHT BLADE
LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 872.9 lumens
Efficiency: N/A
Efficacy: 37.1 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 1.11 / 0.96
Luminous Opening: Rectangular (W 0.31' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 23.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1061013

CATALOG NUMBER: S124RDRP-H795D940-X4F0-XX-UDD-BVL-W

Luminous Intensity Polar Plot





TEST NUMBER: P1061013

CATALOG NUMBER: S124RDRP-H795D940-X4F0-XX-UDD-BVL-W

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90
2	105	98	93	89	102	97	92	88	93	89	86	90	87	84	87	85	82	81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	75	81	77	74	72
4	91	82	75	70	89	81	75	70	79	73	69	76	72	68	74	70	67	65
5	86	75	68	63	84	74	68	63	72	67	62	71	66	62	69	65	61	59
6	80	70	62	57	79	69	62	57	67	61	56	66	60	56	64	59	56	54
7	75	64	57	52	74	64	57	52	62	56	52	61	55	51	60	55	51	49
8	71	60	53	48	70	59	52	48	58	52	48	57	51	47	56	51	47	45
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42
10	63	52	45	41	62	52	45	41	51	45	41	50	44	41	49	44	40	39

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5964	5964	5964
5°	5762	5846	5958
10°	5309	5559	5893
15°	4769	5167	5761
20°	4157	4700	5564
25°	3507	4171	5322
30°	2829	3604	5043
35°	2094	3016	4760
40°	1297	2403	4477
45°	515	1752	4217
50°	229	1100	3833
55°	183	573	3355
60°	126	434	2675
65°	84	430	1838
70°	83	388	859
75°	110	379	379
80°	164	441	441
85°	326	879	642

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 4217 cd/sqm



TEST NUMBER: P1061013

CATALOG NUMBER: S124RDRP-H795D940-X4F0-XX-UDD-BVL-W

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.5	7.3
10°-20°	164.0	18.8
20°-30°	207.0	23.7
30°-40°	189.9	21.8
40°-50°	129.3	14.8
50°-60°	70.4	8.1
60°-70°	30.5	3.5
70°-80°	11.1	1.3
80°-90°	7.1	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	434.5	49.8
0°-40°	624.4	71.5
0°-60°	824.1	94.4
0°-90°	872.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	872.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	693	693	693	693	693	
5°	667	676	676	684	689	62
15°	535	554	580	621	646	149
25°	369	395	439	509	560	169
35°	199	228	287	378	453	123
45°	42	71	144	255	346	39
55°	12	13	38	141	224	11
65°	4	6	21	44	90	5
75°	3	11	11	11	11	3
85°	3	7	9	9	6	3
90°	0	0	0	0	0	



TEST NUMBER: P1061013

CATALOG NUMBER: S124RDRP-H795D940-X4F0-XX-UDD-BVL-W

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	692.6	692.6	692.6	692.6	692.6
2.5°	684.5	692.6	686.9	688.5	688.5
5°	666.6	675.5	676.3	683.6	689.3
7.5°	639.7	652.7	659.3	673.9	683.6
10°	607.2	622.7	635.7	660.9	673.9
12.5°	572.3	590.2	609.7	643.0	661.7
15°	534.9	553.6	579.6	621.0	646.2
17.5°	493.4	516.2	547.9	597.5	628.4
20°	453.6	476.4	512.9	569.0	607.2
22.5°	412.1	435.7	476.4	538.9	584.5
25°	369.1	395.1	439.0	508.9	560.1
27.5°	326.8	354.4	400.8	477.2	534.1
30°	284.5	312.1	362.5	444.6	507.2
32.5°	241.4	269.9	324.3	410.5	479.6
35°	199.2	228.4	286.9	378.0	452.8
37.5°	156.1	187.0	249.6	346.3	426.0
40°	115.4	146.3	213.8	314.6	398.3
42.5°	77.2	108.1	177.2	283.7	372.3
45°	42.3	70.7	143.9	255.2	346.3
47.5°	22.8	39.0	111.4	227.6	317.0
50°	17.1	21.1	82.1	198.3	286.1
52.5°	14.6	16.3	56.9	167.5	255.2
55°	12.2	13.0	38.2	140.6	223.5
57.5°	9.8	10.6	28.5	113.8	189.4
60°	7.3	8.9	25.2	87.8	155.3
62.5°	5.7	7.3	23.6	64.2	122.7
65°	4.1	5.7	21.1	43.9	90.2
67.5°	4.1	6.5	17.9	28.5	61.0
70°	3.3	8.9	15.4	18.7	34.1
72.5°	3.3	9.8	13.0	13.0	13.0
75°	3.3	10.6	11.4	11.4	11.4
77.5°	3.3	9.8	10.6	9.8	9.8
80°	3.3	8.9	8.9	8.9	8.9
82.5°	3.3	8.1	8.9	8.9	7.3
85°	3.3	7.3	8.9	8.9	6.5
87.5°	2.4	7.3	8.1	8.1	4.9
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1061013
 CATALOG NUMBER: S124RDRP-H795D940-X4F0-XX-UDD-BVL-W

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	14.61	15.89	14.98	16.20	16.52
	3H	0.00	0.00	0.00	0.15	0.51	14.99	16.12	15.37	16.45	16.82
	4H	0.00	0.97	0.32	1.32	1.70	14.97	16.02	15.37	16.37	16.75
	6H	1.11	2.07	1.52	2.44	2.84	14.96	15.92	15.37	16.29	16.69
	8H	1.70	2.61	2.13	3.01	3.41	14.96	15.87	15.39	16.26	16.67
	12H	2.38	3.25	2.81	3.63	4.06	14.97	15.84	15.40	16.23	16.66
4H	2H	0.86	1.91	1.26	2.26	2.65	14.42	15.48	14.83	15.83	16.21
	3H	2.44	3.30	2.85	3.70	4.11	14.84	15.70	15.26	16.11	16.51
	4H	3.75	4.51	4.18	4.93	5.38	14.84	15.61	15.28	16.03	16.47
	6H	4.88	5.54	5.34	5.99	6.45	14.88	15.54	15.35	15.99	16.46
	8H	5.39	6.01	5.86	6.45	6.93	14.91	15.53	15.38	15.97	16.45
	12H	5.94	6.49	6.43	6.97	7.45	14.97	15.52	15.46	16.00	16.48
8H	4H	4.83	5.45	5.30	5.90	6.37	14.75	15.37	15.22	15.82	16.29
	6H	6.37	6.87	6.87	7.37	7.85	14.83	15.34	15.33	15.83	16.31
	8H	7.18	7.63	7.70	8.15	8.64	14.91	15.37	15.44	15.88	16.38
	12H	8.01	8.41	8.53	8.91	9.48	15.08	15.48	15.60	15.98	16.55
12H	4H	5.02	5.56	5.51	6.05	6.52	14.72	15.26	15.20	15.74	16.22
	6H	6.72	7.18	7.24	7.69	8.19	14.80	15.26	15.33	15.77	16.27
	8H	7.73	8.13	8.25	8.63	9.20	14.94	15.34	15.45	15.84	16.41