

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1058325

Luminaire Tested: S122RDRP-H290D930-X4F0-XX-UDD-SVL-W

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2024
Report Number: P1058325
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2406-143-56)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDRP-H290D930-X4F0-XX-UDD-SVL-W
Description: DEFINE 2 WHITE REGRESSED DIRECT RECESSED HOUSING WITH SILVER STRAIGHT BLADE
LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 283.5 lumens
Efficiency: N/A
Efficacy: 24.2 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.98 / 0.95
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1058325

CATALOG NUMBER: S122RDRP-H290D930-X4F0-XX-UDD-SVL-W

Luminous Intensity Polar Plot





TEST NUMBER: P1058325

CATALOG NUMBER: S122RDRP-H290D930-X4F0-XX-UDD-SVL-W

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	89
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76	83	78	75	80	77	74	72
4	91	82	75	70	89	81	74	69	78	73	68	76	71	68	74	70	67	65
5	86	75	68	63	84	74	68	63	72	67	62	71	65	61	69	64	61	59
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54
7	76	65	57	52	74	64	57	52	62	56	52	61	56	52	60	55	51	50
8	71	60	53	48	70	59	53	48	58	52	48	57	52	48	56	51	47	46
9	67	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	42
10	64	53	46	41	63	52	46	41	51	45	41	50	45	41	50	45	41	39

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4312	4312	4312
5°	4168	4232	4297
10°	3892	4021	4203
15°	3549	3735	4040
20°	3158	3389	3745
25°	2736	2977	3400
30°	2295	2553	3064
35°	1807	2113	2714
40°	1289	1705	2267
45°	762	1349	1759
50°	548	976	1197
55°	457	705	605
60°	373	565	513
65°	301	502	472
70°	264	486	448
75°	250	492	449
80°	255	595	478
85°	360	953	593

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 1759 cd/sqm



TEST NUMBER: P1058325

CATALOG NUMBER: S122RDRP-H290D930-X4F0-XX-UDD-SVL-W

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.4	7.6
10°-20°	55.1	19.4
20°-30°	67.9	24.0
30°-40°	60.4	21.3
40°-50°	38.6	13.6
50°-60°	18.5	6.5
60°-70°	10.9	3.8
70°-80°	7.0	2.5
80°-90°	3.7	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	144.4	50.9
0°-40°	204.9	72.3
0°-60°	262.0	92.4
0°-90°	283.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	283.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	234	234	234	234	234	
5°	225	229	228	230	232	21
15°	186	190	196	204	212	52
25°	134	140	146	157	167	62
35°	80	86	94	108	120	50
45°	29	38	52	60	67	24
55°	14	18	22	21	19	13
65°	7	12	12	10	11	7
75°	4	8	7	7	6	4
85°	2	4	4	4	3	2
90°	0	0	0	0	0	



TEST NUMBER: P1058325

CATALOG NUMBER: S122RDRP-H290D930-X4F0-XX-UDD-SVL-W

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	233.7	233.7	233.7	233.7	233.7
2.5°	230.6	234.4	232.0	232.0	232.7
5°	225.0	229.2	228.5	229.9	232.0
7.5°	217.0	221.6	222.3	226.1	229.2
10°	207.7	212.5	214.6	220.2	224.3
12.5°	197.2	202.1	205.9	212.9	218.8
15°	185.8	190.3	195.5	204.5	211.5
17.5°	173.3	179.2	184.4	193.8	201.8
20°	160.8	166.3	172.6	181.6	190.7
22.5°	147.9	153.1	159.4	168.8	179.2
25°	134.4	139.6	146.2	156.6	167.0
27.5°	121.2	126.4	132.7	144.1	155.2
30°	107.7	112.9	119.8	131.6	143.8
32.5°	94.1	99.7	106.6	119.5	132.3
35°	80.2	86.5	93.8	108.0	120.5
37.5°	66.7	72.9	82.0	95.8	107.7
40°	53.5	60.8	70.8	83.3	94.1
42.5°	40.6	48.6	61.1	71.2	80.6
45°	29.2	37.9	51.7	60.1	67.4
47.5°	22.2	28.5	42.7	49.3	54.5
50°	19.1	22.9	34.0	38.9	41.7
52.5°	16.7	20.1	27.1	29.5	29.5
55°	14.2	18.4	21.9	21.2	18.8
57.5°	12.2	16.7	18.1	15.3	16.0
60°	10.1	15.3	15.3	13.5	13.9
62.5°	8.3	14.2	13.2	11.8	12.2
65°	6.9	12.5	11.5	10.4	10.8
67.5°	5.6	11.1	10.1	9.4	9.4
70°	4.9	10.1	9.0	8.3	8.3
72.5°	4.2	8.7	8.0	7.3	7.3
75°	3.5	7.6	6.9	6.6	6.3
77.5°	3.1	6.6	6.3	5.6	5.2
80°	2.4	5.6	5.6	5.2	4.5
82.5°	2.1	4.9	4.9	4.5	3.8
85°	1.7	4.2	4.5	3.8	2.8
87.5°	1.4	3.8	3.8	3.1	2.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1058325

CATALOG NUMBER: S122RDRP-H290D930-X4F0-XX-UDD-SVL-W

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.76	8.04	7.13	8.35	8.67	6.55	7.82	6.91	8.14	8.45
	3H	8.00	9.13	8.38	9.46	9.83	8.14	9.27	8.52	9.60	9.97
	4H	8.45	9.51	8.85	9.86	10.24	8.86	9.92	9.26	10.27	10.65
	6H	8.82	9.80	9.24	10.17	10.56	9.51	10.48	9.92	10.85	11.25
	8H	8.98	9.90	9.41	10.29	10.70	9.83	10.75	10.26	11.15	11.55
	12H	9.13	10.02	9.57	10.40	10.83	10.13	11.01	10.56	11.40	11.83
4H	2H	7.31	8.37	7.72	8.72	9.11	7.14	8.20	7.55	8.55	8.94
	3H	9.01	9.88	9.42	10.28	10.69	8.97	9.84	9.39	10.25	10.65
	4H	9.80	10.58	10.23	11.00	11.44	9.85	10.63	10.29	11.05	11.50
	6H	10.44	11.12	10.90	11.56	12.03	10.69	11.37	11.16	11.82	12.28
	8H	10.69	11.32	11.16	11.77	12.24	11.11	11.75	11.58	12.19	12.67
	12H	10.94	11.50	11.42	11.98	12.45	11.52	12.08	12.00	12.56	13.03
8H	4H	10.22	10.85	10.68	11.30	11.77	10.27	10.90	10.74	11.35	11.82
	6H	11.20	11.72	11.70	12.21	12.69	11.35	11.87	11.86	12.37	12.85
	8H	11.69	12.16	12.21	12.68	13.17	11.94	12.41	12.46	12.92	13.42
	12H	12.20	12.61	12.71	13.10	13.67	12.54	12.95	13.06	13.45	14.02
12H	4H	10.28	10.84	10.77	11.33	11.80	10.35	10.91	10.83	11.39	11.86
	6H	11.37	11.83	11.89	12.35	12.84	11.52	11.99	12.04	12.50	13.00
	8H	12.01	12.42	12.52	12.92	13.49	12.23	12.64	12.74	13.14	13.71