

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1060983

Luminaire Tested: S124RDRP-H795D850-X4F0-XX-UDD-WVL-W

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2024
Report Number: P1060983
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2406-143-73)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDRP-H795D850-X4F0-XX-UDD-WVL-W
Description: DEFINE 4 WHITE REGRESSED DIRECT RECESSED HOUSING WITH WHITE STRAIGHT BLADE LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 5000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2094.9 lumens
Efficiency: N/A
Efficacy: 89.1 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 1.15 / 1.11
Luminous Opening: Rectangular (W 0.31' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 23.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1060983

CATALOG NUMBER: S124RDRP-H795D850-X4F0-XX-UDD-WVL-W

Luminous Intensity Polar Plot





TEST NUMBER: P1060983

CATALOG NUMBER: S124RDRP-H795D850-X4F0-XX-UDD-WVL-W

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	80	77	75
3	94	84	77	71	91	83	76	70	80	74	69	77	72	68	75	70	67	65
4	86	76	68	62	84	74	67	61	72	66	60	70	64	60	68	63	59	57
5	80	68	60	54	78	67	60	54	65	59	53	63	58	53	62	56	52	50
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37
9	61	49	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33
10	58	45	38	33	56	45	38	33	44	37	33	43	37	32	42	36	32	31

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9831	9831	9831
5°	9546	9659	9816
10°	9064	9329	9753
15°	8521	8935	9638
20°	7926	8463	9379
25°	7267	7900	9072
30°	6550	7303	8730
35°	5799	6681	8401
40°	4929	6031	8063
45°	4036	5328	7751
50°	3533	4575	7296
55°	3246	3944	6750
60°	3010	3550	5950
65°	2820	3335	4982
70°	2646	3051	3739
75°	2489	2791	2722
80°	2306	2554	2306
85°	2095	2500	1996

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 7751 cd/sqm

TEST NUMBER: P1060983

CATALOG NUMBER: S124RDRP-H795D850-X4F0-XX-UDD-WVL-W

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.5	5.0
10°-20°	283.9	13.6
20°-30°	388.0	18.5
30°-40°	407.8	19.5
40°-50°	353.9	16.9
50°-60°	267.0	12.7
60°-70°	173.0	8.3
70°-80°	88.8	4.2
80°-90°	26.9	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	777.4	37.1
0°-40°	1185.3	56.6
0°-60°	1806.2	86.2
0°-90°	2094.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2094.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1142	1142	1142	1142	1142	
5°	1104	1120	1117	1126	1136	103
15°	956	979	1002	1048	1081	268
25°	765	792	832	895	955	351
35°	552	582	636	720	799	343
45°	331	363	438	547	636	261
55°	216	222	263	373	450	195
65°	138	141	164	198	244	138
75°	75	84	84	85	82	79
85°	21	26	25	24	20	24
90°	0	0	0	0	0	

TEST NUMBER: P1060983

CATALOG NUMBER: S124RDRP-H795D850-X4F0-XX-UDD-WVL-W

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1141.7	1141.7	1141.7	1141.7	1141.7
2.5°	1128.6	1142.7	1132.6	1134.6	1135.6
5°	1104.3	1119.5	1117.4	1126.5	1135.6
7.5°	1073.0	1091.2	1095.2	1113.4	1128.6
10°	1036.6	1056.8	1066.9	1096.2	1115.4
12.5°	998.2	1018.4	1036.6	1074.0	1101.3
15°	955.8	979.0	1002.3	1047.7	1081.1
17.5°	911.3	935.6	964.9	1014.4	1053.8
20°	864.9	889.1	923.5	977.0	1023.5
22.5°	815.3	842.6	879.0	936.6	991.1
25°	764.8	792.1	831.5	895.2	954.8
27.5°	712.3	740.6	783.0	853.7	917.4
30°	658.7	689.1	734.5	809.3	878.0
32.5°	604.2	636.5	685.0	764.8	839.6
35°	551.6	582.0	635.5	720.4	799.2
37.5°	497.1	527.4	585.0	676.9	758.8
40°	438.5	471.8	536.5	631.5	717.3
42.5°	383.9	417.3	487.0	588.0	677.9
45°	331.4	362.7	437.5	546.6	636.5
47.5°	291.0	313.2	388.0	506.2	592.1
50°	263.7	273.8	341.5	461.7	544.6
52.5°	239.5	247.5	299.1	417.3	498.1
55°	216.2	222.3	262.7	372.8	449.6
57.5°	196.0	199.0	230.4	328.4	397.1
60°	174.8	178.8	206.1	282.9	345.5
62.5°	157.6	159.6	184.9	239.5	294.0
65°	138.4	141.4	163.7	198.0	244.5
67.5°	121.2	126.3	141.4	161.7	193.0
70°	105.1	112.1	121.2	131.3	148.5
72.5°	89.9	98.0	103.1	107.1	104.1
75°	74.8	83.9	83.9	84.9	81.8
77.5°	60.6	68.7	67.7	66.7	62.6
80°	46.5	53.5	51.5	50.5	46.5
82.5°	34.4	39.4	37.4	36.4	31.3
85°	21.2	26.3	25.3	24.2	20.2
87.5°	10.1	15.2	14.1	13.1	9.1
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1060983

CATALOG NUMBER: S124RDRP-H795D850-X4F0-XX-UDD-WVL-W

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.44	15.93	14.81	16.24	16.56	18.18	19.67	18.55	19.98	20.30
	3H	16.11	17.44	16.49	17.77	18.13	19.31	20.64	19.69	20.97	21.33
	4H	16.78	18.03	17.18	18.38	18.75	19.60	20.85	20.00	21.20	21.58
	6H	17.29	18.44	17.70	18.81	19.20	19.80	20.96	20.22	21.32	21.72
	8H	17.46	18.56	17.89	18.95	19.35	19.86	20.96	20.29	21.35	21.75
	12H	17.58	18.63	18.01	19.01	19.44	19.89	20.94	20.32	21.32	21.75
4H	2H	15.24	16.48	15.64	16.83	17.21	18.35	19.60	18.75	19.95	20.33
	3H	17.11	18.14	17.52	18.54	18.94	19.68	20.71	20.09	21.11	21.52
	4H	17.91	18.84	18.34	19.26	19.70	20.10	21.03	20.53	21.44	21.88
	6H	18.55	19.36	19.01	19.81	20.27	20.42	21.23	20.87	21.67	22.13
	8H	18.78	19.54	19.24	19.98	20.45	20.51	21.27	20.98	21.71	22.18
	12H	18.94	19.62	19.43	20.10	20.57	20.58	21.26	21.07	21.74	22.21
8H	4H	18.26	19.02	18.72	19.46	19.93	20.23	20.99	20.69	21.43	21.90
	6H	19.05	19.67	19.55	20.17	20.64	20.65	21.27	21.14	21.76	22.24
	8H	19.37	19.93	19.88	20.44	20.93	20.80	21.37	21.32	21.88	22.36
	12H	19.63	20.13	20.14	20.62	21.19	20.94	21.44	21.45	21.93	22.50
12H	4H	18.29	18.97	18.77	19.44	19.92	20.23	20.91	20.72	21.39	21.86
	6H	19.11	19.67	19.63	20.18	20.67	20.67	21.23	21.18	21.74	22.23
	8H	19.50	19.99	20.01	20.49	21.05	20.88	21.37	21.39	21.87	22.43