

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1058446

Luminaire Tested: S122RDRP-H675D835-X4F0-XX-UDD-BVL-B

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2024
Report Number: P1058446
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2406-143-21)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDRP-H675D835-X4F0-XX-UDD-BVL-B
Description: DEFINE 2 BLACK REGRESSED DIRECT RECESSED HOUSING WITH BLACK STRAIGHT BLADE
LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 421.9 lumens
Efficiency: N/A
Efficacy: 18.0 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.8 / 0.88
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 23.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1058446

CATALOG NUMBER: S122RDRP-H675D835-X4F0-XX-UDD-BVL-B

Luminous Intensity Polar Plot





TEST NUMBER: P1058446

CATALOG NUMBER: S122RDRP-H675D835-X4F0-XX-UDD-BVL-B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86
3	101	95	90	85	99	93	89	85	91	87	83	88	85	82	86	83	81	79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	63
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	56	54
9	73	63	57	53	72	62	57	52	61	56	52	61	56	52	60	55	52	51
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8280	8280	8280
5°	8222	8100	8135
10°	8051	7714	7519
15°	7574	7049	6759
20°	6761	6258	5905
25°	5911	5292	5021
30°	5073	4325	4042
35°	4230	3377	3034
40°	3290	2491	1941
45°	2302	1660	843
50°	1252	873	299
55°	183	306	212
60°	33	70	140
65°	0	39	83
70°	0	0	49
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2302 cd/sqm



TEST NUMBER: P1058446

CATALOG NUMBER: S122RDRP-H675D835-X4F0-XX-UDD-BVL-B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.2	9.8
10°-20°	103.9	24.6
20°-30°	121.1	28.7
30°-40°	97.1	23.0
40°-50°	48.2	11.4
50°-60°	9.5	2.3
60°-70°	0.8	0.2
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	266.2	63.1
0°-40°	363.3	86.1
0°-60°	421.0	99.8
0°-90°	421.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	421.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	449	449	449	449	449	
5°	444	444	437	438	439	42
15°	396	389	369	360	354	110
25°	290	276	260	254	247	134
35°	188	169	150	143	135	117
45°	88	78	64	43	32	68
55°	6	11	10	6	7	11
65°	0	0	1	1	2	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1058446

CATALOG NUMBER: S122RDRP-H675D835-X4F0-XX-UDD-BVL-B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	448.7	448.7	448.7	448.7	448.7
2.5°	446.8	448.7	443.9	448.7	449.6
5°	443.9	443.9	437.3	438.3	439.2
7.5°	439.2	437.3	425.9	424.0	422.1
10°	429.7	425.9	411.7	404.1	401.3
12.5°	416.4	410.7	391.8	383.2	378.5
15°	396.5	388.9	369.0	359.5	353.8
17.5°	370.9	364.3	345.3	334.9	329.2
20°	344.3	334.9	318.7	308.3	300.7
22.5°	318.7	306.4	289.3	281.7	274.1
25°	290.3	276.0	259.9	254.2	246.6
27.5°	266.6	248.5	229.6	225.8	219.1
30°	238.1	221.0	203.0	197.3	189.7
32.5°	213.4	194.5	176.4	169.8	163.2
35°	187.8	168.9	149.9	143.2	134.7
37.5°	163.2	145.1	126.2	115.7	108.1
40°	136.6	121.4	103.4	90.1	80.6
42.5°	112.9	99.6	82.5	65.5	56.0
45°	88.2	77.8	63.6	42.7	32.3
47.5°	65.5	57.9	46.5	24.7	17.1
50°	43.6	40.8	30.4	12.3	10.4
52.5°	23.7	25.6	18.0	7.6	8.5
55°	5.7	11.4	9.5	5.7	6.6
57.5°	0.9	1.9	4.7	4.7	4.7
60°	0.9	0.9	1.9	2.8	3.8
62.5°	0.9	0.0	0.9	1.9	2.8
65°	0.0	0.0	0.9	0.9	1.9
67.5°	0.0	0.0	0.0	0.9	0.9
70°	0.0	0.0	0.0	0.9	0.9
72.5°	0.0	0.0	0.0	0.0	0.9
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1058446
 CATALOG NUMBER: S122RDRP-H675D835-X4F0-XX-UDD-BVL-B

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00