

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1058451

Luminaire Tested: S122RDRP-H675D835-X4F0-XX-UDD-SVL-W

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2024
Report Number: P1058451
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2406-143-56)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDRP-H675D835-X4F0-XX-UDD-SVL-W
Description: DEFINE 2 WHITE REGRESSED DIRECT RECESSED HOUSING WITH SILVER STRAIGHT BLADE
LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 775.4 lumens
Efficiency: N/A
Efficacy: 33.0 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.98 / 0.95
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 23.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1058451

CATALOG NUMBER: S122RDRP-H675D835-X4F0-XX-UDD-SVL-W

Luminous Intensity Polar Plot





TEST NUMBER: P1058451

CATALOG NUMBER: S122RDRP-H675D835-X4F0-XX-UDD-SVL-W

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	89
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76	83	78	75	80	77	74	72
4	91	82	75	70	89	81	74	69	78	73	68	76	71	68	74	70	67	65
5	86	75	68	63	84	74	68	63	72	67	62	71	65	61	69	64	61	59
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54
7	76	65	57	52	74	64	57	52	62	56	52	61	56	52	60	55	51	50
8	71	60	53	48	70	59	53	48	58	52	48	57	52	48	56	51	47	46
9	67	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	42
10	64	53	46	41	63	52	46	41	51	45	41	50	45	41	50	45	41	39

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11797	11797	11797
5°	11403	11579	11755
10°	10645	11001	11499
15°	9708	10216	11051
20°	8636	9270	10241
25°	7484	8142	9303
30°	6275	6982	8380
35°	4942	5778	7425
40°	3524	4668	6200
45°	2082	3693	4809
50°	1499	2673	3273
55°	1251	1924	1650
60°	1015	1543	1402
65°	830	1367	1284
70°	718	1333	1230
75°	677	1355	1219
80°	701	1615	1307
85°	995	2604	1609

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 4809 cd/sqm



TEST NUMBER: P1058451

CATALOG NUMBER: S122RDRP-H675D835-X4F0-XX-UDD-SVL-W

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.6	7.6
10°-20°	150.6	19.4
20°-30°	185.8	24.0
30°-40°	165.3	21.3
40°-50°	105.5	13.6
50°-60°	50.7	6.5
60°-70°	29.7	3.8
70°-80°	19.0	2.4
80°-90°	10.1	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	395.1	51.0
0°-40°	560.4	72.3
0°-60°	716.6	92.4
0°-90°	775.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	775.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	639	639	639	639	639	
5°	616	627	625	629	635	57
15°	508	521	535	560	578	142
25°	368	382	400	428	457	168
35°	219	236	256	295	330	136
45°	80	104	142	164	184	67
55°	39	50	60	58	51	35
65°	19	34	31	28	29	19
75°	10	21	19	18	17	10
85°	5	11	12	10	8	5
90°	0	0	0	0	0	



TEST NUMBER: P1058451

CATALOG NUMBER: S122RDRP-H675D835-X4F0-XX-UDD-SVL-W

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	639.3	639.3	639.3	639.3	639.3
2.5°	630.8	641.2	634.6	634.6	636.5
5°	615.6	627.0	625.1	628.9	634.6
7.5°	593.7	606.1	608.0	618.4	627.0
10°	568.1	581.4	587.1	602.3	613.7
12.5°	539.6	552.9	563.3	582.3	598.5
15°	508.2	520.6	534.8	559.5	578.5
17.5°	474.0	490.2	504.4	530.1	551.9
20°	439.8	455.0	472.1	496.8	521.5
22.5°	404.7	418.9	436.0	461.7	490.2
25°	367.6	381.9	399.9	428.4	456.9
27.5°	331.5	345.8	362.9	394.2	424.6
30°	294.5	308.7	327.7	360.0	393.3
32.5°	257.4	272.6	291.6	326.8	361.9
35°	219.4	236.5	256.5	295.4	329.6
37.5°	182.4	199.5	224.2	262.2	294.5
40°	146.3	166.2	193.8	228.0	257.4
42.5°	111.1	133.0	167.2	194.7	220.4
45°	79.8	103.5	141.5	164.3	184.3
47.5°	60.8	77.9	116.8	134.9	149.1
50°	52.2	62.7	93.1	106.4	114.0
52.5°	45.6	55.1	74.1	80.7	80.7
55°	38.9	50.3	59.8	57.9	51.3
57.5°	33.2	45.6	49.4	41.8	43.7
60°	27.5	41.8	41.8	37.0	38.0
62.5°	22.8	38.9	36.1	32.3	33.2
65°	19.0	34.2	31.3	28.5	29.4
67.5°	15.2	30.4	27.5	25.6	25.6
70°	13.3	27.5	24.7	22.8	22.8
72.5°	11.4	23.7	21.8	19.9	19.9
75°	9.5	20.9	19.0	18.0	17.1
77.5°	8.5	18.0	17.1	15.2	14.2
80°	6.6	15.2	15.2	14.2	12.3
82.5°	5.7	13.3	13.3	12.3	10.4
85°	4.7	11.4	12.3	10.4	7.6
87.5°	3.8	10.4	10.4	8.5	5.7
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1058451
 CATALOG NUMBER: S122RDRP-H675D835-X4F0-XX-UDD-SVL-W

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.25	11.52	10.61	11.83	12.15	10.04	11.31	10.40	11.63	11.94
	3H	11.48	12.61	11.86	12.94	13.31	11.63	12.76	12.01	13.09	13.46
	4H	11.93	12.99	12.33	13.34	13.72	12.34	13.40	12.74	13.75	14.13
	6H	12.31	13.28	12.72	13.65	14.04	12.99	13.96	13.40	14.33	14.73
	8H	12.46	13.38	12.89	13.77	14.18	13.32	14.24	13.75	14.63	15.04
	12H	12.62	13.50	13.05	13.88	14.31	13.61	14.50	14.05	14.88	15.31
4H	2H	10.79	11.85	11.20	12.20	12.59	10.63	11.69	11.03	12.04	12.42
	3H	12.49	13.36	12.90	13.76	14.17	12.46	13.33	12.87	13.74	14.14
	4H	13.28	14.06	13.72	14.48	14.93	13.33	14.12	13.77	14.54	14.98
	6H	13.92	14.60	14.39	15.05	15.51	14.18	14.85	14.64	15.30	15.77
	8H	14.17	14.80	14.64	15.25	15.72	14.60	15.23	15.07	15.68	16.15
	12H	14.42	14.98	14.90	15.46	15.93	15.00	15.56	15.48	16.04	16.52
8H	4H	13.70	14.33	14.17	14.78	15.25	13.75	14.38	14.22	14.83	15.30
	6H	14.68	15.19	15.18	15.69	16.17	14.83	15.35	15.34	15.85	16.33
	8H	15.17	15.63	15.69	16.15	16.64	15.42	15.89	15.94	16.41	16.90
	12H	15.67	16.08	16.18	16.58	17.15	16.02	16.44	16.54	16.93	17.50
12H	4H	13.77	14.33	14.25	14.81	15.28	13.83	14.39	14.31	14.87	15.34
	6H	14.84	15.31	15.37	15.83	16.32	15.00	15.47	15.52	15.98	16.47
	8H	15.48	15.89	16.00	16.39	16.96	15.71	16.12	16.22	16.61	17.19