

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1058410

Luminaire Tested: S122RDRP-H485D935-X4F0-XX-UDD-BVL-B

Issue Date: 8/7/2025

**Test Information**

Test Method: LM-79-2024  
Report Number: P1058410  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2406-143-21)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/7/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S122RDRP-H485D935-X4F0-XX-UDD-BVL-B  
Description: DEFINE 2 BLACK REGRESSED DIRECT RECESSED HOUSING WITH BLACK STRAIGHT BLADE LOUVER WITH DIFFUSER  
HIGH PERFORMANCE LIGHT ENGINE  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 259.4 lumens  
Efficiency: N/A  
Efficacy: 14.9 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.8 / 0.88  
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 17.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1058410

CATALOG NUMBER: S122RDRP-H485D935-X4F0-XX-UDD-BVL-B

### Luminous Intensity Polar Plot





TEST NUMBER: P1058410

CATALOG NUMBER: S122RDRP-H485D935-X4F0-XX-UDD-BVL-B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93					93			
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86					86			
3	101	95	90	85	99	93	89	85	91	87	83	88	85	82	86	83	81	79					79			
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73					73			
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67					67			
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62					62			
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58					58			
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	56	54					54			
9	73	63	57	53	72	62	57	52	61	56	52	61	56	52	60	55	52	51					51			
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47					47			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5089	5089	5089
5°	5055	4979	5001
10°	4950	4742	4622
15°	4657	4335	4155
20°	4157	3849	3631
25°	3634	3254	3087
30°	3119	2659	2484
35°	2602	2075	1865
40°	2023	1532	1195
45°	1414	1020	517
50°	769	537	184
55°	113	187	132
60°	22	44	85
65°	0	26	52
70°	0	0	32
75°	0	0	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1414 cd/sqm



TEST NUMBER: P1058410

CATALOG NUMBER: S122RDRP-H485D935-X4F0-XX-UDD-BVL-B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	25.3	9.8
10°-20°	63.9	24.6
20°-30°	74.5	28.7
30°-40°	59.7	23.0
40°-50°	29.6	11.4
50°-60°	5.8	2.3
60°-70°	0.5	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	163.7	63.1
0°-40°	223.3	86.1
0°-60°	258.8	99.8
0°-90°	259.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	259.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	276	276	276	276	276	
5°	273	273	269	269	270	26
15°	244	239	227	221	218	68
25°	178	170	160	156	152	82
35°	116	104	92	88	83	72
45°	54	48	39	26	20	42
55°	4	7	6	4	4	7
65°	0	0	1	1	1	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1058410

CATALOG NUMBER: S122RDRP-H485D935-X4F0-XX-UDD-BVL-B

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	275.8	275.8	275.8	275.8	275.8
2.5°	274.7	275.8	272.9	275.8	276.4
5°	272.9	272.9	268.8	269.4	270.0
7.5°	270.0	268.8	261.9	260.7	259.5
10°	264.2	261.9	253.1	248.4	246.7
12.5°	256.0	252.5	240.9	235.6	232.7
15°	243.8	239.1	226.9	221.0	217.5
17.5°	228.0	223.9	212.3	205.9	202.4
20°	211.7	205.9	196.0	189.5	184.9
22.5°	196.0	188.4	177.9	173.2	168.5
25°	178.5	169.7	159.8	156.3	151.6
27.5°	163.9	152.8	141.1	138.8	134.7
30°	146.4	135.9	124.8	121.3	116.6
32.5°	131.2	119.6	108.5	104.4	100.3
35°	115.5	103.8	92.1	88.1	82.8
37.5°	100.3	89.2	77.6	71.1	66.5
40°	84.0	74.6	63.6	55.4	49.6
42.5°	69.4	61.2	50.7	40.2	34.4
45°	54.2	47.8	39.1	26.2	19.8
47.5°	40.2	35.6	28.6	15.2	10.5
50°	26.8	25.1	18.7	7.6	6.4
52.5°	14.6	15.7	11.1	4.7	5.2
55°	3.5	7.0	5.8	3.5	4.1
57.5°	0.6	1.2	2.9	2.9	2.9
60°	0.6	0.6	1.2	1.7	2.3
62.5°	0.6	0.0	0.6	1.2	1.7
65°	0.0	0.0	0.6	0.6	1.2
67.5°	0.0	0.0	0.0	0.6	0.6
70°	0.0	0.0	0.0	0.6	0.6
72.5°	0.0	0.0	0.0	0.0	0.6
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1058410  
 CATALOG NUMBER: S122RDRP-H485D935-X4F0-XX-UDD-BVL-B

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00