

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1057849

Luminaire Tested: S122RDRP-S1005D935-X4F0-XX-UDD-WVL-B

Issue Date: 8/7/2025

**Test Information**

Test Method: LM-79-2024  
Report Number: P1057849  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2406-143-19)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/7/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S122RDRP-S1005D935-X4F0-XX-UDD-WVL-B  
Description: DEFINE 2 BLACK REGRESSED DIRECT RECESSED HOUSING WITH WHITE STRAIGHT BLADE  
LOUVER WITH DIFFUSER  
CORE LIGHT ENGINE  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1213.2 lumens  
Efficiency: N/A  
Efficacy: 29.0 lumens/watt  
Spacing Criteria (0/90/45): 1 / 0.92 / 1.02  
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 41.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1057849

CATALOG NUMBER: S122RDRP-S1005D935-X4F0-XX-UDD-WVL-B

### Luminous Intensity Polar Plot





TEST NUMBER: P1057849

CATALOG NUMBER: S122RDRP-S1005D935-X4F0-XX-UDD-WVL-B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77
3	95	87	80	74	93	85	79	74	82	77	73	80	75	71	77	73	70	68
4	89	79	71	65	87	77	70	65	75	69	64	73	68	63	71	66	63	61
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54
6	77	66	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49
7	72	60	53	47	71	60	52	47	58	52	47	57	51	47	56	50	46	44
8	68	56	48	43	66	55	48	43	54	47	43	53	47	43	52	46	42	41
9	64	52	45	40	63	51	44	39	50	44	39	49	43	39	48	43	39	37
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14742	14742	14742
5°	14655	14444	14539
10°	14396	13895	13777
15°	13875	13147	12880
20°	12838	12190	11916
25°	11784	11007	10799
30°	10760	9812	9703
35°	9743	8682	8481
40°	8672	7568	7171
45°	7469	6506	5744
50°	6172	5477	4820
55°	4462	4543	4337
60°	3709	3897	3945
65°	3166	3388	3611
70°	2606	3021	3296
75°	2174	2538	2994
80°	1626	2030	2699
85°	529	1080	2414

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7469 cd/sqm

TEST NUMBER: P1057849

CATALOG NUMBER: S122RDRP-S1005D935-X4F0-XX-UDD-WVL-B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	73.8	6.1
10°-20°	194.5	16.0
20°-30°	251.7	20.7
30°-40°	246.8	20.3
40°-50°	194.4	16.0
50°-60°	127.4	10.5
60°-70°	77.6	6.4
70°-80°	38.8	3.2
80°-90°	8.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	520.0	42.9
0°-40°	766.8	63.2
0°-60°	1088.6	89.7
0°-90°	1213.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1213.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	799	799	799	799	799	
5°	791	791	780	785	785	75
15°	726	716	688	679	674	202
25°	579	560	541	538	530	266
35°	432	408	385	384	376	270
45°	286	268	249	232	220	221
55°	139	146	141	136	135	132
65°	72	74	78	81	83	72
75°	30	32	36	41	42	32
85°	2	4	5	9	11	5
90°	0	0	0	0	0	



TEST NUMBER: P1057849

CATALOG NUMBER: S122RDRP-S1005D935-X4F0-XX-UDD-WVL-B

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	798.9	798.9	798.9	798.9	798.9
2.5°	796.3	797.6	789.9	797.6	800.1
5°	791.2	791.2	779.8	784.9	784.9
7.5°	782.3	781.0	763.2	763.2	762.0
10°	768.3	763.2	741.6	737.8	735.3
12.5°	750.5	741.6	716.2	709.8	706.0
15°	726.3	716.2	688.2	679.3	674.2
17.5°	690.7	680.6	656.4	646.2	641.1
20°	653.8	638.6	620.8	611.9	606.8
22.5°	615.7	597.9	581.3	575.0	569.9
25°	578.8	559.7	540.6	538.1	530.4
27.5°	543.2	520.3	501.2	499.9	493.6
30°	505.0	480.8	460.5	461.8	455.4
32.5°	469.4	446.5	422.3	423.6	416.0
35°	432.5	408.3	385.4	384.2	376.5
37.5°	394.3	371.4	349.8	344.7	337.1
40°	360.0	337.1	314.2	305.3	297.7
42.5°	323.1	302.8	282.4	268.4	258.2
45°	286.2	268.4	249.3	231.5	220.1
47.5°	250.6	236.6	220.1	198.4	190.8
50°	215.0	204.8	190.8	171.7	167.9
52.5°	178.1	174.3	165.4	152.6	151.4
55°	138.7	146.3	141.2	136.1	134.8
57.5°	117.0	118.3	122.1	120.8	120.8
60°	100.5	100.5	105.6	106.9	106.9
62.5°	85.2	86.5	91.6	94.1	94.1
65°	72.5	73.8	77.6	81.4	82.7
67.5°	59.8	62.3	66.1	70.0	71.2
70°	48.3	50.9	56.0	59.8	61.1
72.5°	39.4	40.7	45.8	49.6	50.9
75°	30.5	31.8	35.6	40.7	42.0
77.5°	21.6	24.2	28.0	31.8	34.3
80°	15.3	16.5	19.1	24.2	25.4
82.5°	8.9	10.2	12.7	16.5	17.8
85°	2.5	3.8	5.1	8.9	11.4
87.5°	0.0	0.0	0.0	2.5	5.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1057849

CATALOG NUMBER: S122RDRP-S1005D935-X4F0-XX-UDD-WVL-B

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.47	16.87	15.84	17.18	17.49	15.65	17.04	16.01	17.36	17.67
	3H	16.60	17.85	16.98	18.18	18.54	17.11	18.35	17.49	18.68	19.05
	4H	16.95	18.12	17.36	18.47	18.85	17.65	18.81	18.05	19.16	19.55
	6H	17.14	18.21	17.55	18.58	18.97	18.06	19.13	18.48	19.50	19.90
	8H	17.17	18.18	17.59	18.57	18.98	18.19	19.21	18.62	19.60	20.00
	12H	17.15	18.12	17.58	18.50	18.93	18.27	19.25	18.70	19.63	20.06
4H	2H	15.93	17.09	16.33	17.44	17.82	16.07	17.24	16.48	17.59	17.97
	3H	17.27	18.23	17.68	18.63	19.03	17.75	18.71	18.16	19.11	19.51
	4H	17.71	18.57	18.15	18.99	19.43	18.41	19.27	18.85	19.69	20.13
	6H	17.98	18.73	18.44	19.17	19.64	18.95	19.69	19.41	20.14	20.60
	8H	18.03	18.72	18.49	19.17	19.64	19.12	19.81	19.58	20.26	20.72
	12H	18.02	18.64	18.51	19.12	19.59	19.24	19.85	19.72	20.33	20.81
8H	4H	17.93	18.62	18.39	19.07	19.53	18.56	19.26	19.03	19.70	20.17
	6H	18.27	18.84	18.77	19.34	19.82	19.19	19.76	19.69	20.26	20.74
	8H	18.35	18.86	18.87	19.37	19.86	19.43	19.94	19.95	20.45	20.94
	12H	18.37	18.82	18.88	19.31	19.88	19.61	20.06	20.12	20.55	21.12
12H	4H	17.94	18.55	18.42	19.03	19.51	18.55	19.16	19.03	19.65	20.12
	6H	18.30	18.81	18.82	19.32	19.81	19.19	19.70	19.71	20.21	20.70
	8H	18.41	18.86	18.93	19.36	19.93	19.46	19.91	19.98	20.41	20.98