

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1058167

Luminaire Tested: S122RDRP-S865D935-X4F0-XX-UDD-BVL-B

Issue Date: 8/7/2025

**Test Information**

Test Method: LM-79-2024  
Report Number: P1058167  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2406-143-21)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/7/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S122RDRP-S865D935-X4F0-XX-UDD-BVL-B  
Description: DEFINE 2 BLACK REGRESSED DIRECT RECESSED HOUSING WITH BLACK STRAIGHT BLADE LOUVER WITH DIFFUSER  
CORE LIGHT ENGINE  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 482.1 lumens  
Efficiency: N/A  
Efficacy: 13.8 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.8 / 0.88  
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 35  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1058167

CATALOG NUMBER: S122RDRP-S865D935-X4F0-XX-UDD-BVL-B

### Luminous Intensity Polar Plot





TEST NUMBER: P1058167

CATALOG NUMBER: S122RDRP-S865D935-X4F0-XX-UDD-BVL-B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93					93			
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86					86			
3	101	95	90	85	99	93	89	85	91	87	83	88	85	82	86	83	81	79					79			
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73					73			
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67					67			
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62					62			
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58					58			
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	56	54					54			
9	73	63	57	53	72	62	57	52	61	56	52	61	56	52	60	55	52	51					51			
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47					47			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9461	9461	9461
5°	9395	9256	9295
10°	9200	8814	8591
15°	8656	8054	7724
20°	7725	7152	6747
25°	6753	6047	5737
30°	5796	4941	4619
35°	4834	3857	3467
40°	3760	2845	2219
45°	2630	1895	963
50°	1432	996	342
55°	209	347	244
60°	41	81	159
65°	0	48	96
70°	0	0	59
75°	0	0	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2630 cd/sqm



TEST NUMBER: P1058167

CATALOG NUMBER: S122RDRP-S865D935-X4F0-XX-UDD-BVL-B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	47.1	9.8
10°-20°	118.7	24.6
20°-30°	138.4	28.7
30°-40°	110.9	23.0
40°-50°	55.1	11.4
50°-60°	10.9	2.3
60°-70°	1.0	0.2
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	304.2	63.1
0°-40°	415.1	86.1
0°-60°	481.1	99.8
0°-90°	482.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	482.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	513	513	513	513	513	
5°	507	507	500	501	502	48
15°	453	444	422	411	404	126
25°	332	315	297	290	282	153
35°	215	193	171	164	154	133
45°	101	89	73	49	37	78
55°	6	13	11	6	8	13
65°	0	0	1	1	2	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1058167

CATALOG NUMBER: S122RDRP-S865D935-X4F0-XX-UDD-BVL-B

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	512.7	512.7	512.7	512.7	512.7
2.5°	510.5	512.7	507.2	512.7	513.7
5°	507.2	507.2	499.7	500.7	501.8
7.5°	501.8	499.7	486.7	484.5	482.3
10°	491.0	486.7	470.4	461.7	458.5
12.5°	475.8	469.3	447.6	437.9	432.5
15°	453.1	444.4	421.6	410.8	404.3
17.5°	423.8	416.2	394.5	382.6	376.1
20°	393.4	382.6	364.2	352.3	343.6
22.5°	364.2	350.1	330.6	321.9	313.2
25°	331.7	315.4	297.0	290.5	281.8
27.5°	304.6	284.0	262.3	258.0	250.4
30°	272.0	252.5	231.9	225.4	216.8
32.5°	243.9	222.2	201.6	194.0	186.4
35°	214.6	192.9	171.2	163.7	153.9
37.5°	186.4	165.8	144.2	132.2	123.6
40°	156.1	138.7	118.1	103.0	92.1
42.5°	129.0	113.8	94.3	74.8	63.9
45°	100.8	88.9	72.6	48.8	36.9
47.5°	74.8	66.1	53.1	28.2	19.5
50°	49.9	46.6	34.7	14.1	11.9
52.5°	27.1	29.3	20.6	8.7	9.8
55°	6.5	13.0	10.8	6.5	7.6
57.5°	1.1	2.2	5.4	5.4	5.4
60°	1.1	1.1	2.2	3.3	4.3
62.5°	1.1	0.0	1.1	2.2	3.3
65°	0.0	0.0	1.1	1.1	2.2
67.5°	0.0	0.0	0.0	1.1	1.1
70°	0.0	0.0	0.0	1.1	1.1
72.5°	0.0	0.0	0.0	0.0	1.1
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1058167  
 CATALOG NUMBER: S122RDRP-S865D935-X4F0-XX-UDD-BVL-B

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00