

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1058212

Luminaire Tested: S122RDRP-H1005D840-X4F0-XX-UDD-BVL-B

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2024
Report Number: P1058212
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2406-143-21)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDRP-H1005D840-X4F0-XX-UDD-BVL-B
Description: DEFINE 2 BLACK REGRESSED DIRECT RECESSED HOUSING WITH BLACK STRAIGHT BLADE LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 641.9 lumens
Efficiency: N/A
Efficacy: 17.6 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.8 / 0.88
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 36.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1058212

CATALOG NUMBER: S122RDRP-H1005D840-X4F0-XX-UDD-BVL-B

Luminous Intensity Polar Plot





TEST NUMBER: P1058212

CATALOG NUMBER: S122RDRP-H1005D840-X4F0-XX-UDD-BVL-B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93					93			
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86					86			
3	101	95	90	85	99	93	89	85	91	87	83	88	85	82	86	83	81	79					79			
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73					73			
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67					67			
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62					62			
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58					58			
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	56	54					54			
9	73	63	57	53	72	62	57	52	61	56	52	61	56	52	60	55	52	51					51			
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47					47			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12596	12596	12596
5°	12510	12323	12377
10°	12250	11737	11439
15°	11525	10725	10283
20°	10288	9522	8984
25°	8991	8050	7639
30°	7717	6580	6149
35°	6438	5136	4616
40°	5005	3789	2956
45°	3502	2523	1281
50°	1906	1326	456
55°	280	463	325
60°	52	107	214
65°	0	61	127
70°	0	0	76
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3502 cd/sqm



TEST NUMBER: P1058212

CATALOG NUMBER: S122RDRP-H1005D840-X4F0-XX-UDD-BVL-B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.7	9.8
10°-20°	158.1	24.6
20°-30°	184.2	28.7
30°-40°	147.7	23.0
40°-50°	73.4	11.4
50°-60°	14.5	2.3
60°-70°	1.3	0.2
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	405.0	63.1
0°-40°	552.7	86.1
0°-60°	640.5	99.8
0°-90°	641.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	641.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	683	683	683	683	683	
5°	675	675	665	667	668	64
15°	603	592	561	547	538	167
25°	442	420	395	387	375	203
35°	286	257	228	218	205	178
45°	134	118	97	65	49	104
55°	9	17	14	9	10	17
65°	0	0	1	1	3	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1058212

CATALOG NUMBER: S122RDRP-H1005D840-X4F0-XX-UDD-BVL-B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	682.6	682.6	682.6	682.6	682.6
2.5°	679.7	682.6	675.4	682.6	684.1
5°	675.4	675.4	665.3	666.8	668.2
7.5°	668.2	665.3	648.0	645.1	642.2
10°	653.8	648.0	626.4	614.8	610.5
12.5°	633.6	624.9	596.0	583.1	575.8
15°	603.3	591.7	561.4	547.0	538.3
17.5°	564.3	554.2	525.3	509.5	500.8
20°	523.9	509.5	484.9	469.0	457.5
22.5°	484.9	466.2	440.2	428.6	417.1
25°	441.6	420.0	395.4	386.8	375.2
27.5°	405.5	378.1	349.3	343.5	333.4
30°	362.2	336.3	308.8	300.2	288.6
32.5°	324.7	295.9	268.4	258.3	248.2
35°	285.8	256.9	228.0	217.9	204.9
37.5°	248.2	220.8	191.9	176.1	164.5
40°	207.8	184.7	157.3	137.1	122.7
42.5°	171.7	151.5	125.6	99.6	85.1
45°	134.2	118.3	96.7	64.9	49.1
47.5°	99.6	88.0	70.7	37.5	26.0
50°	66.4	62.1	46.2	18.8	15.9
52.5°	36.1	39.0	27.4	11.5	13.0
55°	8.7	17.3	14.4	8.7	10.1
57.5°	1.4	2.9	7.2	7.2	7.2
60°	1.4	1.4	2.9	4.3	5.8
62.5°	1.4	0.0	1.4	2.9	4.3
65°	0.0	0.0	1.4	1.4	2.9
67.5°	0.0	0.0	0.0	1.4	1.4
70°	0.0	0.0	0.0	1.4	1.4
72.5°	0.0	0.0	0.0	0.0	1.4
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1058212
 CATALOG NUMBER: S122RDRP-H1005D840-X4F0-XX-UDD-BVL-B

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.24
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.25
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.14
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00