

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1058214

Luminaire Tested: S122RDRP-H1005D840-X4F0-XX-UDD-BVL-W

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2024
Report Number: P1058214
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2406-143-57)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDRP-H1005D840-X4F0-XX-UDD-BVL-W
Description: DEFINE 2 WHITE REGRESSED DIRECT RECESSED HOUSING WITH BLACK STRAIGHT BLADE
LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 983.4 lumens
Efficiency: N/A
Efficacy: 26.9 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.96 / 0.91
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 36.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1058214

CATALOG NUMBER: S122RDRP-H1005D840-X4F0-XX-UDD-BVL-W

Luminous Intensity Polar Plot





TEST NUMBER: P1058214

CATALOG NUMBER: S122RDRP-H1005D840-X4F0-XX-UDD-BVL-W

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81
3	98	91	85	80	96	89	84	79	86	82	78	84	80	76	81	78	75	74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67
5	87	77	70	65	85	76	70	65	74	69	64	72	67	64	71	66	63	61
6	82	72	65	60	80	71	64	59	69	63	59	68	62	58	66	62	58	56
7	77	67	60	55	76	66	59	55	64	59	54	63	58	54	62	57	54	52
8	73	62	55	51	72	62	55	51	60	54	50	59	54	50	58	53	50	48
9	69	58	52	47	68	58	51	47	57	51	47	56	50	47	55	50	46	45
10	66	55	48	44	64	54	48	44	53	48	44	53	47	43	52	47	43	42

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16672	16672	16672
5°	16013	16308	16628
10°	14761	15411	16224
15°	13227	14138	15493
20°	11609	12575	14221
25°	9830	10860	12833
30°	7886	9117	11427
35°	5830	7294	9900
40°	3657	5711	8043
45°	1433	4301	5960
50°	706	2905	3652
55°	557	1908	1628
60°	428	1546	1495
65°	314	1450	1450
70°	388	1484	1484
75°	414	1647	1547
80°	616	2147	1690
85°	1228	3663	2456

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 87.5°
 Luminance: 6726 cd/sqm



TEST NUMBER: P1058214

CATALOG NUMBER: S122RDRP-H1005D840-X4F0-XX-UDD-BVL-W

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.5	8.4
10°-20°	208.6	21.2
20°-30°	249.6	25.4
30°-40°	210.1	21.4
40°-50°	119.6	12.2
50°-60°	47.2	4.8
60°-70°	29.7	3.0
70°-80°	22.1	2.2
80°-90°	14.0	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	540.7	55.0
0°-40°	750.8	76.3
0°-60°	917.6	93.3
0°-90°	983.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	983.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	904	904	904	904	904	
5°	864	883	880	890	898	80
15°	692	717	740	784	811	193
25°	483	504	533	588	630	220
35°	259	282	324	393	440	160
45°	55	97	165	207	228	52
55°	17	38	59	61	51	16
65°	7	33	33	32	33	8
75°	6	23	23	22	22	6
85°	6	16	17	16	12	5
90°	0	0	0	0	0	



TEST NUMBER: P1058214

CATALOG NUMBER: S122RDRP-H1005D840-X4F0-XX-UDD-BVL-W

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	903.5	903.5	903.5	903.5	903.5
2.5°	889.0	904.9	894.8	896.3	897.7
5°	864.5	883.3	880.4	890.5	897.7
7.5°	828.3	848.6	855.8	873.1	886.1
10°	787.8	811.0	822.5	850.0	865.9
12.5°	741.6	767.6	785.0	819.7	842.8
15°	692.4	717.0	740.1	783.5	811.0
17.5°	643.3	667.9	692.4	740.1	769.1
20°	591.2	614.4	640.4	691.0	724.2
22.5°	536.3	560.9	586.9	639.0	679.4
25°	482.8	504.5	533.4	588.4	630.3
27.5°	426.4	448.1	479.9	536.3	581.1
30°	370.1	391.8	427.9	485.7	536.3
32.5°	313.7	336.8	375.9	439.5	490.1
35°	258.8	281.9	323.8	393.2	439.5
37.5°	205.3	231.3	277.6	345.5	388.9
40°	151.8	182.1	237.1	297.8	333.9
42.5°	101.2	138.8	199.5	250.1	280.4
45°	54.9	96.9	164.8	206.7	228.4
47.5°	30.4	62.2	131.5	164.8	177.8
50°	24.6	43.4	101.2	125.8	127.2
52.5°	20.2	39.0	75.2	89.6	82.4
55°	17.3	37.6	59.3	60.7	50.6
57.5°	14.5	36.1	49.2	43.4	43.4
60°	11.6	36.1	41.9	39.0	40.5
62.5°	8.7	36.1	37.6	34.7	36.1
65°	7.2	33.2	33.2	31.8	33.2
67.5°	7.2	30.4	30.4	28.9	30.4
70°	7.2	28.9	27.5	27.5	27.5
72.5°	5.8	26.0	26.0	24.6	24.6
75°	5.8	23.1	23.1	21.7	21.7
77.5°	5.8	21.7	21.7	20.2	18.8
80°	5.8	18.8	20.2	18.8	15.9
82.5°	5.8	17.3	18.8	17.3	13.0
85°	5.8	15.9	17.3	15.9	11.6
87.5°	4.3	15.9	15.9	13.0	8.7
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1058214

CATALOG NUMBER: S122RDRP-H1005D840-X4F0-XX-UDD-BVL-W

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.46	8.68	7.83	9.00	9.31	9.50	10.72	9.86	11.03	11.34
	3H	9.01	10.09	9.39	10.42	10.79	11.47	12.55	11.85	12.89	13.25
	4H	9.56	10.58	9.97	10.93	11.31	12.38	13.40	12.79	13.75	14.13
	6H	10.12	11.05	10.54	11.42	11.82	13.27	14.20	13.68	14.57	14.96
	8H	10.42	11.30	10.85	11.69	12.10	13.67	14.55	14.10	14.94	15.35
	12H	10.78	11.62	11.21	12.00	12.43	14.11	14.95	14.55	15.34	15.77
4H	2H	8.65	9.66	9.05	10.01	10.40	10.11	11.12	10.52	11.48	11.86
	3H	10.85	11.68	11.26	12.09	12.49	12.36	13.19	12.77	13.60	14.00
	4H	11.90	12.65	12.34	13.07	13.52	13.43	14.18	13.87	14.60	15.04
	6H	12.80	13.45	13.27	13.90	14.36	14.54	15.19	15.00	15.64	16.10
	8H	13.19	13.79	13.66	14.24	14.71	15.06	15.67	15.53	16.12	16.59
	12H	13.61	14.14	14.10	14.63	15.10	15.64	16.17	16.13	16.66	17.13
8H	4H	12.70	13.31	13.18	13.76	14.23	13.92	14.53	14.39	14.98	15.45
	6H	14.09	14.58	14.59	15.08	15.56	15.32	15.81	15.82	16.31	16.79
	8H	14.81	15.25	15.33	15.77	16.26	16.05	16.50	16.58	17.02	17.51
	12H	15.56	15.95	16.07	16.45	17.02	16.89	17.28	17.40	17.78	18.35
12H	4H	12.87	13.40	13.35	13.89	14.36	14.02	14.56	14.51	15.04	15.52
	6H	14.42	14.87	14.94	15.38	15.88	15.53	15.98	16.06	16.50	16.99
	8H	15.33	15.73	15.85	16.22	16.80	16.42	16.81	16.93	17.31	17.88