

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1056511

Luminaire Tested: S125R3DRP-H1090D935-X4F0-XX-UDD-F-B

Issue Date: 7/25/2025

Test Information

Test Method: LM-79-2024
Report Number: P1056511
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2503-402-11)
Test Lab: INNOVATION CENTER
Issue Date: 7/25/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125R3DRP-H1090D935-X4F0-XX-UDD-F-B
Description: DEFINE 5, BLACK 3-INCH REGRESSED DIRECT RECESSED HOUSING WITH FROSTED LENS
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1758.6 lumens
Efficiency: N/A
Efficacy: 56.9 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 0.89 / 1.07
Luminous Opening: Rectangular (W 0.39' x L: 3.9' x H: 0')
CIE Type: Direct

Input Watts (W): 30.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1056511

CATALOG NUMBER: S125R3DRP-H1090D935-X4F0-XX-UDD-F-B

Luminous Intensity Polar Plot





TEST NUMBER: P1056511

CATALOG NUMBER: S125R3DRP-H1090D935-X4F0-XX-UDD-F-B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	104	101	109	106	103	100	101	99	97	98	96	94	94	93	91	89
2	103	97	91	87	101	95	90	86	92	88	84	89	85	82	86	83	80	78
3	96	87	81	75	94	86	80	75	83	78	74	80	76	72	78	74	71	69
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	61
5	83	72	64	59	81	71	64	58	69	63	58	67	62	57	65	61	57	55
6	77	66	58	53	76	65	58	52	63	57	52	62	56	52	60	55	51	49
7	72	61	53	47	71	60	52	47	58	52	47	57	51	47	56	50	46	45
8	68	56	48	43	66	55	48	43	54	47	43	53	47	43	52	46	42	41
9	64	52	44	39	62	51	44	39	50	44	39	49	43	39	48	43	39	37
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7670	7670	7670
5°	7607	7585	7577
10°	7565	7341	7186
15°	7468	7012	6713
20°	7345	6609	6091
25°	7204	6139	5402
30°	7031	5626	4669
35°	6857	5057	3860
40°	6668	4445	3056
45°	6471	3795	2214
50°	6256	3063	1431
55°	6017	2239	636
60°	5732	1383	182
65°	5378	503	109
70°	4868	178	45
75°	4228	60	30
80°	3241	45	0
85°	1484	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6471 cd/sqm



TEST NUMBER: P1056511

CATALOG NUMBER: S125R3DRP-H1090D935-X4F0-XX-UDD-F-B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.8	5.7
10°-20°	270.6	15.4
20°-30°	366.1	20.8
30°-40°	376.0	21.4
40°-50°	311.6	17.7
50°-60°	200.0	11.4
60°-70°	96.6	5.5
70°-80°	32.7	1.9
80°-90°	4.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	737.4	41.9
0°-40°	1113.5	63.3
0°-60°	1625.0	92.4
0°-90°	1758.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1758.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1085	1085	1085	1085	1085	
5°	1072	1081	1069	1062	1068	102
15°	1020	1008	958	925	917	288
25°	924	878	787	716	692	425
35°	795	718	586	484	447	497
45°	647	541	380	262	222	499
55°	488	358	182	80	52	436
65°	322	177	30	9	6	318
75°	155	33	2	1	1	164
85°	18	0	0	0	0	29
90°	0	0	0	0	0	



TEST NUMBER: P1056511

CATALOG NUMBER: S125R3DRP-H1090D935-X4F0-XX-UDD-F-B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1084.9	1084.9	1084.9	1084.9	1084.9
2.5°	1078.5	1087.1	1079.6	1078.5	1080.6
5°	1072.0	1080.6	1068.8	1062.4	1067.7
7.5°	1064.5	1068.8	1048.4	1037.6	1039.8
10°	1053.8	1052.7	1022.6	1004.3	1001.1
12.5°	1037.6	1032.2	992.5	966.7	961.3
15°	1020.4	1007.5	958.1	924.7	917.2
17.5°	1000.0	979.6	920.4	877.4	866.7
20°	976.3	948.4	878.5	825.8	809.7
22.5°	950.5	915.0	834.4	772.0	750.5
25°	923.6	878.5	787.1	716.1	692.5
27.5°	893.5	840.8	739.8	659.1	630.1
30°	861.3	801.1	689.2	601.1	572.0
32.5°	827.9	761.3	638.7	543.0	507.5
35°	794.6	718.3	586.0	483.9	447.3
37.5°	759.1	675.3	534.4	428.0	388.2
40°	722.6	631.2	481.7	369.9	331.2
42.5°	684.9	586.0	429.0	315.0	275.3
45°	647.3	540.9	379.6	262.4	221.5
47.5°	608.6	494.6	328.0	210.8	175.3
50°	568.8	449.5	278.5	164.5	130.1
52.5°	529.0	403.2	228.0	119.4	88.2
55°	488.2	358.1	181.7	79.6	51.6
57.5°	447.3	311.8	138.7	44.1	19.4
60°	405.4	267.7	97.8	15.1	12.9
62.5°	364.5	220.4	61.3	11.8	9.7
65°	321.5	177.4	30.1	8.6	6.5
67.5°	279.6	136.6	12.9	5.4	3.2
70°	235.5	98.9	8.6	3.2	2.2
72.5°	194.6	63.4	5.4	2.2	1.1
75°	154.8	33.3	2.2	1.1	1.1
77.5°	116.1	14.0	1.1	1.1	1.1
80°	79.6	6.5	1.1	1.1	0.0
82.5°	47.3	2.2	1.1	1.1	0.0
85°	18.3	0.0	0.0	0.0	0.0
87.5°	1.1	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1056511
 CATALOG NUMBER: S125R3DRP-H1090D935-X4F0-XX-UDD-F-B

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.15	19.53	18.51	19.84	20.16	3.02	4.40	3.38	4.71	5.03
	3H	19.70	20.92	20.08	21.25	21.62	2.94	4.17	3.32	4.49	4.86
	4H	20.22	21.36	20.62	21.71	22.10	2.87	4.02	3.27	4.37	4.75
	6H	20.56	21.61	20.97	21.98	22.37	2.80	3.85	3.22	4.22	4.62
	8H	20.64	21.64	21.07	22.03	22.43	2.76	3.76	3.19	4.15	4.55
	12H	20.66	21.61	21.09	21.99	22.42	2.72	3.67	3.15	4.06	4.49
4H	2H	17.95	19.09	18.35	19.44	19.83	3.88	5.02	4.28	5.37	5.75
	3H	19.56	20.50	19.98	20.90	21.30	3.83	4.76	4.24	5.16	5.57
	4H	20.09	20.92	20.52	21.34	21.78	3.75	4.58	4.18	5.00	5.44
	6H	20.46	21.18	20.92	21.63	22.09	3.69	4.40	4.15	4.85	5.31
	8H	20.56	21.23	21.03	21.68	22.15	3.63	4.31	4.10	4.75	5.22
	12H	20.60	21.19	21.08	21.67	22.14	3.59	4.19	4.08	4.67	5.14
8H	4H	19.96	20.63	20.43	21.08	21.55	4.77	5.44	5.24	5.89	6.36
	6H	20.31	20.86	20.82	21.36	21.84	4.69	5.24	5.19	5.73	6.21
	8H	20.41	20.90	20.93	21.42	21.91	4.64	5.13	5.16	5.64	6.13
	12H	20.45	20.89	20.97	21.38	21.95	4.60	5.03	5.11	5.52	6.09
12H	4H	19.92	20.51	20.40	20.99	21.46	4.85	5.44	5.33	5.92	6.40
	6H	20.25	20.75	20.77	21.26	21.75	4.75	5.24	5.27	5.76	6.25
	8H	20.37	20.80	20.88	21.30	21.87	4.72	5.15	5.23	5.65	6.22