

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1058299

Luminaire Tested: S122RDRP-H290D840-X4F0-XX-UDD-WVL-B

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2024
Report Number: P1058299
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2406-143-19)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDRP-H290D840-X4F0-XX-UDD-WVL-B
Description: DEFINE 2 BLACK REGRESSED DIRECT RECESSED HOUSING WITH WHITE STRAIGHT BLADE LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 409.7 lumens
Efficiency: N/A
Efficacy: 35.0 lumens/watt
Spacing Criteria (0/90/45): 1 / 0.92 / 1.02
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1058299

CATALOG NUMBER: S122RDRP-H290D840-X4F0-XX-UDD-WVL-B

Luminous Intensity Polar Plot





TEST NUMBER: P1058299

CATALOG NUMBER: S122RDRP-H290D840-X4F0-XX-UDD-WVL-B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77
3	95	87	80	74	93	85	79	74	82	77	73	80	75	71	77	73	70	68
4	89	79	71	65	87	77	70	65	75	69	64	73	68	63	71	66	63	61
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54
6	77	66	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49
7	72	60	53	47	71	60	52	47	58	52	47	57	51	47	56	50	46	44
8	68	56	48	43	66	55	48	43	54	47	43	53	47	43	52	46	42	41
9	64	52	45	40	63	51	44	39	50	44	39	49	43	39	48	43	39	37
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4978	4978	4978
5°	4949	4877	4909
10°	4860	4692	4652
15°	4686	4440	4350
20°	4336	4116	4024
25°	3978	3718	3646
30°	3633	3313	3277
35°	3289	2933	2863
40°	2929	2556	2421
45°	2521	2197	1939
50°	2084	1849	1628
55°	1506	1535	1464
60°	1251	1318	1332
65°	1070	1144	1218
70°	879	1020	1111
75°	734	856	1012
80°	553	680	914
85°	191	360	826

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2521 cd/sqm

TEST NUMBER: P1058299

CATALOG NUMBER: S122RDRP-H290D840-X4F0-XX-UDD-WVL-B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.9	6.1
10°-20°	65.7	16.0
20°-30°	85.0	20.7
30°-40°	83.3	20.3
40°-50°	65.6	16.0
50°-60°	43.0	10.5
60°-70°	26.2	6.4
70°-80°	13.1	3.2
80°-90°	2.8	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	175.6	42.9
0°-40°	258.9	63.2
0°-60°	367.6	89.7
0°-90°	409.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	409.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	270	270	270	270	270	
5°	267	267	263	265	265	25
15°	245	242	232	229	228	68
25°	195	189	183	182	179	90
35°	146	138	130	130	127	91
45°	97	91	84	78	74	74
55°	47	49	48	46	46	44
65°	24	25	26	28	28	24
75°	10	11	12	14	14	11
85°	1	1	2	3	4	2
90°	0	0	0	0	0	



TEST NUMBER: P1058299

CATALOG NUMBER: S122RDRP-H290D840-X4F0-XX-UDD-WVL-B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	269.8	269.8	269.8	269.8	269.8
2.5°	268.9	269.3	266.7	269.3	270.2
5°	267.2	267.2	263.3	265.0	265.0
7.5°	264.2	263.7	257.7	257.7	257.3
10°	259.4	257.7	250.4	249.1	248.3
12.5°	253.4	250.4	241.8	239.7	238.4
15°	245.3	241.8	232.4	229.4	227.7
17.5°	233.2	229.8	221.6	218.2	216.5
20°	220.8	215.6	209.6	206.6	204.9
22.5°	207.9	201.9	196.3	194.2	192.4
25°	195.4	189.0	182.6	181.7	179.1
27.5°	183.4	175.7	169.2	168.8	166.7
30°	170.5	162.4	155.5	155.9	153.8
32.5°	158.5	150.8	142.6	143.0	140.5
35°	146.0	137.9	130.2	129.7	127.1
37.5°	133.2	125.4	118.1	116.4	113.8
40°	121.6	113.8	106.1	103.1	100.5
42.5°	109.1	102.2	95.4	90.6	87.2
45°	96.6	90.6	84.2	78.2	74.3
47.5°	84.6	79.9	74.3	67.0	64.4
50°	72.6	69.2	64.4	58.0	56.7
52.5°	60.1	58.8	55.8	51.5	51.1
55°	46.8	49.4	47.7	46.0	45.5
57.5°	39.5	39.9	41.2	40.8	40.8
60°	33.9	33.9	35.7	36.1	36.1
62.5°	28.8	29.2	30.9	31.8	31.8
65°	24.5	24.9	26.2	27.5	27.9
67.5°	20.2	21.0	22.3	23.6	24.1
70°	16.3	17.2	18.9	20.2	20.6
72.5°	13.3	13.7	15.5	16.8	17.2
75°	10.3	10.7	12.0	13.7	14.2
77.5°	7.3	8.2	9.4	10.7	11.6
80°	5.2	5.6	6.4	8.2	8.6
82.5°	3.0	3.4	4.3	5.6	6.0
85°	0.9	1.3	1.7	3.0	3.9
87.5°	0.0	0.0	0.0	0.9	1.7
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1058299
 CATALOG NUMBER: S122RDRP-H290D840-X4F0-XX-UDD-WVL-B

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.69	13.09	12.06	13.40	13.72	11.88	13.27	12.24	13.59	13.90
	3H	12.82	14.07	13.20	14.40	14.76	13.34	14.58	13.72	14.91	15.28
	4H	13.18	14.34	13.58	14.69	15.07	13.88	15.04	14.28	15.39	15.78
	6H	13.36	14.43	13.78	14.80	15.19	14.29	15.36	14.71	15.73	16.13
	8H	13.39	14.41	13.82	14.80	15.20	14.42	15.44	14.85	15.83	16.23
	12H	13.37	14.35	13.81	14.73	15.16	14.50	15.48	14.94	15.86	16.29
4H	2H	12.15	13.31	12.55	13.66	14.05	12.30	13.47	12.71	13.82	14.20
	3H	13.49	14.45	13.90	14.85	15.25	13.98	14.94	14.39	15.34	15.74
	4H	13.93	14.79	14.37	15.21	15.65	14.64	15.50	15.08	15.92	16.36
	6H	14.21	14.95	14.67	15.40	15.86	15.18	15.92	15.64	16.36	16.83
	8H	14.25	14.95	14.72	15.39	15.86	15.35	16.04	15.81	16.48	16.95
	12H	14.25	14.86	14.73	15.34	15.82	15.47	16.08	15.95	16.56	17.04
8H	4H	14.15	14.84	14.61	15.29	15.76	14.79	15.48	15.26	15.93	16.40
	6H	14.50	15.07	15.00	15.56	16.04	15.42	15.99	15.92	16.48	16.96
	8H	14.57	15.08	15.09	15.60	16.09	15.66	16.17	16.17	16.68	17.17
	12H	14.59	15.04	15.10	15.54	16.10	15.84	16.29	16.35	16.79	17.35
12H	4H	14.16	14.77	14.64	15.26	15.73	14.78	15.39	15.26	15.87	16.35
	6H	14.52	15.03	15.04	15.55	16.04	15.42	15.93	15.93	16.44	16.93
	8H	14.64	15.09	15.15	15.58	16.15	15.69	16.14	16.20	16.64	17.20