

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1056620

Luminaire Tested: S125R3DRP-H850D935-X4F0-XX-UDD-F-S

Issue Date: 7/25/2025

**Test Information**

Test Method: LM-79-2024  
Report Number: P1056620  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2503-402-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/25/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S125R3DRP-H850D935-X4F0-XX-UDD-F-S  
Description: DEFINE 5, SILVER 3-INCH REGRESSED DIRECT RECESSED HOUSING WITH FROSTED LENS  
HIGH PERFORMANCE LIGHT ENGINE  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1627.5 lumens  
Efficiency: N/A  
Efficacy: 68.4 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 0.95 / 1.11  
Luminous Opening: Rectangular (W 0.39' x L: 3.9' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 23.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1056620

CATALOG NUMBER: S125R3DRP-H850D935-X4F0-XX-UDD-F-S

### Luminous Intensity Polar Plot





TEST NUMBER: P1056620

CATALOG NUMBER: S125R3DRP-H850D935-X4F0-XX-UDD-F-S

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88
2	102	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47
7	71	58	50	45	69	58	50	45	56	49	44	55	49	44	54	48	44	42
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	36	35
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6366	6366	6366
5°	6313	6295	6307
10°	6267	6122	6057
15°	6194	5901	5742
20°	6085	5620	5319
25°	5970	5288	4838
30°	5832	4921	4308
35°	5677	4504	3749
40°	5517	4048	3170
45°	5360	3568	2625
50°	5171	3035	2063
55°	4973	2466	1500
60°	4751	1839	1073
65°	4463	1213	836
70°	4033	845	585
75°	3507	546	456
80°	2748	407	375
85°	1419	341	268

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 5360 cd/sqm



TEST NUMBER: P1056620

CATALOG NUMBER: S125R3DRP-H850D935-X4F0-XX-UDD-F-S

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	83.9	5.2
10°-20°	228.0	14.0
20°-30°	315.3	19.4
30°-40°	334.1	20.5
40°-50°	291.6	17.9
50°-60°	207.4	12.7
60°-70°	115.3	7.1
70°-80°	44.3	2.7
80°-90°	7.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	627.2	38.5
0°-40°	961.2	59.1
0°-60°	1460.2	89.7
0°-90°	1627.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1627.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	900	900	900	900	900	
5°	890	896	887	885	889	84
15°	846	839	806	789	785	238
25°	765	740	678	636	620	352
35°	658	613	522	459	434	412
45°	536	472	357	285	263	413
55°	404	324	200	138	122	361
65°	267	175	72	53	50	264
75°	128	50	20	17	17	136
85°	18	5	4	3	3	26
90°	0	0	0	0	0	



TEST NUMBER: P1056620

CATALOG NUMBER: S125R3DRP-H850D935-X4F0-XX-UDD-F-S

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	900.5	900.5	900.5	900.5	900.5
2.5°	893.8	903.0	895.5	896.3	897.1
5°	889.6	896.3	887.1	884.6	888.8
7.5°	883.0	888.0	872.1	866.3	868.8
10°	873.0	874.6	852.9	844.6	843.8
12.5°	860.4	857.9	831.3	817.9	817.1
15°	846.3	838.8	806.3	788.7	784.6
17.5°	828.8	817.1	777.1	754.6	747.9
20°	808.8	792.9	747.1	717.9	707.0
22.5°	788.7	767.1	713.7	677.0	665.3
25°	765.4	739.5	677.9	636.2	620.3
27.5°	740.4	709.5	641.2	592.8	573.6
30°	714.5	678.7	602.8	548.6	527.8
32.5°	687.0	646.2	562.8	503.6	481.9
35°	657.8	612.8	521.9	458.6	434.4
37.5°	628.7	578.6	481.9	414.4	389.4
40°	597.8	543.6	438.6	369.4	343.5
42.5°	567.8	507.8	397.7	326.8	303.5
45°	536.1	471.9	356.9	285.1	262.6
47.5°	503.6	434.4	316.0	246.0	223.4
50°	470.2	397.7	276.0	207.6	187.6
52.5°	436.9	361.0	238.5	170.9	153.4
55°	403.5	323.5	200.1	138.4	121.7
57.5°	370.2	286.8	164.3	108.4	93.4
60°	336.0	249.3	130.1	80.0	75.9
62.5°	301.8	212.6	100.9	65.9	62.5
65°	266.8	175.1	72.5	53.4	50.0
67.5°	231.8	140.9	52.5	40.9	38.4
70°	195.1	107.6	40.9	30.8	28.3
72.5°	160.1	77.5	29.2	22.5	21.7
75°	128.4	50.0	20.0	16.7	16.7
77.5°	96.7	30.0	14.2	12.5	12.5
80°	67.5	17.5	10.0	9.2	9.2
82.5°	40.9	9.2	6.7	5.8	5.8
85°	17.5	5.0	4.2	3.3	3.3
87.5°	3.3	1.7	1.7	1.7	1.7
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1056620  
 CATALOG NUMBER: S125R3DRP-H850D935-X4F0-XX-UDD-F-S

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.59	19.04	17.96	19.35	19.67	10.23	11.68	10.60	11.99	12.30
	3H	19.15	20.44	19.53	20.77	21.13	10.79	12.08	11.17	12.41	12.77
	4H	19.67	20.87	20.07	21.22	21.60	10.92	12.12	11.32	12.47	12.85
	6H	20.01	21.12	20.42	21.48	21.88	10.98	12.09	11.40	12.46	12.85
	8H	20.09	21.14	20.52	21.53	21.94	10.99	12.04	11.42	12.43	12.83
	12H	20.12	21.12	20.55	21.50	21.93	10.98	11.98	11.41	12.37	12.80
4H	2H	17.49	18.69	17.89	19.04	19.42	10.79	12.00	11.20	12.35	12.73
	3H	19.16	20.14	19.57	20.54	20.95	11.47	12.45	11.88	12.86	13.26
	4H	19.70	20.59	20.14	21.00	21.45	11.63	12.51	12.06	12.93	13.37
	6H	20.10	20.86	20.56	21.31	21.77	11.74	12.50	12.20	12.95	13.41
	8H	20.20	20.91	20.67	21.36	21.83	11.75	12.46	12.22	12.91	13.38
	12H	20.25	20.88	20.73	21.36	21.84	11.75	12.38	12.23	12.86	13.34
8H	4H	19.61	20.32	20.07	20.77	21.24	11.89	12.61	12.36	13.05	13.52
	6H	19.99	20.58	20.49	21.07	21.55	12.03	12.61	12.53	13.11	13.59
	8H	20.10	20.63	20.62	21.14	21.63	12.06	12.58	12.57	13.09	13.58
	12H	20.17	20.63	20.68	21.12	21.69	12.08	12.54	12.59	13.03	13.60
12H	4H	19.57	20.20	20.06	20.69	21.16	11.91	12.54	12.39	13.02	13.50
	6H	19.94	20.47	20.46	20.98	21.47	12.04	12.57	12.56	13.08	13.57
	8H	20.07	20.53	20.58	21.03	21.59	12.10	12.56	12.61	13.06	13.62