

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1058300

Luminaire Tested: S122RDRP-H290D840-X4F0-XX-UDD-WVL-S

Issue Date: 8/7/2025

**Test Information**

Test Method: LM-79-2024  
Report Number: P1058300  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2406-143-58)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/7/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S122RDRP-H290D840-X4F0-XX-UDD-WVL-S  
Description: DEFINE 2 SILVER REGRESSED DIRECT RECESSED HOUSING WITH WHITE STRAIGHT BLADE LOUVER WITH DIFFUSER  
HIGH PERFORMANCE LIGHT ENGINE  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 482.3 lumens  
Efficiency: N/A  
Efficacy: 41.2 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 1.05 / 1.05  
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1058300

CATALOG NUMBER: S122RDRP-H290D840-X4F0-XX-UDD-WVL-S

### Luminous Intensity Polar Plot





TEST NUMBER: P1058300

CATALOG NUMBER: S122RDRP-H290D840-X4F0-XX-UDD-WVL-S

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87
2	102	95	89	84	100	93	88	83	90	85	81	87	83	79	84	80	78	76
3	94	85	78	73	92	84	77	72	81	75	71	78	73	69	76	72	68	66
4	88	77	69	63	85	76	69	63	73	67	62	71	66	61	69	64	61	59
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52
6	76	64	56	50	74	63	56	50	61	55	50	60	54	49	58	53	49	47
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5466	5466	5466
5°	5294	5383	5453
10°	5035	5162	5372
15°	4698	4887	5223
20°	4338	4575	4921
25°	3948	4174	4585
30°	3535	3782	4276
35°	3079	3379	3951
40°	2599	3023	3551
45°	2064	2670	3108
50°	1777	2297	2578
55°	1618	1962	1979
60°	1476	1746	1683
65°	1349	1576	1485
70°	1252	1462	1322
75°	1162	1376	1162
80°	1095	1328	1052
85°	1101	1355	910

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 3108 cd/sqm

TEST NUMBER: P1058300

CATALOG NUMBER: S122RDRP-H290D840-X4F0-XX-UDD-WVL-S

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	27.3	5.7
10°-20°	72.3	15.0
20°-30°	95.1	19.7
30°-40°	95.6	19.8
40°-50°	77.5	16.1
50°-60°	53.4	11.1
60°-70°	34.9	7.2
70°-80°	19.5	4.0
80°-90°	6.6	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	194.7	40.4
0°-40°	290.4	60.2
0°-60°	421.3	87.3
0°-90°	482.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	482.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	296	296	296	296	296	
5°	286	291	291	292	294	27
15°	246	252	256	265	273	69
25°	194	199	205	214	225	89
35°	137	143	150	163	175	85
45°	79	88	102	111	119	63
55°	50	56	61	62	62	45
65°	31	37	36	34	34	31
75°	16	20	19	17	16	17
85°	5	7	6	6	4	6
90°	0	0	0	0	0	



TEST NUMBER: P1058300

CATALOG NUMBER: S122RDRP-H290D840-X4F0-XX-UDD-WVL-S

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	296.2	296.2	296.2	296.2	296.2
2.5°	292.3	297.5	294.4	294.4	294.9
5°	285.8	291.4	290.6	291.9	294.4
7.5°	277.7	283.7	283.7	287.6	291.0
10°	268.7	274.7	275.5	281.6	286.7
12.5°	257.5	263.5	266.1	273.8	280.7
15°	245.9	251.9	255.8	265.2	273.4
17.5°	233.4	239.4	244.6	254.5	262.6
20°	220.9	226.5	233.0	241.6	250.6
22.5°	207.2	213.2	219.2	227.4	237.7
25°	193.9	199.0	205.0	214.1	225.2
27.5°	179.7	185.3	190.9	201.6	213.2
30°	165.9	171.5	177.5	188.7	200.7
32.5°	151.3	157.3	163.3	175.8	188.3
35°	136.7	143.1	150.0	163.3	175.4
37.5°	122.5	129.4	137.6	151.3	161.6
40°	107.9	115.2	125.5	137.6	147.4
42.5°	92.4	101.4	113.9	124.2	133.3
45°	79.1	88.1	102.3	111.3	119.1
47.5°	69.2	76.5	90.3	98.0	104.5
50°	61.9	67.5	80.0	85.5	89.8
52.5°	55.9	61.5	70.1	73.9	75.2
55°	50.3	55.9	61.0	62.3	61.5
57.5°	44.7	50.7	53.7	52.4	52.4
60°	40.0	46.4	47.3	45.6	45.6
62.5°	35.2	41.7	41.7	39.5	39.5
65°	30.9	37.0	36.1	34.4	34.0
67.5°	27.1	32.7	31.4	29.7	29.2
70°	23.2	28.4	27.1	24.9	24.5
72.5°	19.8	24.5	22.8	21.1	20.2
75°	16.3	20.2	19.3	17.2	16.3
77.5°	13.3	16.3	15.5	13.8	12.9
80°	10.3	12.9	12.5	10.7	9.9
82.5°	7.7	9.9	9.5	8.2	6.9
85°	5.2	6.9	6.4	5.6	4.3
87.5°	2.6	4.7	4.3	3.9	2.1
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1058300  
 CATALOG NUMBER: S122RDRP-H290D840-X4F0-XX-UDD-WVL-S

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.63	14.07	12.99	14.38	14.70	12.98	14.43	13.35	14.74	15.05
	3H	14.17	15.46	14.55	15.79	16.16	14.33	15.62	14.71	15.95	16.31
	4H	14.74	15.95	15.15	16.30	16.68	14.81	16.02	15.22	16.37	16.75
	6H	15.17	16.29	15.59	16.66	17.05	15.17	16.29	15.58	16.65	17.05
	8H	15.33	16.39	15.75	16.78	17.18	15.29	16.35	15.71	16.74	17.14
	12H	15.44	16.46	15.87	16.84	17.27	15.36	16.38	15.79	16.76	17.19
4H	2H	13.21	14.42	13.61	14.77	15.15	13.50	14.71	13.90	15.06	15.44
	3H	15.04	16.04	15.45	16.44	16.84	15.07	16.08	15.49	16.48	16.88
	4H	15.79	16.69	16.22	17.10	17.54	15.68	16.58	16.11	17.00	17.44
	6H	16.37	17.15	16.83	17.60	18.06	16.16	16.94	16.62	17.39	17.85
	8H	16.58	17.31	17.04	17.76	18.22	16.33	17.06	16.79	17.50	17.97
	12H	16.75	17.40	17.23	17.88	18.35	16.45	17.10	16.93	17.58	18.05
8H	4H	16.07	16.80	16.53	17.25	17.71	15.98	16.71	16.45	17.16	17.63
	6H	16.83	17.43	17.32	17.92	18.40	16.60	17.20	17.10	17.70	18.17
	8H	17.15	17.69	17.66	18.20	18.69	16.85	17.39	17.37	17.90	18.39
	12H	17.44	17.92	17.95	18.41	18.97	17.06	17.54	17.57	18.03	18.60
12H	4H	16.09	16.74	16.57	17.22	17.69	16.02	16.67	16.50	17.15	17.62
	6H	16.89	17.43	17.40	17.94	18.43	16.68	17.22	17.19	17.73	18.22
	8H	17.28	17.76	17.80	18.26	18.82	17.00	17.48	17.51	17.97	18.54