

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1058585

Luminaire Tested: S122RDRP-H865D940-X4F0-XX-UDD-SVL-S

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2024
Report Number: P1058585
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2406-143-59)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDRP-H865D940-X4F0-XX-UDD-SVL-S
Description: DEFINE 2 SILVER REGRESSED DIRECT RECESSED HOUSING WITH SILVER STRAIGHT BLADE LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 714.2 lumens
Efficiency: N/A
Efficacy: 22.9 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.97 / 0.94
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1058585

CATALOG NUMBER: S122RDRP-H865D940-X4F0-XX-UDD-SVL-S

Luminous Intensity Polar Plot





TEST NUMBER: P1058585

CATALOG NUMBER: S122RDRP-H865D940-X4F0-XX-UDD-SVL-S

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89
2	104	98	93	88	102	96	91	87	93	89	85	90	86	83	87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76	82	78	75	80	77	74	72
4	91	82	75	70	89	81	74	69	78	73	68	76	71	68	74	70	67	65
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54
7	76	65	57	52	74	64	57	52	62	56	52	61	56	52	60	55	51	50
8	71	60	53	48	70	59	53	48	58	52	48	57	52	48	56	51	47	46
9	67	56	49	45	66	56	49	44	55	49	44	54	48	44	53	48	44	42
10	64	53	46	41	63	52	46	41	51	45	41	50	45	41	50	45	41	39

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10924	10924	10924
5°	10541	10723	10866
10°	9824	10172	10622
15°	8952	9431	10182
20°	7957	8558	9394
25°	6894	7517	8517
30°	5772	6448	7658
35°	4553	5339	6742
40°	3262	4367	5526
45°	1910	3450	4274
50°	1381	2509	2885
55°	1158	1792	1512
60°	926	1450	1292
65°	764	1288	1192
70°	647	1235	1122
75°	620	1326	1091
80°	701	1626	1158
85°	1164	2541	1609

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 4274 cd/sqm



TEST NUMBER: P1058585

CATALOG NUMBER: S122RDRP-H865D940-X4F0-XX-UDD-SVL-S

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.3	7.6
10°-20°	139.0	19.5
20°-30°	170.8	23.9
30°-40°	151.0	21.1
40°-50°	96.4	13.5
50°-60°	47.0	6.6
60°-70°	28.0	3.9
70°-80°	17.9	2.5
80°-90°	9.8	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	364.0	51.0
0°-40°	515.0	72.1
0°-60°	658.4	92.2
0°-90°	714.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	714.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	592	592	592	592	592	
5°	569	581	579	581	587	53
15°	469	482	494	516	533	131
25°	339	351	369	392	418	155
35°	202	213	237	270	299	125
45°	73	94	132	149	164	62
55°	36	48	56	52	47	32
65°	18	33	30	27	27	18
75°	9	20	19	16	15	10
85°	6	11	12	11	8	5
90°	0	0	0	0	0	



TEST NUMBER: P1058585

CATALOG NUMBER: S122RDRP-H865D940-X4F0-XX-UDD-SVL-S

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	592.0	592.0	592.0	592.0	592.0
2.5°	583.3	594.2	587.7	587.7	588.7
5°	569.1	581.1	578.9	581.1	586.6
7.5°	549.4	561.4	563.6	572.4	578.9
10°	524.3	536.3	542.9	557.1	566.9
12.5°	498.1	510.1	519.9	538.5	552.7
15°	468.6	481.7	493.7	515.6	533.0
17.5°	438.0	451.1	466.4	488.3	509.0
20°	405.2	417.3	435.8	456.6	478.4
22.5°	373.6	384.5	404.1	423.8	450.0
25°	338.6	350.6	369.2	392.1	418.3
27.5°	304.7	316.8	335.3	361.5	388.9
30°	270.9	281.8	302.6	329.9	359.4
32.5°	235.9	246.9	269.8	299.3	329.9
35°	202.1	213.0	237.0	269.8	299.3
37.5°	168.2	180.2	207.5	238.1	263.2
40°	135.4	149.6	181.3	207.5	229.4
42.5°	102.7	122.3	156.2	178.0	195.5
45°	73.2	93.9	132.2	148.6	163.8
47.5°	55.7	72.1	109.2	121.2	131.1
50°	48.1	59.0	87.4	96.1	100.5
52.5°	41.5	52.4	69.9	73.2	71.0
55°	36.0	48.1	55.7	52.4	47.0
57.5°	30.6	44.8	45.9	39.3	40.4
60°	25.1	40.4	39.3	33.9	35.0
62.5°	20.8	37.1	33.9	30.6	30.6
65°	17.5	32.8	29.5	27.3	27.3
67.5°	14.2	29.5	26.2	24.0	24.0
70°	12.0	26.2	22.9	20.8	20.8
72.5°	10.9	22.9	20.8	18.6	18.6
75°	8.7	19.7	18.6	16.4	15.3
77.5°	7.6	16.4	16.4	15.3	13.1
80°	6.6	14.2	15.3	13.1	10.9
82.5°	6.6	13.1	13.1	12.0	8.7
85°	5.5	10.9	12.0	10.9	7.6
87.5°	3.3	9.8	9.8	8.7	5.5
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1058585
 CATALOG NUMBER: S122RDRP-H865D940-X4F0-XX-UDD-SVL-S

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.34	11.62	10.70	11.93	12.24	9.86	11.14	10.22	11.45	11.76
	3H	11.51	12.65	11.89	12.98	13.35	11.42	12.56	11.80	12.89	13.26
	4H	11.94	13.00	12.34	13.35	13.74	12.11	13.17	12.51	13.52	13.90
	6H	12.29	13.26	12.70	13.63	14.03	12.75	13.73	13.17	14.10	14.50
	8H	12.48	13.41	12.91	13.80	14.21	13.04	13.97	13.47	14.36	14.76
	12H	12.71	13.59	13.14	13.97	14.40	13.35	14.24	13.79	14.62	15.05
4H	2H	10.84	11.90	11.24	12.25	12.64	10.46	11.52	10.86	11.87	12.26
	3H	12.48	13.36	12.90	13.76	14.17	12.26	13.14	12.67	13.54	13.94
	4H	13.25	14.03	13.68	14.45	14.90	13.10	13.89	13.54	14.31	14.75
	6H	13.85	14.53	14.31	14.98	15.44	13.96	14.64	14.42	15.08	15.55
	8H	14.15	14.79	14.62	15.23	15.71	14.35	14.98	14.82	15.43	15.90
	12H	14.47	15.03	14.95	15.51	15.99	14.78	15.34	15.27	15.83	16.30
8H	4H	13.67	14.30	14.14	14.75	15.22	13.56	14.20	14.03	14.65	15.12
	6H	14.62	15.14	15.12	15.63	16.12	14.67	15.19	15.17	15.69	16.17
	8H	15.16	15.63	15.68	16.15	16.64	15.25	15.71	15.77	16.23	16.72
	12H	15.73	16.14	16.24	16.64	17.21	15.91	16.33	16.43	16.82	17.39
12H	4H	13.74	14.30	14.22	14.78	15.26	13.65	14.21	14.13	14.69	15.17
	6H	14.80	15.27	15.32	15.78	16.28	14.85	15.32	15.38	15.84	16.33
	8H	15.49	15.91	16.01	16.40	16.97	15.56	15.98	16.08	16.47	17.04