

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1058545

Luminaire Tested: S122RDRP-H865D850-X4F0-XX-UDD-BVL-B

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2024
Report Number: P1058545
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2406-143-21)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDRP-H865D850-X4F0-XX-UDD-BVL-B
Description: DEFINE 2 BLACK REGRESSED DIRECT RECESSED HOUSING WITH BLACK STRAIGHT BLADE LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 5000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 603.5 lumens
Efficiency: N/A
Efficacy: 19.3 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.8 / 0.88
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1058545

CATALOG NUMBER: S122RDRP-H865D850-X4F0-XX-UDD-BVL-B

Luminous Intensity Polar Plot





TEST NUMBER: P1058545

CATALOG NUMBER: S122RDRP-H865D850-X4F0-XX-UDD-BVL-B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93					93			
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86					86			
3	101	95	90	85	99	93	89	85	91	87	83	88	85	82	86	83	81	79					79			
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73					73			
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67					67			
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62					62			
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58					58			
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	56	54					54			
9	73	63	57	53	72	62	57	52	61	56	52	61	56	52	60	55	52	51					51			
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47					47			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11841	11841	11841
5°	11760	11584	11636
10°	11516	11032	10753
15°	10834	10083	9668
20°	9671	8952	8446
25°	8453	7568	7181
30°	7255	6185	5781
35°	6051	4830	4341
40°	4707	3563	2777
45°	3293	2372	1203
50°	1791	1246	428
55°	261	438	306
60°	52	100	199
65°	0	61	118
70°	0	0	76
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3293 cd/sqm



TEST NUMBER: P1058545

CATALOG NUMBER: S122RDRP-H865D850-X4F0-XX-UDD-BVL-B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.9	9.8
10°-20°	148.6	24.6
20°-30°	173.2	28.7
30°-40°	138.8	23.0
40°-50°	69.0	11.4
50°-60°	13.6	2.3
60°-70°	1.2	0.2
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	380.7	63.1
0°-40°	519.6	86.1
0°-60°	602.1	99.8
0°-90°	603.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	603.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	642	642	642	642	642	
5°	635	635	625	627	628	60
15°	567	556	528	514	506	157
25°	415	395	372	364	353	191
35°	269	242	214	205	193	167
45°	126	111	91	61	46	97
55°	8	16	14	8	10	16
65°	0	0	1	1	3	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1058545

CATALOG NUMBER: S122RDRP-H865D850-X4F0-XX-UDD-BVL-B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	641.7	641.7	641.7	641.7	641.7
2.5°	639.0	641.7	634.9	641.7	643.1
5°	634.9	634.9	625.4	626.8	628.2
7.5°	628.2	625.4	609.2	606.4	603.7
10°	614.6	609.2	588.8	578.0	573.9
12.5°	595.6	587.5	560.3	548.1	541.3
15°	567.1	556.2	527.8	514.2	506.1
17.5°	530.5	521.0	493.8	478.9	470.8
20°	492.5	478.9	455.9	440.9	430.1
22.5°	455.9	438.2	413.8	402.9	392.1
25°	415.2	394.8	371.7	363.6	352.7
27.5°	381.2	355.5	328.3	322.9	313.4
30°	340.5	316.1	290.3	282.2	271.3
32.5°	305.3	278.1	252.3	242.8	233.4
35°	268.6	241.5	214.4	204.9	192.7
37.5°	233.4	207.6	180.4	165.5	154.7
40°	195.4	173.7	147.9	128.9	115.3
42.5°	161.4	142.5	118.0	93.6	80.0
45°	126.2	111.2	90.9	61.1	46.1
47.5°	93.6	82.8	66.5	35.3	24.4
50°	62.4	58.3	43.4	17.6	14.9
52.5°	33.9	36.6	25.8	10.9	12.2
55°	8.1	16.3	13.6	8.1	9.5
57.5°	1.4	2.7	6.8	6.8	6.8
60°	1.4	1.4	2.7	4.1	5.4
62.5°	1.4	0.0	1.4	2.7	4.1
65°	0.0	0.0	1.4	1.4	2.7
67.5°	0.0	0.0	0.0	1.4	1.4
70°	0.0	0.0	0.0	1.4	1.4
72.5°	0.0	0.0	0.0	0.0	1.4
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1058545
 CATALOG NUMBER: S122RDRP-H865D850-X4F0-XX-UDD-BVL-B

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.06
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.10
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00