

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1058347

Luminaire Tested: S122RDRP-H290D950-X4F0-XX-UDD-BVL-B

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2024
Report Number: P1058347
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2406-143-21)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDRP-H290D950-X4F0-XX-UDD-BVL-B
Description: DEFINE 2 BLACK REGRESSED DIRECT RECESSED HOUSING WITH BLACK STRAIGHT BLADE LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 5000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 180.5 lumens
Efficiency: N/A
Efficacy: 15.4 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.8 / 0.88
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1058347

CATALOG NUMBER: S122RDRP-H290D950-X4F0-XX-UDD-BVL-B

Luminous Intensity Polar Plot





TEST NUMBER: P1058347

CATALOG NUMBER: S122RDRP-H290D950-X4F0-XX-UDD-BVL-B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86
3	101	95	90	85	99	93	89	85	91	87	83	88	85	82	86	83	81	79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	63
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	56	54
9	73	63	57	53	72	62	57	52	61	56	52	61	56	52	60	55	52	51
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3541	3541	3541
5°	3518	3466	3480
10°	3444	3300	3215
15°	3240	3015	2892
20°	2892	2676	2525
25°	2529	2264	2148
30°	2169	1849	1730
35°	1809	1444	1298
40°	1407	1065	831
45°	984	710	360
50°	537	373	129
55°	77	132	90
60°	15	30	59
65°	0	17	35
70°	0	0	22
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 984 cd/sqm



TEST NUMBER: P1058347

CATALOG NUMBER: S122RDRP-H290D950-X4F0-XX-UDD-BVL-B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.6	9.8
10°-20°	44.4	24.6
20°-30°	51.8	28.7
30°-40°	41.5	23.0
40°-50°	20.6	11.4
50°-60°	4.1	2.3
60°-70°	0.4	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	113.9	63.1
0°-40°	155.4	86.1
0°-60°	180.1	99.8
0°-90°	180.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	180.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	192	192	192	192	192	
5°	190	190	187	188	188	18
15°	170	166	158	154	151	47
25°	124	118	111	109	106	57
35°	80	72	64	61	58	50
45°	38	33	27	18	14	29
55°	2	5	4	2	3	5
65°	0	0	0	0	1	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1058347

CATALOG NUMBER: S122RDRP-H290D950-X4F0-XX-UDD-BVL-B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	191.9	191.9	191.9	191.9	191.9
2.5°	191.1	191.9	189.9	191.9	192.3
5°	189.9	189.9	187.1	187.5	187.9
7.5°	187.9	187.1	182.2	181.4	180.6
10°	183.8	182.2	176.1	172.9	171.6
12.5°	178.1	175.7	167.6	163.9	161.9
15°	169.6	166.4	157.8	153.8	151.4
17.5°	158.7	155.8	147.7	143.2	140.8
20°	147.3	143.2	136.3	131.9	128.6
22.5°	136.3	131.1	123.8	120.5	117.3
25°	124.2	118.1	111.2	108.7	105.5
27.5°	114.0	106.3	98.2	96.6	93.7
30°	101.8	94.5	86.8	84.4	81.2
32.5°	91.3	83.2	75.5	72.6	69.8
35°	80.3	72.2	64.1	61.3	57.6
37.5°	69.8	62.1	54.0	49.5	46.3
40°	58.4	51.9	44.2	38.5	34.5
42.5°	48.3	42.6	35.3	28.0	23.9
45°	37.7	33.3	27.2	18.3	13.8
47.5°	28.0	24.8	19.9	10.5	7.3
50°	18.7	17.4	13.0	5.3	4.5
52.5°	10.1	11.0	7.7	3.2	3.7
55°	2.4	4.9	4.1	2.4	2.8
57.5°	0.4	0.8	2.0	2.0	2.0
60°	0.4	0.4	0.8	1.2	1.6
62.5°	0.4	0.0	0.4	0.8	1.2
65°	0.0	0.0	0.4	0.4	0.8
67.5°	0.0	0.0	0.0	0.4	0.4
70°	0.0	0.0	0.0	0.4	0.4
72.5°	0.0	0.0	0.0	0.0	0.4
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1058347
 CATALOG NUMBER: S122RDRP-H290D950-X4F0-XX-UDD-BVL-B

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00