

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1062112

Luminaire Tested: S125RDRP-H610D850-X4F0-XX-UDD-SVL-B

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2024
Report Number: P1062112
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2406-143-47)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDRP-H610D850-X4F0-XX-UDD-SVL-B
Description: DEFINE 5 BLACK REGRESSED DIRECT RECESSED HOUSING WITH SILVER STRAIGHT BLADE LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 5000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 840.4 lumens
Efficiency: N/A
Efficacy: 48.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular (W 0.39' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 17.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1062112

CATALOG NUMBER: S125RDRP-H610D850-X4F0-XX-UDD-SVL-B

Luminous Intensity Polar Plot





TEST NUMBER: P1062112

CATALOG NUMBER: S125RDRP-H610D850-X4F0-XX-UDD-SVL-B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90
2	104	98	93	88	102	96	91	87	93	89	85	90	86	83	87	84	82	80
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71
4	90	81	74	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	53	52
7	74	62	55	50	72	62	55	50	60	54	49	59	53	49	58	53	49	47
8	69	58	50	45	68	57	50	45	56	50	45	55	49	45	54	48	45	43
9	65	54	47	42	64	53	46	42	52	46	41	51	45	41	50	45	41	39
10	62	50	43	38	61	50	43	38	49	43	38	48	42	38	47	42	38	36

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4001	4001	4001
5°	3996	3929	3929
10°	3965	3779	3681
15°	3910	3568	3374
20°	3825	3311	3030
25°	3719	3018	2631
30°	3581	2694	2219
35°	3432	2359	1800
40°	3265	1991	1334
45°	3070	1596	805
50°	2840	1171	554
55°	2562	718	461
60°	2176	487	366
65°	1720	373	288
70°	1085	268	238
75°	354	197	197
80°	119	147	174
85°	55	118	118

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3070 cd/sqm



TEST NUMBER: P1062112

CATALOG NUMBER: S125RDRP-H610D850-X4F0-XX-UDD-SVL-B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.7	6.4
10°-20°	141.9	16.9
20°-30°	186.7	22.2
30°-40°	183.4	21.8
40°-50°	138.8	16.5
50°-60°	84.1	10.0
60°-70°	39.7	4.7
70°-80°	10.4	1.2
80°-90°	1.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	382.4	45.5
0°-40°	565.8	67.3
0°-60°	788.7	93.9
0°-90°	840.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	840.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	581	581	581	581	581	
5°	578	577	568	569	568	55
15°	549	534	501	481	473	155
25°	490	453	397	360	346	225
35°	408	354	281	231	214	255
45°	315	248	164	104	83	243
55°	213	146	60	41	38	190
65°	106	54	23	19	18	104
75°	13	9	7	7	7	21
85°	1	1	2	2	2	1
90°	0	0	0	0	0	



TEST NUMBER: P1062112

CATALOG NUMBER: S125RDRP-H610D850-X4F0-XX-UDD-SVL-B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	581.1	581.1	581.1	581.1	581.1
2.5°	580.4	580.4	575.9	581.1	581.1
5°	578.1	576.7	568.5	569.3	568.5
7.5°	573.7	570.8	556.7	553.0	550.1
10°	567.1	561.2	540.5	531.6	526.5
12.5°	559.7	549.4	521.3	508.7	500.6
15°	548.6	533.8	500.6	481.4	473.3
17.5°	536.8	515.4	476.3	453.4	443.0
20°	522.0	496.9	451.9	423.8	413.5
22.5°	505.8	476.3	423.8	392.8	378.8
25°	489.5	452.6	397.2	360.3	346.3
27.5°	471.1	429.0	367.0	328.6	313.1
30°	450.4	405.4	338.9	299.0	279.1
32.5°	429.7	381.0	309.4	265.8	245.9
35°	408.3	353.7	280.6	231.1	214.1
37.5°	385.4	327.8	251.0	199.4	179.4
40°	363.3	302.0	221.5	166.9	148.4
42.5°	339.7	276.2	192.0	135.1	114.4
45°	315.3	248.1	163.9	104.1	82.7
47.5°	290.2	223.0	135.9	76.8	62.0
50°	265.1	196.4	109.3	56.9	51.7
52.5°	239.2	170.6	82.7	47.3	45.0
55°	213.4	146.2	59.8	40.6	38.4
57.5°	186.8	119.6	45.0	34.7	32.5
60°	158.0	96.0	35.4	28.8	26.6
62.5°	131.4	75.3	28.8	23.6	22.2
65°	105.6	53.9	22.9	19.2	17.7
67.5°	79.0	36.2	17.7	14.8	14.8
70°	53.9	23.6	13.3	11.8	11.8
72.5°	32.5	14.0	9.6	9.6	9.6
75°	13.3	8.9	7.4	7.4	7.4
77.5°	4.4	5.2	5.2	5.9	5.9
80°	3.0	3.0	3.7	4.4	4.4
82.5°	1.5	2.2	2.2	3.0	3.0
85°	0.7	0.7	1.5	1.5	1.5
87.5°	0.0	0.0	0.0	0.7	0.7
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1062112
 CATALOG NUMBER: S125RDRP-H610D850-X4F0-XX-UDD-SVL-B

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.15	15.48	14.51	15.79	16.10	4.80	6.13	5.17	6.45	6.76
	3H	14.85	16.03	15.23	16.36	16.72	5.58	6.76	5.96	7.09	7.46
	4H	14.87	15.96	15.27	16.31	16.70	5.83	6.93	6.24	7.28	7.66
	6H	14.80	15.80	15.21	16.17	16.57	6.01	7.02	6.43	7.39	7.78
	8H	14.76	15.71	15.19	16.10	16.51	6.06	7.01	6.49	7.40	7.81
	12H	14.72	15.63	15.15	16.01	16.44	6.07	6.98	6.50	7.36	7.79
4H	2H	13.98	15.07	14.38	15.42	15.81	5.29	6.39	5.69	6.74	7.12
	3H	14.72	15.61	15.14	16.02	16.42	6.20	7.09	6.61	7.49	7.90
	4H	14.74	15.54	15.18	15.96	16.40	6.51	7.31	6.95	7.73	8.17
	6H	14.68	15.36	15.14	15.81	16.28	6.77	7.45	7.23	7.90	8.37
	8H	14.63	15.27	15.10	15.71	16.19	6.84	7.48	7.31	7.92	8.39
	12H	14.58	15.15	15.07	15.63	16.11	6.86	7.43	7.35	7.91	8.38
8H	4H	14.62	15.26	15.09	15.71	16.18	6.63	7.26	7.09	7.71	8.18
	6H	14.55	15.07	15.05	15.57	16.05	6.94	7.46	7.44	7.96	8.44
	8H	14.50	14.96	15.02	15.48	15.97	7.05	7.51	7.57	8.03	8.52
	12H	14.45	14.87	14.97	15.36	15.93	7.11	7.53	7.63	8.02	8.59
12H	4H	14.58	15.14	15.07	15.63	16.10	6.60	7.16	7.08	7.64	8.12
	6H	14.49	14.96	15.01	15.47	15.97	6.91	7.38	7.43	7.89	8.39
	8H	14.46	14.87	14.97	15.36	15.93	7.05	7.47	7.57	7.96	8.53