

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1062196

Luminaire Tested: S125RDRP-H850D850-X4F0-XX-UDD-WVL-B

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2024
Report Number: P1062196
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2406-143-46)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDRP-H850D850-X4F0-XX-UDD-WVL-B
Description: DEFINE 5 BLACK REGRESSED DIRECT RECESSED HOUSING WITH WHITE STRAIGHT BLADE
LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 5000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1804.1 lumens
Efficiency: N/A
Efficacy: 76.8 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 0.95 / 1.11
Luminous Opening: Rectangular (W 0.39' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 23.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1062196

CATALOG NUMBER: S125RDRP-H850D850-X4F0-XX-UDD-WVL-B

Luminous Intensity Polar Plot





TEST NUMBER: P1062196

CATALOG NUMBER: S125RDRP-H850D850-X4F0-XX-UDD-WVL-B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	80	77	75
3	93	84	77	71	91	82	76	70	80	74	69	77	72	68	74	70	67	65
4	86	75	68	61	84	74	67	61	72	65	60	70	64	59	67	63	59	57
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50
6	74	62	54	48	73	61	53	48	59	53	47	58	52	47	56	51	47	45
7	69	57	49	43	68	56	48	43	55	48	43	53	47	42	52	46	42	40
8	65	52	44	39	63	52	44	39	50	43	39	49	43	38	48	42	38	36
9	61	48	41	35	60	48	40	35	47	40	35	46	39	35	45	39	35	33
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	42	36	32	30

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6558	6558	6558
5°	6554	6454	6468
10°	6529	6254	6159
15°	6464	6008	5801
20°	6349	5713	5394
25°	6190	5373	4965
30°	6034	4990	4489
35°	5832	4606	3981
40°	5642	4201	3430
45°	5407	3756	2809
50°	5173	3256	2459
55°	4853	2719	2271
60°	4429	2378	2122
65°	3874	2173	1971
70°	3142	1957	1832
75°	2256	1788	1705
80°	1558	1598	1598
85°	1145	1390	1469

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5407 cd/sqm



TEST NUMBER: P1062196

CATALOG NUMBER: S125RDRP-H850D850-X4F0-XX-UDD-WVL-B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.5	4.9
10°-20°	239.5	13.3
20°-30°	331.0	18.3
30°-40°	352.6	19.5
40°-50°	309.7	17.2
50°-60°	234.9	13.0
60°-70°	152.5	8.5
70°-80°	75.6	4.2
80°-90°	19.8	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	659.1	36.5
0°-40°	1011.7	56.1
0°-60°	1556.3	86.3
0°-90°	1804.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1804.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	952	952	952	952	952	
5°	948	946	934	937	936	90
15°	907	886	843	823	814	255
25°	815	770	707	671	654	375
35°	694	630	548	498	474	434
45°	555	478	386	316	288	428
55°	404	325	226	195	189	361
65°	238	177	133	123	121	235
75°	85	74	67	65	64	95
85°	14	16	18	18	19	18
90°	0	0	0	0	0	



TEST NUMBER: P1062196

CATALOG NUMBER: S125RDRP-H850D850-X4F0-XX-UDD-WVL-B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	952.4	952.4	952.4	952.4	952.4
2.5°	950.3	952.4	944.1	951.3	953.4
5°	948.2	946.2	933.8	936.9	935.8
7.5°	942.0	937.9	917.2	915.1	911.0
10°	933.8	923.4	894.5	887.2	881.0
12.5°	922.4	905.8	870.7	856.2	849.0
15°	906.9	886.2	842.8	823.1	813.8
17.5°	888.3	859.3	813.8	786.9	776.6
20°	866.5	832.4	779.7	748.7	736.2
22.5°	842.8	802.4	743.5	710.4	697.0
25°	814.8	770.4	707.3	671.1	653.5
27.5°	786.9	737.3	669.0	628.7	610.1
30°	759.0	702.1	627.7	584.2	564.6
32.5°	729.0	665.9	589.4	541.8	519.1
35°	693.9	629.7	548.0	498.4	473.6
37.5°	659.7	591.5	507.7	451.9	428.1
40°	627.7	555.3	467.4	406.4	381.6
42.5°	591.5	517.0	427.1	363.0	335.0
45°	555.3	477.7	385.7	316.4	288.5
47.5°	517.0	440.5	342.3	274.0	255.4
50°	482.9	402.2	304.0	242.0	229.6
52.5°	443.6	365.0	264.7	217.2	208.9
55°	404.3	324.7	226.5	195.4	189.2
57.5°	364.0	288.5	196.5	176.8	170.6
60°	321.6	251.3	172.7	157.2	154.1
62.5°	279.2	213.0	152.0	140.6	136.5
65°	237.8	176.8	133.4	123.1	121.0
67.5°	195.4	143.7	114.8	107.5	106.5
70°	156.1	116.8	97.2	93.1	91.0
72.5°	120.0	93.1	81.7	78.6	77.6
75°	84.8	74.5	67.2	65.1	64.1
77.5°	56.9	56.9	53.8	51.7	52.7
80°	39.3	41.4	40.3	40.3	40.3
82.5°	25.9	27.9	29.0	29.0	29.0
85°	14.5	16.5	17.6	17.6	18.6
87.5°	5.2	6.2	7.2	8.3	8.3
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1062196
 CATALOG NUMBER: S125RDRP-H850D850-X4F0-XX-UDD-WVL-B

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.09	18.58	17.45	18.89	19.21	13.33	14.82	13.69	15.13	15.45
	3H	18.40	19.73	18.78	20.06	20.42	14.91	16.25	15.29	16.58	16.94
	4H	18.77	20.02	19.17	20.37	20.75	15.51	16.77	15.91	17.12	17.49
	6H	18.94	20.10	19.36	20.47	20.86	15.98	17.14	16.40	17.51	17.90
	8H	18.98	20.08	19.41	20.47	20.87	16.15	17.25	16.57	17.64	18.04
	12H	18.99	20.05	19.42	20.43	20.86	16.26	17.31	16.69	17.69	18.12
4H	2H	17.20	18.45	17.60	18.80	19.18	13.99	15.24	14.39	15.59	15.97
	3H	18.69	19.72	19.10	20.12	20.53	15.77	16.81	16.18	17.21	17.61
	4H	19.16	20.09	19.59	20.51	20.95	16.49	17.42	16.92	17.84	18.28
	6H	19.45	20.26	19.91	20.70	21.16	17.08	17.89	17.54	18.33	18.79
	8H	19.52	20.27	19.98	20.72	21.19	17.28	18.04	17.75	18.48	18.95
	12H	19.56	20.23	20.04	20.71	21.18	17.44	18.11	17.92	18.59	19.06
8H	4H	19.24	20.00	19.71	20.45	20.91	16.80	17.56	17.26	18.00	18.47
	6H	19.61	20.23	20.11	20.72	21.20	17.51	18.13	18.00	18.62	19.10
	8H	19.72	20.28	20.24	20.80	21.28	17.79	18.35	18.30	18.86	19.35
	12H	19.81	20.31	20.32	20.80	21.36	18.02	18.51	18.53	19.00	19.57
12H	4H	19.24	19.91	19.72	20.39	20.86	16.83	17.50	17.31	17.98	18.45
	6H	19.61	20.17	20.13	20.68	21.17	17.56	18.12	18.07	18.63	19.12
	8H	19.77	20.27	20.28	20.76	21.32	17.89	18.39	18.40	18.88	19.45