

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1055685

Luminaire Tested: S123R3DRP-H1000D830-X4F0-XX-UDD-F-W

Issue Date: 7/25/2025

Test Information

Test Method: LM-79-2024
Report Number: P1055685
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2503-402-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/25/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123R3DRP-H1000D830-X4F0-XX-UDD-F-W
Description: DEFINE 3, WHITE 3-INCH REGRESSED DIRECT RECESSED HOUSING WITH FROSTED LENS
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2760.1 lumens
Efficiency: N/A
Efficacy: 89.3 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 0.83 / 1.02
Luminous Opening: Rectangular (W 0.23' x L: 3.9' x H: 0')
CIE Type: Direct

Input Watts (W): 30.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1055685

CATALOG NUMBER: S123R3DRP-H1000D830-X4F0-XX-UDD-F-W

Luminous Intensity Polar Plot





TEST NUMBER: P1055685

CATALOG NUMBER: S123R3DRP-H1000D830-X4F0-XX-UDD-F-W

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86
2	101	94	88	83	99	92	87	82	89	84	80	85	82	78	83	79	76	74
3	93	84	77	71	91	82	76	70	80	74	69	77	72	68	74	70	67	65
4	86	75	68	61	84	74	67	61	72	65	60	70	64	59	67	63	59	57
5	80	68	60	54	78	67	60	54	65	58	53	63	57	53	62	56	52	50
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	39	37
9	61	49	41	36	60	48	41	36	47	40	36	46	40	35	45	39	35	34
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18974	18974	18974
5°	18805	18761	18719
10°	18690	18056	17567
15°	18468	17101	16044
20°	18198	15872	14105
25°	17882	14453	12135
30°	17485	12929	10259
35°	17064	11435	8662
40°	16636	9986	7281
45°	16136	8610	6423
50°	15632	7330	5895
55°	15168	6533	5444
60°	14533	5903	5081
65°	13936	5406	4767
70°	12986	4981	4480
75°	11622	4607	4220
80°	9970	4249	3923
85°	7000	3915	3749

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16136 cd/sqm



TEST NUMBER: P1055685

CATALOG NUMBER: S123R3DRP-H1000D830-X4F0-XX-UDD-F-W

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.9	5.3
10°-20°	386.0	14.0
20°-30°	508.4	18.4
30°-40°	516.1	18.7
40°-50°	448.6	16.3
50°-60°	351.4	12.7
60°-70°	238.8	8.7
70°-80°	129.4	4.7
80°-90°	35.6	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1040.3	37.7
0°-40°	1556.4	56.4
0°-60°	2356.4	85.4
0°-90°	2760.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2760.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1574	1574	1574	1574	1574	
5°	1554	1573	1550	1536	1547	148
15°	1480	1458	1370	1303	1285	417
25°	1344	1263	1086	951	912	619
35°	1159	1022	777	629	588	725
45°	946	759	505	390	377	730
55°	722	501	311	265	259	644
65°	488	271	190	170	167	482
75°	250	125	99	92	91	266
85°	51	31	28	26	27	64
90°	0	0	0	0	0	



TEST NUMBER: P1055685

CATALOG NUMBER: S123R3DRP-H1000D830-X4F0-XX-UDD-F-W

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1573.8	1573.8	1573.8	1573.8	1573.8
2.5°	1560.8	1580.8	1565.5	1566.7	1571.4
5°	1553.8	1572.6	1550.2	1536.1	1546.7
7.5°	1543.2	1557.3	1516.1	1493.7	1497.3
10°	1526.7	1531.4	1474.9	1439.6	1434.9
12.5°	1504.3	1496.1	1425.5	1373.7	1365.4
15°	1479.6	1458.4	1370.1	1303.0	1285.4
17.5°	1451.4	1416.0	1305.4	1223.0	1195.9
20°	1418.4	1369.0	1237.1	1132.4	1099.4
22.5°	1383.1	1319.5	1163.0	1039.4	1005.2
25°	1344.2	1263.0	1086.5	951.1	912.2
27.5°	1301.9	1206.5	1008.8	864.0	820.4
30°	1256.0	1147.7	928.7	779.2	736.9
32.5°	1208.9	1085.3	852.2	700.4	659.2
35°	1159.4	1021.7	776.9	628.6	588.5
37.5°	1108.8	957.0	703.9	560.3	522.6
40°	1057.0	891.1	634.5	496.7	462.6
42.5°	1001.7	825.1	567.4	436.7	410.8
45°	946.4	759.2	505.0	389.6	376.7
47.5°	891.1	692.1	446.1	356.7	344.9
50°	833.4	627.4	390.8	326.1	314.3
52.5°	776.9	563.8	344.9	296.6	288.4
55°	721.6	501.4	310.8	264.8	259.0
57.5°	663.9	440.2	276.6	240.1	233.1
60°	602.7	381.4	244.8	214.2	210.7
62.5°	547.3	326.1	216.6	191.9	188.3
65°	488.5	270.7	189.5	169.5	167.1
67.5°	428.5	224.8	164.8	148.3	147.1
70°	368.4	189.5	141.3	128.3	127.1
72.5°	309.6	156.6	118.9	110.6	108.3
75°	249.5	124.8	98.9	91.8	90.6
77.5°	195.4	96.5	78.9	74.2	73.0
80°	143.6	71.8	61.2	57.7	56.5
82.5°	94.2	49.4	43.6	41.2	41.2
85°	50.6	30.6	28.3	25.9	27.1
87.5°	17.7	12.9	12.9	11.8	12.9
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1055685
 CATALOG NUMBER: S123R3DRP-H1000D830-X4F0-XX-UDD-F-W

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	20.78	22.27	21.15	22.59	22.90	15.93	17.42	16.30	17.74	18.05
	3H	22.67	24.01	23.05	24.34	24.70	17.56	18.90	17.94	19.23	19.59
	4H	23.43	24.68	23.83	25.03	25.41	18.20	19.45	18.60	19.80	20.18
	6H	23.99	25.15	24.40	25.52	25.91	18.69	19.85	19.10	20.21	20.61
	8H	24.16	25.27	24.59	25.66	26.06	18.86	19.96	19.28	20.35	20.75
	12H	24.26	25.32	24.69	25.70	26.13	18.98	20.04	19.41	20.42	20.85
4H	2H	20.83	22.09	21.23	22.43	22.81	16.66	17.92	17.06	18.26	18.64
	3H	22.85	23.89	23.26	24.29	24.69	18.48	19.52	18.89	19.92	20.33
	4H	23.66	24.60	24.10	25.02	25.46	19.23	20.17	19.66	20.58	21.02
	6H	24.35	25.16	24.80	25.61	26.07	19.84	20.65	20.29	21.10	21.56
	8H	24.58	25.34	25.04	25.79	26.25	20.05	20.82	20.52	21.26	21.73
	12H	24.73	25.41	25.21	25.89	26.36	20.22	20.90	20.70	21.38	21.85
8H	4H	23.69	24.45	24.15	24.90	25.36	19.61	20.37	20.07	20.82	21.29
	6H	24.42	25.05	24.91	25.54	26.02	20.34	20.97	20.84	21.46	21.94
	8H	24.69	25.25	25.20	25.76	26.25	20.63	21.19	21.14	21.70	22.19
	12H	24.90	25.40	25.41	25.89	26.45	20.87	21.37	21.38	21.86	22.43
12H	4H	23.67	24.36	24.16	24.83	25.31	19.67	20.35	20.15	20.83	21.30
	6H	24.40	24.97	24.92	25.48	25.97	20.42	20.99	20.94	21.50	21.99
	8H	24.71	25.21	25.22	25.70	26.26	20.77	21.27	21.28	21.76	22.33