

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P995750

Luminaire Tested: S122DRP-B1005DB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P995750
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-10)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DRP-B1005DB2750-4F0-XX-W2A-F_2700K
Description: Define 2 Direct Perimeter with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4029.0 lumens
Efficiency: N/A
Efficacy: 65.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 61.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P995750

CATALOG NUMBER: S122DRP-B1005DB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P995750

CATALOG NUMBER: S122DRP-B1005DB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	109	104	100	96	106	102	98	95	98	95	92	94	91	89	90	88	86	84		
2	99	91	85	79	97	89	83	78	86	81	76	83	78	74	80	76	73	71		
3	91	80	72	66	88	79	71	65	76	69	64	73	68	63	71	66	62	60		
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	54	51		
5	77	64	55	49	75	63	55	48	61	53	48	59	52	47	57	51	47	45		
6	71	58	49	43	69	57	48	42	55	48	42	53	47	42	52	46	41	39		
7	66	52	44	38	64	52	43	38	50	43	37	49	42	37	47	41	37	35		
8	61	48	40	34	60	47	39	34	46	39	33	45	38	33	44	38	33	31		
9	57	44	36	30	56	43	36	30	42	35	30	41	35	30	40	34	30	28		
10	54	41	33	28	53	40	33	28	39	32	27	38	32	27	37	32	27	26		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25067	25067	25067
5°	25163	24801	24945
10°	25014	24549	24671
15°	24704	24231	24205
20°	24265	23752	23726
25°	23830	23165	23165
30°	23268	22628	22433
35°	22746	21981	21656
40°	22087	21333	20924
45°	21441	20691	20179
50°	20738	20023	19312
55°	20003	19247	18532
60°	19185	18318	17643
65°	18308	17394	16596
70°	17194	16277	15504
75°	15645	14996	14623
80°	13883	13464	12771
85°	11333	10788	9680

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21441 cd/sqm

TEST NUMBER: P995750

CATALOG NUMBER: S122DRP-B1005DB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.0	3.7
10°-20°	419.4	10.4
20°-30°	616.3	15.3
30°-40°	715.8	17.8
40°-50°	714.9	17.7
50°-60°	623.3	15.5
60°-70°	460.8	11.4
70°-80°	260.7	6.5
80°-90°	68.8	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1184.7	29.4
0°-40°	1900.5	47.2
0°-60°	3238.7	80.4
0°-90°	4029.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4029.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1584	1584	1584	1584	1584	
5°	1584	1578	1561	1573	1570	150
15°	1508	1498	1479	1485	1477	425
25°	1364	1352	1326	1329	1326	628
35°	1177	1162	1138	1128	1121	735
45°	958	947	924	908	901	739
55°	725	716	697	679	672	648
65°	489	480	464	451	443	483
75°	256	253	245	236	239	273
85°	62	61	59	55	53	73
90°	0	0	0	0	0	



TEST NUMBER: P995750

CATALOG NUMBER: S122DRP-B1005DB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1583.6	1583.6	1583.6	1583.6	1583.6
2.5°	1592.8	1585.1	1568.4	1583.6	1580.6
5°	1583.6	1577.5	1560.8	1573.0	1569.9
7.5°	1573.0	1563.8	1547.1	1559.3	1556.2
10°	1556.2	1545.6	1527.3	1539.5	1534.9
12.5°	1533.4	1524.2	1506.0	1513.6	1510.5
15°	1507.5	1498.4	1478.6	1484.7	1477.0
17.5°	1475.5	1466.4	1446.6	1454.2	1446.6
20°	1440.5	1431.4	1410.0	1414.6	1408.5
22.5°	1405.5	1391.8	1372.0	1372.0	1368.9
25°	1364.4	1352.2	1326.3	1329.3	1326.3
27.5°	1318.7	1308.0	1288.2	1283.7	1276.0
30°	1273.0	1260.8	1238.0	1233.4	1227.3
32.5°	1224.3	1215.1	1190.8	1181.6	1175.5
35°	1177.1	1161.8	1137.5	1128.3	1120.7
37.5°	1123.8	1110.1	1085.7	1075.0	1067.4
40°	1068.9	1056.8	1032.4	1018.7	1012.6
42.5°	1015.7	1003.5	979.1	963.9	954.7
45°	957.8	947.1	924.3	907.5	901.4
47.5°	901.4	890.8	866.4	849.7	840.5
50°	842.1	834.4	813.1	791.8	784.2
52.5°	784.2	773.5	753.7	737.0	726.3
55°	724.8	715.7	697.4	679.1	671.5
57.5°	665.4	657.8	638.0	619.7	613.7
60°	606.0	600.0	578.6	561.9	557.3
62.5°	548.2	537.5	522.3	507.1	501.0
65°	488.8	479.7	464.4	450.7	443.1
67.5°	427.9	420.3	406.6	395.9	389.8
70°	371.5	365.5	351.7	341.1	335.0
72.5°	313.7	307.6	300.0	289.3	284.7
75°	255.8	252.8	245.2	236.0	239.1
77.5°	204.0	198.0	194.9	190.3	185.8
80°	152.3	150.7	147.7	143.1	140.1
82.5°	103.5	103.5	102.0	95.9	95.9
85°	62.4	60.9	59.4	54.8	53.3
87.5°	27.4	24.4	21.3	16.7	15.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)