

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P995752

Luminaire Tested: S122DRP-B1005DB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P995752
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-10)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DRP-B1005DB2750-4F0-XX-W2A-F_3500K
Description: Define 2 Direct Perimeter with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4081.0 lumens
Efficiency: N/A
Efficacy: 66.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 61.3
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P995752

CATALOG NUMBER: S122DRP-B1005DB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P995752

CATALOG NUMBER: S122DRP-B1005DB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90	88	86		84
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80	76	73		71
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71	66	62		60
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63	58	54		51
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57	51	47		45
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52	46	41		39
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47	41	37		35
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44	38	33		31
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40	34	30		28
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37	32	27		26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25392	25392	25392
5°	25489	25120	25268
10°	25337	24866	24989
15°	25022	24542	24518
20°	24579	24058	24033
25°	24138	23463	23463
30°	23568	22919	22723
35°	23040	22265	21937
40°	22373	21608	21195
45°	21719	20958	20441
50°	21004	20282	19560
55°	20262	19495	18772
60°	19435	18555	17871
65°	18544	17619	16810
70°	17416	16490	15703
75°	15846	15186	14813
80°	14056	13637	12935
85°	11478	10934	9808

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21719 cd/sqm

TEST NUMBER: P995752

CATALOG NUMBER: S122DRP-B1005DB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.0	3.7
10°-20°	424.8	10.4
20°-30°	624.2	15.3
30°-40°	725.0	17.8
40°-50°	724.1	17.7
50°-60°	631.4	15.5
60°-70°	466.7	11.4
70°-80°	264.1	6.5
80°-90°	69.7	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1200.0	29.4
0°-40°	1925.0	47.2
0°-60°	3280.5	80.4
0°-90°	4081.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4081.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1604	1604	1604	1604	1604	
5°	1604	1598	1581	1593	1590	152
15°	1527	1518	1498	1504	1496	430
25°	1382	1370	1343	1346	1343	636
35°	1192	1177	1152	1143	1135	745
45°	970	959	936	919	913	749
55°	734	725	706	688	680	656
65°	495	486	470	456	449	490
75°	259	256	248	239	242	277
85°	63	62	60	56	54	74
90°	0	0	0	0	0	

TEST NUMBER: P995752

CATALOG NUMBER: S122DRP-B1005DB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1604.1	1604.1	1604.1	1604.1	1604.1
2.5°	1613.3	1605.6	1588.6	1604.1	1601.0
5°	1604.1	1597.9	1580.9	1593.3	1590.2
7.5°	1593.3	1584.0	1567.0	1579.4	1576.3
10°	1576.3	1565.5	1547.0	1559.3	1554.7
12.5°	1553.2	1543.9	1525.4	1533.1	1530.0
15°	1526.9	1517.7	1497.6	1503.8	1496.1
17.5°	1494.6	1485.3	1465.3	1473.0	1465.3
20°	1459.1	1449.8	1428.2	1432.9	1426.7
22.5°	1423.6	1409.7	1389.7	1389.7	1386.6
25°	1382.0	1369.6	1343.4	1346.5	1343.4
27.5°	1335.7	1324.9	1304.8	1300.2	1292.5
30°	1289.4	1277.1	1253.9	1249.3	1243.2
32.5°	1240.1	1230.8	1206.1	1196.9	1190.7
35°	1192.3	1176.8	1152.2	1142.9	1135.2
37.5°	1138.3	1124.4	1099.7	1088.9	1081.2
40°	1082.7	1070.4	1045.7	1031.8	1025.7
42.5°	1028.8	1016.4	991.7	976.3	967.1
45°	970.2	959.4	936.2	919.3	913.1
47.5°	913.1	902.3	877.6	860.6	851.4
50°	852.9	845.2	823.6	802.0	794.3
52.5°	794.3	783.5	763.5	746.5	735.7
55°	734.2	724.9	706.4	687.9	680.2
57.5°	674.0	666.3	646.3	627.7	621.6
60°	613.9	607.7	586.1	569.1	564.5
62.5°	555.3	544.5	529.0	513.6	507.4
65°	495.1	485.8	470.4	456.5	448.8
67.5°	433.4	425.7	411.8	401.0	394.8
70°	376.3	370.2	356.3	345.5	339.3
72.5°	317.7	311.6	303.8	293.1	288.4
75°	259.1	256.0	248.3	239.1	242.2
77.5°	206.7	200.5	197.4	192.8	188.2
80°	154.2	152.7	149.6	145.0	141.9
82.5°	104.9	104.9	103.3	97.2	97.2
85°	63.2	61.7	60.2	55.5	54.0
87.5°	27.8	24.7	21.6	17.0	15.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)