

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P995842

Luminaire Tested: S122DRP-B675DB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P995842
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-10)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DRP-B675DB2750-4F0-XX-W2A-F_3500K
Description: Define 2 Direct Perimeter with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2727.0 lumens
Efficiency: N/A
Efficacy: 76.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 35.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P995842

CATALOG NUMBER: S122DRP-B675DB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P995842

CATALOG NUMBER: S122DRP-B675DB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	109	104	100	96	106	102	98	95	98	95	92	94	91	89	90	88	86	84		
2	99	91	85	79	97	89	83	78	86	81	76	83	78	74	80	76	73	71		
3	91	80	72	66	88	79	71	65	76	69	64	73	68	63	71	66	62	60		
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	54	51		
5	77	64	55	49	75	63	55	48	61	53	48	59	52	47	57	51	47	45		
6	71	58	49	43	69	57	48	42	55	48	42	53	47	42	52	46	41	39		
7	66	52	44	38	64	52	43	38	50	43	37	49	42	37	47	41	37	35		
8	61	48	40	34	60	47	39	34	46	39	33	45	38	33	44	38	33	31		
9	57	44	36	30	56	43	36	30	42	35	30	41	35	30	40	34	30	28		
10	54	41	33	28	53	40	33	28	39	32	27	38	32	27	37	32	27	26		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16967	16967	16967
5°	17032	16786	16884
10°	16930	16615	16699
15°	16720	16401	16383
20°	16424	16077	16059
25°	16130	15679	15679
30°	15748	15315	15184
35°	15395	14878	14659
40°	14950	14440	14163
45°	14513	14005	13658
50°	14034	13554	13071
55°	13539	13026	12543
60°	12986	12397	11942
65°	12390	11772	11233
70°	11640	11020	10492
75°	10587	10146	9896
80°	9398	9116	8642
85°	7683	7301	6557

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14513 cd/sqm

TEST NUMBER: P995842

CATALOG NUMBER: S122DRP-B675DB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.9	3.7
10°-20°	283.8	10.4
20°-30°	417.1	15.3
30°-40°	484.5	17.8
40°-50°	483.9	17.7
50°-60°	421.9	15.5
60°-70°	311.9	11.4
70°-80°	176.5	6.5
80°-90°	46.6	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	801.8	29.4
0°-40°	1286.3	47.2
0°-60°	2192.1	80.4
0°-90°	2727.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2727.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1072	1072	1072	1072	1072	
5°	1072	1068	1056	1065	1063	102
15°	1020	1014	1001	1005	1000	287
25°	924	915	898	900	898	425
35°	797	786	770	764	759	497
45°	648	641	626	614	610	500
55°	491	484	472	460	454	439
65°	331	325	314	305	300	327
75°	173	171	166	160	162	185
85°	42	41	40	37	36	50
90°	0	0	0	0	0	

TEST NUMBER: P995842

CATALOG NUMBER: S122DRP-B675DB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1071.9	1071.9	1071.9	1071.9	1071.9
2.5°	1078.1	1072.9	1061.6	1071.9	1069.8
5°	1071.9	1067.7	1056.4	1064.7	1062.6
7.5°	1064.7	1058.5	1047.1	1055.4	1053.3
10°	1053.3	1046.1	1033.7	1042.0	1038.9
12.5°	1037.9	1031.7	1019.3	1024.5	1022.4
15°	1020.3	1014.2	1000.8	1004.9	999.7
17.5°	998.7	992.5	979.1	984.3	979.1
20°	975.0	968.8	954.4	957.5	953.3
22.5°	951.3	942.0	928.6	928.6	926.5
25°	923.5	915.2	897.7	899.7	897.7
27.5°	892.5	885.3	871.9	868.8	863.7
30°	861.6	853.4	837.9	834.8	830.7
32.5°	828.6	822.5	806.0	799.8	795.7
35°	796.7	786.4	769.9	763.7	758.6
37.5°	760.6	751.3	734.8	727.6	722.5
40°	723.5	715.3	698.8	689.5	685.4
42.5°	687.4	679.2	662.7	652.4	646.2
45°	648.3	641.1	625.6	614.3	610.1
47.5°	610.1	602.9	586.4	575.1	568.9
50°	569.9	564.8	550.4	535.9	530.8
52.5°	530.8	523.6	510.2	498.8	491.6
55°	490.6	484.4	472.0	459.7	454.5
57.5°	450.4	445.2	431.8	419.5	415.3
60°	410.2	406.1	391.6	380.3	377.2
62.5°	371.0	363.8	353.5	343.2	339.1
65°	330.8	324.7	314.3	305.1	299.9
67.5°	289.6	284.5	275.2	268.0	263.8
70°	251.5	247.4	238.1	230.9	226.7
72.5°	212.3	208.2	203.0	195.8	192.7
75°	173.1	171.1	165.9	159.7	161.8
77.5°	138.1	134.0	131.9	128.8	125.7
80°	103.1	102.0	100.0	96.9	94.8
82.5°	70.1	70.1	69.1	64.9	64.9
85°	42.3	41.2	40.2	37.1	36.1
87.5°	18.6	16.5	14.4	11.3	10.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)