

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1059530

Luminaire Tested: S123RDRP-H1165D927-X4F0-XX-UDD-SVL-S

Issue Date: 8/7/2025

**Test Information**

Test Method: LM-79-2024  
Report Number: P1059530  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2406-143-68)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/7/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123RDRP-H1165D927-X4F0-XX-UDD-SVL-S  
Description: DEFINE 3 SILVER REGRESSED DIRECT RECESSED HOUSING WITH SILVER STRAIGHT BLADE  
LOUVER WITH DIFFUSER  
HIGH PERFORMANCE LIGHT ENGINE  
Light Source: 2700K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1013.7 lumens  
Efficiency: N/A  
Efficacy: 27.8 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 1.07 / 0.98  
Luminous Opening: Rectangular (W 0.23' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 36.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1059530

CATALOG NUMBER: S123RDRP-H1165D927-X4F0-XX-UDD-SVL-S

### Luminous Intensity Polar Plot



TEST NUMBER: P1059530

CATALOG NUMBER: S123RDRP-H1165D927-X4F0-XX-UDD-SVL-S

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71
4	91	81	74	69	88	80	73	68	77	72	67	75	70	66	73	69	66	64
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58
6	79	68	61	56	78	67	60	55	66	60	55	64	59	54	63	58	54	52
7	74	63	56	51	73	62	55	50	61	55	50	60	54	50	58	53	49	48
8	70	58	51	46	69	58	51	46	57	50	46	56	50	46	54	49	45	44
9	66	54	47	43	65	54	47	43	53	47	42	52	46	42	51	46	42	40
10	62	51	44	39	61	50	44	39	50	43	39	49	43	39	48	43	39	37

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8888	8888	8888
5°	8584	8726	8870
10°	7997	8313	8735
15°	7281	7778	8502
20°	6517	7139	8119
25°	5684	6371	7674
30°	4780	5588	7222
35°	3802	4736	6795
40°	2710	3861	6352
45°	1614	3100	5688
50°	1191	2362	4925
55°	995	1607	3914
60°	806	1325	2750
65°	645	1136	1473
70°	532	985	910
75°	499	953	853
80°	521	1048	825
85°	741	1482	1037

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 5688 cd/sqm



TEST NUMBER: P1059530

CATALOG NUMBER: S123RDRP-H1165D927-X4F0-XX-UDD-SVL-S

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	69.5	6.9
10°-20°	180.6	17.8
20°-30°	230.4	22.7
30°-40°	216.8	21.4
40°-50°	155.7	15.4
50°-60°	89.3	8.8
60°-70°	40.8	4.0
70°-80°	20.5	2.0
80°-90°	10.0	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	480.5	47.4
0°-40°	697.3	68.8
0°-60°	942.3	93.0
0°-90°	1013.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1013.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	757	757	757	757	757	
5°	728	742	740	746	752	68
15°	599	620	640	674	699	167
25°	439	459	492	545	592	200
35°	265	284	330	406	474	164
45°	97	118	187	275	342	81
55°	49	50	78	145	191	44
65°	23	32	41	45	53	23
75°	11	22	21	19	19	12
85°	6	11	11	10	8	6
90°	0	0	0	0	0	



TEST NUMBER: P1059530

CATALOG NUMBER: S123RDRP-H1165D927-X4F0-XX-UDD-SVL-S

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	756.9	756.9	756.9	756.9	756.9
2.5°	746.9	758.0	751.4	751.4	752.5
5°	728.2	742.5	740.3	745.8	752.5
7.5°	701.6	717.1	721.5	734.8	745.8
10°	670.7	688.4	697.2	718.2	732.6
12.5°	636.5	656.3	670.7	697.2	718.2
15°	598.9	619.9	639.8	674.0	699.4
17.5°	560.2	581.2	606.6	646.4	676.2
20°	521.5	542.5	571.3	613.3	649.7
22.5°	479.6	500.5	531.5	579.0	623.2
25°	438.7	458.6	491.7	544.7	592.3
27.5°	395.6	415.5	451.9	509.4	562.4
30°	352.5	372.4	412.1	474.0	532.6
32.5°	309.4	328.2	371.3	439.8	502.8
35°	265.2	284.0	330.4	405.5	474.0
37.5°	219.9	238.7	292.8	374.6	445.3
40°	176.8	197.8	251.9	343.6	414.4
42.5°	134.8	156.9	218.8	310.5	379.0
45°	97.2	118.2	186.7	275.1	342.5
47.5°	74.0	85.1	158.0	239.8	307.2
50°	65.2	66.3	129.3	207.7	269.6
52.5°	56.4	57.5	100.6	176.8	229.8
55°	48.6	49.7	78.5	144.7	191.2
57.5°	40.9	43.1	64.1	114.9	153.6
60°	34.3	38.7	56.4	87.3	117.1
62.5°	27.6	35.4	48.6	64.1	84.0
65°	23.2	32.0	40.9	45.3	53.0
67.5°	18.8	29.8	34.3	32.0	32.0
70°	15.5	26.5	28.7	26.5	26.5
72.5°	13.3	25.4	24.3	22.1	22.1
75°	11.0	22.1	21.0	18.8	18.8
77.5°	9.9	18.8	17.7	16.6	15.5
80°	7.7	15.5	15.5	14.4	12.2
82.5°	6.6	13.3	13.3	12.2	9.9
85°	5.5	11.0	11.0	9.9	7.7
87.5°	4.4	9.9	9.9	8.8	5.5
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1059530  
 CATALOG NUMBER: S123RDRP-H1165D927-X4F0-XX-UDD-SVL-S

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.58	8.89	7.94	9.21	9.52	14.80	16.12	15.16	16.43	16.74
	3H	8.98	10.14	9.36	10.47	10.84	15.03	16.20	15.41	16.53	16.90
	4H	9.54	10.63	9.94	10.98	11.36	15.14	16.23	15.54	16.58	16.96
	6H	9.99	11.00	10.41	11.37	11.76	15.25	16.25	15.66	16.62	17.01
	8H	10.18	11.13	10.61	11.52	11.92	15.30	16.24	15.73	16.64	17.04
	12H	10.37	11.28	10.80	11.66	12.09	15.35	16.25	15.78	16.64	17.07
4H	2H	8.65	9.74	9.05	10.09	10.47	14.76	15.85	15.16	16.20	16.58
	3H	10.34	11.23	10.75	11.63	12.04	15.13	16.02	15.54	16.42	16.83
	4H	11.17	11.97	11.61	12.39	12.83	15.31	16.11	15.75	16.53	16.97
	6H	11.83	12.52	12.29	12.97	13.43	15.53	16.23	16.00	16.67	17.14
	8H	12.08	12.73	12.55	13.18	13.65	15.63	16.28	16.10	16.73	17.20
	12H	12.34	12.91	12.82	13.39	13.87	15.75	16.32	16.24	16.80	17.28
8H	4H	11.61	12.25	12.08	12.70	13.17	15.36	16.00	15.82	16.45	16.92
	6H	12.56	13.09	13.06	13.59	14.07	15.69	16.22	16.19	16.72	17.20
	8H	13.03	13.50	13.55	14.02	14.51	15.88	16.36	16.40	16.87	17.36
	12H	13.50	13.92	14.02	14.42	14.99	16.11	16.53	16.63	17.03	17.60
12H	4H	11.67	12.24	12.15	12.72	13.20	15.35	15.92	15.83	16.40	16.88
	6H	12.71	13.19	13.23	13.70	14.19	15.72	16.19	16.24	16.71	17.20
	8H	13.30	13.72	13.82	14.22	14.79	15.98	16.40	16.49	16.89	17.47