

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P996016

Luminaire Tested: S122RDRP-B290DB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P996016
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-24)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDRP-B290DB2750-4F0-XX-W2A-F_3500K
Description: Define 2 Regressed Direct Perimeter with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1009.0 lumens
Efficiency: N/A
Efficacy: 77.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 13
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P996016

CATALOG NUMBER: S122RDRP-B290DB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P996016

CATALOG NUMBER: S122RDRP-B290DB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	88	86	86
2	101	94	87	82	98	92	86	81	88	83	79	85	81	78	82	79	76	76	74	74
3	93	83	76	70	90	82	75	69	79	73	68	76	71	67	74	69	66	66	64	64
4	86	75	66	60	83	73	66	60	71	64	59	69	63	58	66	62	57	57	55	55
5	79	67	59	53	77	66	58	52	64	57	52	62	56	51	60	55	51	51	49	49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	45	43	43
7	68	56	47	42	67	55	47	42	53	46	41	52	46	41	51	45	41	41	39	39
8	64	51	43	38	62	51	43	37	49	42	37	48	42	37	47	41	37	37	35	35
9	60	47	39	34	59	47	39	34	46	39	34	44	38	34	44	38	34	34	32	32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	41	35	31	31	29	29

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7766	7766	7766
5°	7796	7668	7711
10°	7736	7543	7479
15°	7646	7320	7109
20°	7525	7001	6649
25°	7398	6639	6204
30°	7223	6266	5631
35°	7053	5859	5131
40°	6881	5441	4550
45°	6680	4970	4025
50°	6472	4494	3509
55°	6262	3982	3014
60°	6015	3444	2501
65°	5738	2895	2277
70°	5406	2384	2097
75°	4997	2171	1957
80°	4412	1942	1778
85°	3469	1526	1526

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6680 cd/sqm

TEST NUMBER: P996016

CATALOG NUMBER: S122RDRP-B290DB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.0	4.6
10°-20°	126.2	12.5
20°-30°	177.2	17.6
30°-40°	193.2	19.1
40°-50°	177.6	17.6
50°-60°	139.4	13.8
60°-70°	90.8	9.0
70°-80°	46.7	4.6
80°-90°	11.9	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	349.4	34.6
0°-40°	542.6	53.8
0°-60°	859.6	85.2
0°-90°	1009.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1009.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	491	491	491	491	491	
5°	491	488	483	487	485	47
15°	467	462	447	438	434	131
25°	424	409	380	362	355	195
35°	365	342	303	275	266	228
45°	298	269	222	190	180	230
55°	227	192	144	118	109	203
65°	153	117	77	62	61	152
75°	82	51	36	32	32	86
85°	19	10	8	8	8	23
90°	0	0	0	0	0	

TEST NUMBER: P996016

CATALOG NUMBER: S122RDRP-B290DB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	490.6	490.6	490.6	490.6	490.6
2.5°	492.8	490.6	485.7	490.2	489.3
5°	490.6	488.4	482.6	486.6	485.3
7.5°	486.6	483.9	477.7	479.5	477.3
10°	481.3	478.2	469.3	468.0	465.3
12.5°	474.6	470.6	458.6	456.0	451.1
15°	466.6	461.7	446.7	438.2	433.8
17.5°	457.3	450.2	431.6	421.8	414.7
20°	446.7	437.8	415.6	404.5	394.7
22.5°	435.1	424.9	399.1	384.1	377.4
25°	423.6	409.4	380.1	361.9	355.2
27.5°	409.8	394.7	362.3	341.4	331.2
30°	395.2	378.3	342.8	320.1	308.1
32.5°	380.9	360.5	324.1	297.5	286.4
35°	365.0	342.3	303.2	275.3	265.5
37.5°	349.4	325.0	283.7	253.1	242.0
40°	333.0	306.4	263.3	231.8	220.2
42.5°	316.1	287.7	242.9	210.0	198.9
45°	298.4	268.6	222.0	190.5	179.8
47.5°	281.5	250.0	202.0	170.5	160.7
50°	262.8	231.3	182.5	151.8	142.5
52.5°	244.6	211.3	163.8	134.5	126.1
55°	226.9	192.2	144.3	117.7	109.2
57.5°	208.7	173.2	127.0	102.1	95.0
60°	190.0	154.5	108.8	86.1	79.0
62.5°	171.8	136.3	93.2	71.9	68.4
65°	153.2	117.2	77.3	62.2	60.8
67.5°	135.4	99.5	62.2	54.6	53.3
70°	116.8	82.1	51.5	47.1	45.3
72.5°	99.0	66.2	43.1	39.5	38.6
75°	81.7	50.6	35.5	32.4	32.0
77.5°	64.4	36.0	28.0	26.2	25.3
80°	48.4	25.8	21.3	19.5	19.5
82.5°	33.7	17.3	14.7	13.8	13.8
85°	19.1	9.8	8.4	8.4	8.4
87.5°	7.1	3.6	3.6	3.1	3.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)