

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1059612

Luminaire Tested: S123RDRP-H340D927-X4F0-XX-UDD-SVL-W

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2024
Report Number: P1059612
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2406-143-65)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDRP-H340D927-X4F0-XX-UDD-SVL-W
Description: DEFINE 3 WHITE REGRESSED DIRECT RECESSED HOUSING WITH SILVER STRAIGHT BLADE
LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 355.5 lumens
Efficiency: N/A
Efficacy: 30.4 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 1.08 / 0.98
Luminous Opening: Rectangular (W 0.23' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1059612

CATALOG NUMBER: S123RDRP-H340D927-X4F0-XX-UDD-SVL-W

Luminous Intensity Polar Plot



TEST NUMBER: P1059612

CATALOG NUMBER: S123RDRP-H340D927-X4F0-XX-UDD-SVL-W

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	89				89
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79				79
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71				71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	66	64				64
5	85	74	67	61	83	73	66	61	71	65	60	69	64	60	68	63	59	58				58
6	79	68	61	55	78	67	60	55	66	59	55	64	59	54	63	58	54	52				52
7	74	63	56	51	73	62	55	50	61	55	50	60	54	50	58	53	49	48				48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44				44
9	66	54	47	43	65	54	47	43	53	47	42	52	46	42	51	46	42	40				40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37				37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3109	3109	3109
5°	3009	3055	3118
10°	2808	2914	3063
15°	2559	2723	2983
20°	2277	2490	2857
25°	1973	2228	2694
30°	1654	1944	2533
35°	1310	1656	2381
40°	927	1361	2233
45°	546	1076	2009
50°	409	817	1761
55°	344	553	1415
60°	277	472	1005
65°	220	403	531
70°	192	350	326
75°	177	327	313
80°	176	358	311
85°	216	525	404

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 2009 cd/sqm



TEST NUMBER: P1059612

CATALOG NUMBER: S123RDRP-H340D927-X4F0-XX-UDD-SVL-W

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.4	6.9
10°-20°	63.3	17.8
20°-30°	80.7	22.7
30°-40°	75.9	21.3
40°-50°	54.6	15.4
50°-60°	31.6	8.9
60°-70°	14.4	4.1
70°-80°	7.2	2.0
80°-90°	3.4	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	168.4	47.4
0°-40°	244.2	68.7
0°-60°	330.4	93.0
0°-90°	355.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	355.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	265	265	265	265	265	
5°	255	260	259	262	264	24
15°	210	218	224	236	245	59
25°	152	160	172	191	208	70
35°	91	99	116	142	166	57
45°	33	41	65	97	121	28
55°	17	17	27	51	69	15
65°	8	11	14	16	19	8
75°	4	8	7	7	7	4
85°	2	4	4	4	3	2
90°	0	0	0	0	0	



TEST NUMBER: P1059612

CATALOG NUMBER: S123RDRP-H340D927-X4F0-XX-UDD-SVL-W

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	264.8	264.8	264.8	264.8	264.8
2.5°	261.8	265.1	262.8	263.1	263.8
5°	255.3	259.5	259.2	261.8	264.5
7.5°	246.0	251.0	253.6	257.6	261.2
10°	235.5	241.1	244.4	251.6	256.9
12.5°	223.3	230.6	234.9	244.4	252.0
15°	210.5	218.1	224.0	236.5	245.4
17.5°	196.0	204.3	211.8	226.6	237.5
20°	182.2	190.1	199.3	215.5	228.6
22.5°	167.1	175.7	186.2	203.3	218.1
25°	152.3	160.2	172.0	191.1	207.9
27.5°	137.5	145.4	157.9	178.9	197.4
30°	122.0	130.3	143.4	166.8	186.8
32.5°	106.9	114.8	129.6	154.9	176.0
35°	91.4	99.3	115.5	142.1	166.1
37.5°	76.3	84.5	101.6	131.6	156.2
40°	60.5	69.4	88.8	120.7	145.7
42.5°	45.7	55.3	76.0	109.5	134.2
45°	32.9	41.1	64.8	97.4	121.0
47.5°	25.7	29.9	54.6	84.9	108.9
50°	22.4	23.0	44.7	73.4	96.4
52.5°	19.4	20.1	35.2	62.5	83.2
55°	16.8	17.4	27.0	51.3	69.1
57.5°	14.1	15.1	22.4	40.8	55.6
60°	11.8	13.2	20.1	31.2	42.8
62.5°	9.5	11.8	17.1	23.0	30.6
65°	7.9	11.2	14.5	16.1	19.1
67.5°	6.6	10.2	12.2	11.5	11.2
70°	5.6	9.2	10.2	9.2	9.5
72.5°	4.6	8.6	8.6	7.9	7.9
75°	3.9	7.6	7.2	6.9	6.9
77.5°	3.3	6.6	6.2	5.9	5.6
80°	2.6	5.3	5.3	4.9	4.6
82.5°	2.3	4.3	4.3	4.3	3.6
85°	1.6	3.6	3.9	3.6	3.0
87.5°	1.3	3.3	3.3	3.0	2.0
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1059612
 CATALOG NUMBER: S123RDRP-H340D927-X4F0-XX-UDD-SVL-W

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	3.90	5.22	4.26	5.53	5.84	11.28	12.60	11.64	12.91	13.22
	3H	5.29	6.46	5.67	6.79	7.16	11.51	12.68	11.89	13.01	13.37
	4H	5.85	6.94	6.25	7.29	7.67	11.62	12.71	12.02	13.06	13.44
	6H	6.28	7.28	6.70	7.65	8.05	11.73	12.74	12.15	13.11	13.50
	8H	6.46	7.41	6.89	7.80	8.20	11.79	12.74	12.22	13.13	13.53
	12H	6.61	7.52	7.04	7.90	8.33	11.85	12.75	12.28	13.14	13.57
4H	2H	5.01	6.10	5.41	6.45	6.83	11.23	12.33	11.64	12.68	13.06
	3H	6.67	7.57	7.09	7.97	8.37	11.59	12.49	12.01	12.89	13.29
	4H	7.49	8.29	7.92	8.71	9.15	11.79	12.59	12.23	13.01	13.45
	6H	8.13	8.82	8.59	9.26	9.73	12.02	12.71	12.48	13.15	13.62
	8H	8.36	9.01	8.83	9.45	9.92	12.12	12.77	12.59	13.21	13.68
	12H	8.57	9.14	9.06	9.62	10.10	12.25	12.82	12.74	13.30	13.78
8H	4H	7.93	8.57	8.40	9.02	9.49	11.83	12.47	12.30	12.92	13.39
	6H	8.84	9.37	9.35	9.87	10.35	12.15	12.68	12.66	13.18	13.66
	8H	9.27	9.74	9.79	10.26	10.75	12.34	12.82	12.87	13.34	13.83
	12H	9.68	10.10	10.19	10.59	11.16	12.60	13.02	13.11	13.51	14.08
12H	4H	7.98	8.56	8.47	9.04	9.51	11.82	12.39	12.30	12.87	13.35
	6H	8.98	9.46	9.50	9.97	10.46	12.17	12.65	12.69	13.16	13.66
	8H	9.52	9.94	10.03	10.44	11.01	12.43	12.85	12.94	13.35	13.92