

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1059769

Luminaire Tested: S123RDRP-H775D927-X4F0-XX-UDD-BVL-B

Issue Date: 8/7/2025

**Test Information**

Test Method: LM-79-2024  
Report Number: P1059769  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2406-143-30)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/7/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123RDRP-H775D927-X4F0-XX-UDD-BVL-B  
Description: DEFINE 3 BLACK REGRESSED DIRECT RECESSED HOUSING WITH BLACK STRAIGHT BLADE  
LOUVER WITH DIFFUSER  
HIGH PERFORMANCE LIGHT ENGINE  
Light Source: 2700K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 519.1 lumens  
Efficiency: N/A  
Efficacy: 22.1 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 0.81 / 0.94  
Luminous Opening: Rectangular (W 0.23' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 23.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1059769

CATALOG NUMBER: S123RDRP-H775D927-X4F0-XX-UDD-BVL-B

### Luminous Intensity Polar Plot





TEST NUMBER: P1059769

CATALOG NUMBER: S123RDRP-H775D927-X4F0-XX-UDD-BVL-B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	87	85	84
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	83	80	78	76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63
6	83	73	66	61	81	72	66	61	70	65	60	69	64	60	67	63	60	58
7	78	68	61	56	77	67	60	56	66	60	56	64	59	55	63	58	55	53
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49
9	70	59	52	48	68	58	52	48	57	52	47	56	51	47	55	51	47	46
10	66	55	49	44	65	55	48	44	54	48	44	53	48	44	52	47	44	42

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5342	5342	5342
5°	5328	5234	5242
10°	5268	4988	4866
15°	5112	4640	4373
20°	4888	4202	3826
25°	4603	3711	3236
30°	4271	3189	2643
35°	3918	2636	1964
40°	3515	2066	1258
45°	3066	1508	523
50°	2543	897	201
55°	1875	375	149
60°	1137	139	87
65°	306	81	42
70°	0	24	24
75°	0	0	32
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3066 cd/sqm



TEST NUMBER: P1059769

CATALOG NUMBER: S123RDRP-H775D927-X4F0-XX-UDD-BVL-B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	41.9	8.1
10°-20°	108.1	20.8
20°-30°	134.7	25.9
30°-40°	120.4	23.2
40°-50°	76.0	14.6
50°-60°	31.8	6.1
60°-70°	6.0	1.2
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	284.7	54.8
0°-40°	405.1	78.0
0°-60°	512.9	98.8
0°-90°	519.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	519.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	455	455	455	455	455	
5°	452	451	444	445	445	43
15°	420	410	382	366	360	118
25°	355	327	286	262	250	163
35°	273	234	184	151	137	170
45°	185	144	91	48	32	142
55°	92	63	18	7	7	82
65°	11	8	3	2	2	15
75°	0	0	0	0	1	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P1059769

CATALOG NUMBER: S123RDRP-H775D927-X4F0-XX-UDD-BVL-B

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	454.9	454.9	454.9	454.9	454.9
2.5°	454.2	454.9	450.6	454.9	455.7
5°	452.0	451.3	444.0	445.4	444.7
7.5°	447.6	445.4	432.2	429.3	427.8
10°	441.8	435.9	418.3	411.0	408.1
12.5°	432.2	424.2	401.5	389.7	385.4
15°	420.5	410.3	381.7	365.6	359.7
17.5°	406.6	391.9	359.7	342.1	333.3
20°	391.2	370.7	336.3	315.0	306.2
22.5°	372.9	350.2	311.4	288.6	279.1
25°	355.3	326.7	286.4	261.5	249.8
27.5°	333.3	303.3	260.1	234.4	222.0
30°	315.0	280.6	235.2	206.6	194.9
32.5°	293.0	257.1	209.5	178.0	167.0
35°	273.3	233.7	183.9	150.9	137.0
37.5°	252.0	211.0	158.2	123.8	110.6
40°	229.3	188.3	134.8	96.7	82.1
42.5°	208.8	165.6	111.4	71.8	57.1
45°	184.6	143.6	90.8	48.4	31.5
47.5°	162.6	123.1	68.9	27.1	16.8
50°	139.2	101.8	49.1	13.9	11.0
52.5°	115.0	81.3	32.2	9.5	8.8
55°	91.6	63.0	18.3	7.3	7.3
57.5°	68.9	45.4	9.5	5.9	5.1
60°	48.4	30.0	5.9	4.4	3.7
62.5°	27.8	17.6	4.4	2.9	2.9
65°	11.0	8.1	2.9	1.5	1.5
67.5°	0.7	2.2	1.5	0.7	0.7
70°	0.0	0.0	0.7	0.7	0.7
72.5°	0.0	0.0	0.7	0.7	0.7
75°	0.0	0.0	0.0	0.0	0.7
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1059769

CATALOG NUMBER: S123RDRP-H775D927-X4F0-XX-UDD-BVL-B

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.01	12.19	11.38	12.50	12.81	0.00	0.00	0.00	0.00	0.00
	3H	10.85	11.88	11.23	12.21	12.58	0.00	0.00	0.00	0.00	0.00
	4H	10.77	11.72	11.17	12.07	12.46	0.00	0.00	0.00	0.00	0.00
	6H	10.67	11.54	11.09	11.92	12.31	0.00	0.00	0.00	0.00	0.00
	8H	10.62	11.44	11.06	11.84	12.24	0.00	0.00	0.00	0.00	0.00
	12H	10.57	11.36	11.01	11.74	12.17	0.00	0.00	0.00	0.00	0.00
4H	2H	10.77	11.72	11.17	12.08	12.46	0.00	0.00	0.00	0.00	0.00
	3H	10.60	11.37	11.02	11.78	12.18	0.00	0.00	0.00	0.00	0.00
	4H	10.50	11.18	10.94	11.60	12.05	0.00	0.00	0.00	0.00	0.00
	6H	10.40	10.99	10.87	11.44	11.91	0.00	0.00	0.00	0.00	0.00
	8H	10.34	10.88	10.81	11.33	11.81	0.00	0.00	0.00	0.00	0.00
	12H	10.28	10.76	10.77	11.24	11.72	0.00	0.00	0.00	0.00	0.00
8H	4H	10.34	10.88	10.81	11.33	11.81	0.00	0.00	0.00	0.00	0.00
	6H	10.22	10.66	10.73	11.16	11.65	0.00	0.00	0.00	0.00	0.00
	8H	10.15	10.55	10.68	11.07	11.56	0.00	0.00	0.00	0.00	0.00
	12H	10.10	10.45	10.61	10.94	11.52	0.00	0.00	0.00	0.00	0.00
12H	4H	10.28	10.76	10.77	11.24	11.72	0.00	0.00	0.00	0.00	0.00
	6H	10.15	10.55	10.68	11.07	11.56	0.00	0.00	0.00	0.00	0.00
	8H	10.10	10.45	10.61	10.94	11.52	0.00	0.00	0.00	0.00	0.00