

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P996132

Luminaire Tested: S123DRP-B1165DB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P996132
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-11)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DRP-B1165DB2750-4F0-XX-W2A-F_4000K
Description: Define 3 Direct Perimeter with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4741.0 lumens
Efficiency: N/A
Efficacy: 77.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 61.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P996132

CATALOG NUMBER: S123DRP-B1165DB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P996132

CATALOG NUMBER: S123DRP-B1165DB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	109	104	100	96	106	102	98	95	98	94	92		94	91	89		90	88	86		84
2	99	91	84	79	97	89	83	78	86	80	76		82	78	74		79	76	72		70
3	91	80	72	66	88	79	71	65	76	69	64		73	67	63		70	66	62		59
4	83	71	62	56	81	70	62	55	67	60	55		65	59	54		63	58	53		51
5	76	64	55	48	74	63	54	48	60	53	47		58	52	47		57	51	46		44
6	71	57	49	42	69	56	48	42	55	47	42		53	46	41		51	46	41		39
7	66	52	43	37	64	51	43	37	50	42	37		48	42	37		47	41	36		34
8	61	48	39	33	60	47	39	33	46	38	33		44	38	33		43	37	33		31
9	57	44	36	30	56	43	35	30	42	35	30		41	34	30		40	34	30		28
10	54	40	33	27	52	40	32	27	39	32	27		38	32	27		37	31	27		25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19609	19609	19609
5°	19700	19430	19565
10°	19568	19260	19380
15°	19340	19043	19078
20°	19072	18732	18749
25°	18715	18361	18325
30°	18319	17950	17813
35°	17906	17516	17289
40°	17476	17036	16772
45°	17000	16596	16191
50°	16525	16052	15607
55°	15903	15492	15021
60°	15276	14837	14366
65°	14721	14123	13685
70°	13901	13309	12718
75°	12701	12248	11724
80°	11455	10972	10873
85°	10065	9670	9287

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17000 cd/sqm

TEST NUMBER: P996132

CATALOG NUMBER: S123DRP-B1165DB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.7	3.6
10°-20°	484.9	10.2
20°-30°	716.2	15.1
30°-40°	836.4	17.6
40°-50°	840.9	17.7
50°-60°	738.7	15.6
60°-70°	550.1	11.6
70°-80°	313.1	6.6
80°-90°	89.0	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1372.8	29.0
0°-40°	2209.3	46.6
0°-60°	3788.8	79.9
0°-90°	4741.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4741.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1822	1822	1822	1822	1822	
5°	1823	1815	1798	1814	1811	173
15°	1736	1729	1709	1721	1712	489
25°	1576	1566	1546	1548	1543	726
35°	1363	1353	1333	1324	1316	853
45°	1117	1110	1090	1071	1064	862
55°	847	846	826	808	800	759
65°	578	570	554	542	537	570
75°	305	299	294	287	282	326
85°	82	78	78	75	75	93
90°	0	0	0	0	0	



TEST NUMBER: P996132

CATALOG NUMBER: S123DRP-B1165DB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1821.7	1821.7	1821.7	1821.7	1821.7
2.5°	1829.5	1823.2	1806.0	1821.7	1820.1
5°	1823.2	1815.4	1798.2	1813.8	1810.7
7.5°	1809.1	1801.3	1784.1	1798.2	1796.6
10°	1790.3	1782.5	1762.1	1776.2	1773.1
12.5°	1765.3	1759.0	1740.2	1749.6	1748.1
15°	1735.5	1729.3	1708.9	1721.4	1712.0
17.5°	1702.6	1694.8	1674.4	1683.8	1680.7
20°	1665.0	1655.6	1635.3	1641.5	1636.8
22.5°	1622.7	1613.3	1593.0	1597.7	1591.4
25°	1575.8	1566.4	1546.0	1547.6	1542.9
27.5°	1527.2	1517.8	1495.9	1497.4	1492.7
30°	1473.9	1466.1	1444.2	1444.2	1433.2
32.5°	1420.7	1409.7	1394.1	1383.1	1378.4
35°	1362.7	1353.3	1333.0	1323.6	1315.7
37.5°	1304.8	1292.2	1271.9	1260.9	1256.2
40°	1243.7	1234.3	1212.4	1199.8	1193.6
42.5°	1182.6	1171.6	1149.7	1137.2	1130.9
45°	1116.8	1110.5	1090.2	1071.4	1063.6
47.5°	1052.6	1043.2	1024.4	1005.6	999.3
50°	986.8	979.0	958.6	941.4	932.0
52.5°	917.9	913.2	891.3	877.2	867.8
55°	847.4	845.8	825.5	808.2	800.4
57.5°	781.6	775.3	759.7	744.0	734.6
60°	709.6	708.0	689.2	675.1	667.3
62.5°	645.3	640.6	621.8	607.7	603.0
65°	578.0	570.2	554.5	542.0	537.3
67.5°	505.9	499.7	487.1	476.2	469.9
70°	441.7	432.3	422.9	412.0	404.1
72.5°	374.4	368.1	357.1	347.7	344.6
75°	305.4	299.2	294.5	286.6	281.9
77.5°	244.4	241.2	235.0	228.7	228.7
80°	184.8	180.1	177.0	175.4	175.4
82.5°	126.9	126.9	126.9	123.7	122.2
85°	81.5	78.3	78.3	75.2	75.2
87.5°	40.7	36.0	34.5	32.9	32.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)