

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1059664

Luminaire Tested: S123RDRP-H560D835-X4F0-XX-UDD-SVL-B

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2024
Report Number: P1059664
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2406-143-29)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDRP-H560D835-X4F0-XX-UDD-SVL-B
Description: DEFINE 3 BLACK REGRESSED DIRECT RECESSED HOUSING WITH SILVER STRAIGHT BLADE
LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 550.7 lumens
Efficiency: N/A
Efficacy: 31.7 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 0.85 / 0.98
Luminous Opening: Rectangular (W 0.23' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 17.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1059664

CATALOG NUMBER: S123RDRP-H560D835-X4F0-XX-UDD-SVL-B

Luminous Intensity Polar Plot





TEST NUMBER: P1059664

CATALOG NUMBER: S123RDRP-H560D835-X4F0-XX-UDD-SVL-B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	83	82
3	98	90	84	80	96	89	83	79	86	82	78	84	80	76	81	78	75	73
4	92	83	76	71	90	82	75	70	79	74	70	77	73	69	75	71	68	66
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60
6	81	70	63	58	79	69	62	58	68	62	57	66	61	57	65	60	56	55
7	76	65	58	53	74	64	57	53	63	57	52	61	56	52	60	55	52	50
8	71	60	53	48	70	60	53	48	58	52	48	57	52	48	56	51	48	46
9	67	56	49	45	66	56	49	44	55	48	44	54	48	44	53	48	44	42
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5009	5009	5009
5°	4998	4912	4920
10°	4938	4701	4622
15°	4825	4424	4223
20°	4621	4069	3771
25°	4355	3645	3294
30°	4065	3197	2776
35°	3777	2726	2235
40°	3421	2247	1620
45°	3016	1744	976
50°	2558	1218	663
55°	1947	731	555
60°	1273	465	434
65°	533	347	347
70°	182	251	271
75°	150	181	209
80°	88	135	176
85°	94	94	175

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3016 cd/sqm

TEST NUMBER: P1059664

CATALOG NUMBER: S123RDRP-H560D835-X4F0-XX-UDD-SVL-B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.4	7.2
10°-20°	103.1	18.7
20°-30°	132.2	24.0
30°-40°	124.1	22.5
40°-50°	86.6	15.7
50°-60°	44.8	8.1
60°-70°	15.3	2.8
70°-80°	4.4	0.8
80°-90°	0.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	274.7	49.9
0°-40°	398.8	72.4
0°-60°	530.2	96.3
0°-90°	550.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	550.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	427	427	427	427	427	
5°	424	423	417	419	417	40
15°	397	387	364	352	347	111
25°	336	315	281	262	254	155
35°	264	231	190	166	156	164
45°	182	149	105	73	59	140
55°	95	71	36	28	27	86
65°	19	16	12	12	12	23
75°	3	3	4	5	5	3
85°	1	1	1	1	1	1
90°	0	0	0	0	0	



TEST NUMBER: P1059664

CATALOG NUMBER: S123RDRP-H560D835-X4F0-XX-UDD-SVL-B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	426.6	426.6	426.6	426.6	426.6
2.5°	426.0	426.6	422.6	426.6	427.3
5°	424.0	423.3	416.7	418.7	417.4
7.5°	420.0	418.0	407.5	404.8	404.8
10°	414.1	410.1	394.3	389.6	387.6
12.5°	406.1	400.9	380.4	371.8	368.5
15°	396.9	387.0	363.9	352.0	347.4
17.5°	383.7	370.5	345.4	331.5	324.3
20°	369.8	353.3	325.6	309.1	301.8
22.5°	355.3	335.5	303.8	285.9	278.0
25°	336.1	315.0	281.3	262.2	254.2
27.5°	317.6	295.2	259.5	237.7	229.8
30°	299.8	273.4	235.8	214.6	204.7
32.5°	282.0	252.3	213.3	190.2	180.9
35°	263.5	231.1	190.2	165.8	155.9
37.5°	243.7	210.7	168.4	142.0	130.1
40°	223.2	188.9	146.6	116.9	105.7
42.5°	202.7	169.1	124.8	94.4	81.2
45°	181.6	148.6	105.0	72.6	58.8
47.5°	160.5	128.1	85.9	52.8	44.2
50°	140.0	109.0	66.7	39.0	36.3
52.5°	117.5	90.5	50.2	32.4	31.7
55°	95.1	71.3	35.7	27.7	27.1
57.5°	75.3	55.5	25.8	23.1	22.5
60°	54.2	39.6	19.8	19.2	18.5
62.5°	35.7	27.1	15.8	15.2	15.2
65°	19.2	16.5	12.5	11.9	12.5
67.5°	7.9	9.2	9.2	9.9	9.9
70°	5.3	5.9	7.3	7.9	7.9
72.5°	4.0	4.6	5.3	5.9	5.9
75°	3.3	3.3	4.0	4.6	4.6
77.5°	2.0	2.6	2.6	3.3	4.0
80°	1.3	2.0	2.0	2.6	2.6
82.5°	0.7	1.3	1.3	2.0	2.0
85°	0.7	0.7	0.7	0.7	1.3
87.5°	0.0	0.0	0.0	0.0	0.7
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1059664
 CATALOG NUMBER: S123RDRP-H560D835-X4F0-XX-UDD-SVL-B

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.93	13.19	12.30	13.51	13.82	5.44	6.70	5.80	7.01	7.32
	3H	11.89	12.99	12.27	13.33	13.69	6.21	7.32	6.59	7.65	8.01
	4H	11.83	12.86	12.24	13.21	13.60	6.41	7.44	6.81	7.79	8.17
	6H	11.76	12.71	12.18	13.08	13.47	6.55	7.50	6.97	7.87	8.26
	8H	11.72	12.61	12.15	13.00	13.41	6.59	7.48	7.02	7.87	8.28
	12H	11.68	12.53	12.11	12.91	13.34	6.61	7.46	7.04	7.84	8.27
4H	2H	11.78	12.81	12.18	13.16	13.55	5.69	6.72	6.09	7.07	7.46
	3H	11.76	12.60	12.18	13.00	13.41	6.60	7.43	7.01	7.84	8.24
	4H	11.71	12.45	12.15	12.87	13.32	6.87	7.61	7.30	8.03	8.47
	6H	11.65	12.29	12.12	12.74	13.21	7.08	7.72	7.55	8.17	8.63
	8H	11.60	12.20	12.07	12.65	13.12	7.14	7.74	7.61	8.19	8.66
	12H	11.56	12.08	12.05	12.57	13.04	7.18	7.70	7.67	8.19	8.66
8H	4H	11.60	12.19	12.07	12.64	13.11	6.85	7.44	7.32	7.89	8.36
	6H	11.54	12.02	12.04	12.52	13.00	7.12	7.60	7.62	8.10	8.58
	8H	11.48	11.92	12.01	12.44	12.93	7.22	7.66	7.75	8.18	8.67
	12H	11.45	11.83	11.97	12.33	12.90	7.30	7.69	7.82	8.18	8.75
12H	4H	11.55	12.08	12.04	12.56	13.04	6.81	7.33	7.30	7.82	8.29
	6H	11.48	11.91	12.00	12.43	12.92	7.08	7.51	7.60	8.03	8.52
	8H	11.45	11.83	11.96	12.33	12.90	7.22	7.60	7.73	8.10	8.67