

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P996193

Luminaire Tested: S123DRP-B560DB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P996193
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-11)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DRP-B560DB2750-4F0-XX-W2A-F_5000K
Description: Define 3 Direct Perimeter with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2220.0 lumens
Efficiency: N/A
Efficacy: 92.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 24
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P996193

CATALOG NUMBER: S123DRP-B560DB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P996193

CATALOG NUMBER: S123DRP-B560DB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	109	104	100	96	106	102	98	95	98	94	92	94	91	89	90	88	86	84			
2	99	91	84	79	97	89	83	78	86	80	76	82	78	74	79	76	72	70			
3	91	80	72	66	88	79	71	65	76	69	64	73	67	63	70	66	62	59			
4	83	71	62	56	81	70	62	55	67	60	55	65	59	54	63	58	53	51			
5	76	64	55	48	74	63	54	48	60	53	47	58	52	47	57	51	46	44			
6	71	57	49	42	69	56	48	42	55	47	42	53	46	41	51	46	41	39			
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34			
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31			
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	30	28			
10	54	40	33	27	52	40	32	27	39	32	27	38	32	27	37	31	27	25			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9182	9182	9182
5°	9224	9098	9162
10°	9163	9018	9075
15°	9056	8917	8934
20°	8931	8771	8780
25°	8764	8598	8581
30°	8579	8405	8341
35°	8385	8202	8096
40°	8183	7977	7853
45°	7961	7771	7581
50°	7738	7517	7308
55°	7446	7253	7034
60°	7154	6947	6727
65°	6892	6612	6408
70°	6508	6231	5954
75°	5947	5735	5490
80°	5362	5139	5089
85°	4705	4533	4347

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7961 cd/sqm

TEST NUMBER: P996193

CATALOG NUMBER: S123DRP-B560DB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.4	3.6
10°-20°	227.1	10.2
20°-30°	335.4	15.1
30°-40°	391.7	17.6
40°-50°	393.8	17.7
50°-60°	345.9	15.6
60°-70°	257.6	11.6
70°-80°	146.6	6.6
80°-90°	41.7	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	642.8	29.0
0°-40°	1034.5	46.6
0°-60°	1774.1	79.9
0°-90°	2220.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2220.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	853	853	853	853	853	
5°	854	850	842	849	848	81
15°	813	810	800	806	802	229
25°	738	734	724	725	722	340
35°	638	634	624	620	616	399
45°	523	520	510	502	498	404
55°	397	396	386	378	375	355
65°	271	267	260	254	252	267
75°	143	140	138	134	132	153
85°	38	37	37	35	35	43
90°	0	0	0	0	0	

TEST NUMBER: P996193

CATALOG NUMBER: S123DRP-B560DB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	853.0	853.0	853.0	853.0	853.0
2.5°	856.7	853.7	845.7	853.0	852.3
5°	853.7	850.1	842.0	849.3	847.9
7.5°	847.1	843.5	835.4	842.0	841.3
10°	838.3	834.7	825.1	831.7	830.3
12.5°	826.6	823.7	814.9	819.3	818.5
15°	812.7	809.7	800.2	806.1	801.7
17.5°	797.3	793.6	784.1	788.5	787.0
20°	779.7	775.3	765.7	768.7	766.5
22.5°	759.9	755.5	745.9	748.1	745.2
25°	737.9	733.5	723.9	724.7	722.5
27.5°	715.1	710.7	700.4	701.2	699.0
30°	690.2	686.5	676.2	676.2	671.1
32.5°	665.2	660.1	652.8	647.6	645.4
35°	638.1	633.7	624.2	619.8	616.1
37.5°	611.0	605.1	595.6	590.4	588.2
40°	582.4	578.0	567.7	561.8	558.9
42.5°	553.8	548.6	538.4	532.5	529.6
45°	523.0	520.0	510.5	501.7	498.0
47.5°	492.9	488.5	479.7	470.9	467.9
50°	462.1	458.4	448.9	440.8	436.4
52.5°	429.8	427.6	417.3	410.7	406.3
55°	396.8	396.1	386.5	378.5	374.8
57.5°	366.0	363.1	355.7	348.4	344.0
60°	332.3	331.5	322.7	316.1	312.5
62.5°	302.2	300.0	291.2	284.6	282.4
65°	270.6	267.0	259.6	253.8	251.6
67.5°	236.9	234.0	228.1	223.0	220.0
70°	206.8	202.4	198.0	192.9	189.2
72.5°	175.3	172.4	167.2	162.8	161.4
75°	143.0	140.1	137.9	134.2	132.0
77.5°	114.4	113.0	110.0	107.1	107.1
80°	86.5	84.3	82.9	82.1	82.1
82.5°	59.4	59.4	59.4	57.9	57.2
85°	38.1	36.7	36.7	35.2	35.2
87.5°	19.1	16.9	16.1	15.4	15.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)