

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1059140

Luminaire Tested: S123RDRP-S1165D935-X4F0-XX-UDD-BVL-S

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2024
Report Number: P1059140
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2406-143-69)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDRP-S1165D935-X4F0-XX-UDD-BVL-S
Description: DEFINE 3 SILVER REGRESSED DIRECT RECESSED HOUSING WITH BLACK STRAIGHT BLADE
LOUVER WITH DIFFUSER
CORE LIGHT ENGINE
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 975.5 lumens
Efficiency: N/A
Efficacy: 23.3 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 1.06 / 0.94
Luminous Opening: Rectangular (W 0.23' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 41.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1059140

CATALOG NUMBER: S123RDRP-S1165D935-X4F0-XX-UDD-BVL-S

Luminous Intensity Polar Plot





TEST NUMBER: P1059140

CATALOG NUMBER: S123RDRP-S1165D935-X4F0-XX-UDD-BVL-S

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90																												
2	105	99	94	89	102	97	92	88	94	90	86	90	87	85	88	85	83	81																												
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73																												
4	92	83	76	71	90	81	75	70	79	74	69	77	72	69	75	71	68	66																												
5	86	76	69	64	84	75	68	64	73	67	63	71	66	62	70	65	62	60																												
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	57	55																												
7	76	65	58	53	75	64	58	53	63	57	53	62	56	52	61	56	52	50																												
8	72	61	54	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46																												
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43																												
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40																												

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9536	9536	9536
5°	9207	9367	9514
10°	8499	8883	9358
15°	7623	8212	9087
20°	6657	7401	8659
25°	5598	6516	8125
30°	4495	5556	7611
35°	3293	4574	7120
40°	2037	3559	6624
45°	784	2680	5897
50°	385	1838	4991
55°	305	1017	3914
60°	204	845	2626
65°	172	759	1173
70°	172	683	683
75°	227	730	676
80°	338	926	757
85°	498	1509	1010

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 5897 cd/sqm



TEST NUMBER: P1059140

CATALOG NUMBER: S123RDRP-S1165D935-X4F0-XX-UDD-BVL-S

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.5	7.6
10°-20°	190.6	19.5
20°-30°	236.6	24.3
30°-40°	212.0	21.7
40°-50°	139.3	14.3
50°-60°	69.8	7.2
60°-70°	27.6	2.8
70°-80°	15.4	1.6
80°-90°	9.7	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	501.7	51.4
0°-40°	713.6	73.2
0°-60°	922.8	94.6
0°-90°	975.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	975.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	812	812	812	812	812	
5°	781	794	795	800	807	72
15°	627	647	676	722	748	175
25°	432	459	503	574	627	198
35°	230	261	319	417	497	142
45°	47	78	161	272	355	45
55°	15	17	50	134	191	13
65°	6	17	27	35	42	6
75°	5	16	16	15	15	5
85°	4	11	11	11	8	4
90°	0	0	0	0	0	



TEST NUMBER: P1059140

CATALOG NUMBER: S123RDRP-S1165D935-X4F0-XX-UDD-BVL-S

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	812.1	812.1	812.1	812.1	812.1
2.5°	802.2	813.3	807.1	807.1	808.4
5°	781.1	793.5	794.7	799.7	807.1
7.5°	750.0	766.2	773.6	788.5	799.7
10°	712.8	730.1	745.0	771.1	784.8
12.5°	671.8	689.2	711.5	747.5	768.6
15°	627.1	647.0	675.5	721.5	747.5
17.5°	581.1	601.0	635.8	687.9	721.5
20°	532.7	555.1	592.3	651.9	692.9
22.5°	484.3	509.1	548.9	613.4	660.6
25°	432.1	459.4	502.9	573.7	627.1
27.5°	382.5	411.0	457.0	534.0	594.8
30°	331.5	360.1	409.8	493.0	561.3
32.5°	279.4	311.7	363.8	454.5	527.7
35°	229.7	260.8	319.1	417.2	496.7
37.5°	181.3	212.3	273.2	381.2	465.7
40°	132.9	165.2	232.2	346.4	432.1
42.5°	86.9	120.4	196.2	311.7	394.9
45°	47.2	78.2	161.4	271.9	355.1
47.5°	26.1	42.2	130.4	234.7	316.6
50°	21.1	23.6	100.6	199.9	273.2
52.5°	17.4	19.9	72.0	166.4	233.4
55°	14.9	17.4	49.7	134.1	191.2
57.5°	12.4	14.9	39.7	103.1	150.3
60°	8.7	14.9	36.0	75.7	111.8
62.5°	7.5	14.9	31.0	52.2	74.5
65°	6.2	17.4	27.3	34.8	42.2
67.5°	5.0	17.4	23.6	22.4	22.4
70°	5.0	17.4	19.9	18.6	19.9
72.5°	5.0	18.6	18.6	17.4	17.4
75°	5.0	16.1	16.1	14.9	14.9
77.5°	5.0	14.9	14.9	13.7	13.7
80°	5.0	13.7	13.7	12.4	11.2
82.5°	5.0	12.4	12.4	11.2	9.9
85°	3.7	11.2	11.2	11.2	7.5
87.5°	3.7	9.9	11.2	9.9	6.2
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1059140
 CATALOG NUMBER: S123RDRP-S1165D935-X4F0-XX-UDD-BVL-S

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.29	1.55	0.66	1.86	2.18	14.38	15.64	14.75	15.95	16.27
	3H	2.82	3.94	3.20	4.27	4.63	14.46	15.58	14.84	15.91	16.27
	4H	3.99	5.03	4.39	5.38	5.76	14.53	15.56	14.93	15.91	16.30
	6H	5.05	6.00	5.46	6.37	6.76	14.62	15.58	15.04	15.95	16.34
	8H	5.59	6.49	6.02	6.88	7.29	14.68	15.58	15.12	15.98	16.38
	12H	6.07	6.93	6.50	7.31	7.74	14.75	15.61	15.19	16.00	16.43
4H	2H	3.55	4.59	3.95	4.94	5.32	14.24	15.28	14.65	15.63	16.01
	3H	6.02	6.86	6.43	7.27	7.67	14.42	15.26	14.83	15.67	16.07
	4H	7.36	8.12	7.79	8.54	8.98	14.55	15.30	14.98	15.72	16.17
	6H	8.50	9.15	8.96	9.60	10.07	14.76	15.42	15.23	15.86	16.33
	8H	9.01	9.62	9.48	10.07	10.54	14.89	15.50	15.36	15.94	16.42
	12H	9.46	10.00	9.95	10.49	10.96	15.05	15.59	15.53	16.07	16.55
8H	4H	8.28	8.89	8.75	9.33	9.81	14.55	15.16	15.02	15.61	16.08
	6H	9.88	10.38	10.39	10.88	11.36	14.88	15.38	15.38	15.88	16.36
	8H	10.71	11.16	11.23	11.68	12.17	15.11	15.56	15.63	16.07	16.57
	12H	11.49	11.89	12.00	12.38	12.95	15.43	15.83	15.95	16.33	16.90
12H	4H	8.44	8.98	8.93	9.47	9.94	14.54	15.08	15.02	15.56	16.04
	6H	10.20	10.65	10.72	11.16	11.66	14.91	15.36	15.43	15.88	16.37
	8H	11.21	11.61	11.72	12.10	12.67	15.22	15.62	15.74	16.11	16.69