

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P996219

Luminaire Tested: S123DRP-B775DB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P996219
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-11)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DRP-B775DB2750-4F0-XX-W2A-F_2700K
Description: Define 3 Direct Perimeter with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3159.0 lumens
Efficiency: N/A
Efficacy: 88.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 35.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P996219

CATALOG NUMBER: S123DRP-B775DB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P996219

CATALOG NUMBER: S123DRP-B775DB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	109	104	100	96	106	102	98	95	98	94	92	94	91	89	90	88	86	86	86	84
2	99	91	84	79	97	89	83	78	86	80	76	82	78	74	79	76	72	72	72	70
3	91	80	72	66	88	79	71	65	76	69	64	73	67	63	70	66	62	62	62	59
4	83	71	62	56	81	70	62	55	67	60	55	65	59	54	63	58	53	53	53	51
5	76	64	55	48	74	63	54	48	60	53	47	58	52	47	57	51	46	46	46	44
6	71	57	49	42	69	56	48	42	55	47	42	53	46	41	51	46	41	41	41	39
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	36	36	34
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	33	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	30	30	30	28
10	54	40	33	27	52	40	32	27	39	32	27	38	32	27	37	31	27	27	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13065	13065	13065
5°	13126	12947	13036
10°	13038	12833	12914
15°	12886	12689	12712
20°	12708	12481	12494
25°	12469	12234	12209
30°	12207	11961	11870
35°	11931	11671	11520
40°	11644	11351	11175
45°	11327	11058	10788
50°	11010	10695	10399
55°	10595	10321	10008
60°	10178	9886	9571
65°	9808	9411	9118
70°	9262	8869	8475
75°	8463	8160	7814
80°	7637	7308	7246
85°	6706	6447	6187

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11327 cd/sqm

TEST NUMBER: P996219

CATALOG NUMBER: S123DRP-B775DB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.4	3.6
10°-20°	323.1	10.2
20°-30°	477.2	15.1
30°-40°	557.3	17.6
40°-50°	560.3	17.7
50°-60°	492.2	15.6
60°-70°	366.6	11.6
70°-80°	208.6	6.6
80°-90°	59.3	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	914.7	29.0
0°-40°	1472.1	46.6
0°-60°	2524.5	79.9
0°-90°	3159.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3159.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1214	1214	1214	1214	1214	
5°	1215	1210	1198	1209	1206	115
15°	1156	1152	1139	1147	1141	326
25°	1050	1044	1030	1031	1028	484
35°	908	902	888	882	877	568
45°	744	740	726	714	709	574
55°	565	564	550	538	533	506
65°	385	380	370	361	358	380
75°	204	199	196	191	188	217
85°	54	52	52	50	50	62
90°	0	0	0	0	0	

TEST NUMBER: P996219

CATALOG NUMBER: S123DRP-B775DB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1213.8	1213.8	1213.8	1213.8	1213.8
2.5°	1219.0	1214.8	1203.4	1213.8	1212.8
5°	1214.8	1209.6	1198.2	1208.6	1206.5
7.5°	1205.5	1200.2	1188.8	1198.2	1197.1
10°	1192.9	1187.7	1174.1	1183.5	1181.5
12.5°	1176.2	1172.1	1159.5	1165.8	1164.8
15°	1156.4	1152.2	1138.7	1147.0	1140.7
17.5°	1134.5	1129.3	1115.7	1122.0	1119.9
20°	1109.4	1103.2	1089.6	1093.8	1090.7
22.5°	1081.3	1075.0	1061.4	1064.6	1060.4
25°	1049.9	1043.7	1030.1	1031.2	1028.0
27.5°	1017.6	1011.3	996.7	997.8	994.6
30°	982.1	976.9	962.3	962.3	955.0
32.5°	946.6	939.3	928.9	921.6	918.4
35°	908.0	901.7	888.2	881.9	876.7
37.5°	869.4	861.0	847.5	840.2	837.0
40°	828.7	822.4	807.8	799.5	795.3
42.5°	788.0	780.7	766.1	757.7	753.5
45°	744.1	740.0	726.4	713.9	708.7
47.5°	701.4	695.1	682.6	670.0	665.9
50°	657.5	652.3	638.7	627.3	621.0
52.5°	611.6	608.5	593.9	584.5	578.2
55°	564.6	563.6	550.0	538.5	533.3
57.5°	520.8	516.6	506.2	495.8	489.5
60°	472.8	471.7	459.2	449.8	444.6
62.5°	430.0	426.9	414.3	404.9	401.8
65°	385.1	379.9	369.5	361.1	358.0
67.5°	337.1	332.9	324.6	317.3	313.1
70°	294.3	288.1	281.8	274.5	269.3
72.5°	249.4	245.3	238.0	231.7	229.6
75°	203.5	199.3	196.2	191.0	187.9
77.5°	162.8	160.7	156.6	152.4	152.4
80°	123.2	120.0	117.9	116.9	116.9
82.5°	84.5	84.5	84.5	82.5	81.4
85°	54.3	52.2	52.2	50.1	50.1
87.5°	27.1	24.0	23.0	21.9	21.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)