

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P996222

Luminaire Tested: S123DRP-B775DB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P996222
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-11)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DRP-B775DB2750-4F0-XX-W2A-F_4000K
Description: Define 3 Direct Perimeter with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3168.0 lumens
Efficiency: N/A
Efficacy: 88.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 35.9
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P996222

CATALOG NUMBER: S123DRP-B775DB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P996222

CATALOG NUMBER: S123DRP-B775DB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	109	104	100	96	106	102	98	95	98	94	92	94	91	89	90	88	86	86	86	84
2	99	91	84	79	97	89	83	78	86	80	76	82	78	74	79	76	72	72	72	70
3	91	80	72	66	88	79	71	65	76	69	64	73	67	63	70	66	62	62	62	59
4	83	71	62	56	81	70	62	55	67	60	55	65	59	54	63	58	53	53	53	51
5	76	64	55	48	74	63	54	48	60	53	47	58	52	47	57	51	46	46	46	44
6	71	57	49	42	69	56	48	42	55	47	42	53	46	41	51	46	41	41	41	39
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	36	36	34
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	33	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	30	30	30	28
10	54	40	33	27	52	40	32	27	39	32	27	38	32	27	37	31	27	27	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13103	13103	13103
5°	13164	12983	13073
10°	13076	12870	12950
15°	12923	12725	12748
20°	12745	12517	12529
25°	12505	12270	12245
30°	12241	11994	11903
35°	11966	11704	11553
40°	11677	11383	11207
45°	11361	11090	10819
50°	11042	10727	10429
55°	10625	10351	10036
60°	10206	9914	9599
65°	9836	9436	9144
70°	9290	8894	8497
75°	8488	8185	7835
80°	7655	7333	7265
85°	6719	6459	6200

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11361 cd/sqm

TEST NUMBER: P996222

CATALOG NUMBER: S123DRP-B775DB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.8	3.6
10°-20°	324.0	10.2
20°-30°	478.6	15.1
30°-40°	558.9	17.6
40°-50°	561.9	17.7
50°-60°	493.6	15.6
60°-70°	367.6	11.6
70°-80°	209.2	6.6
80°-90°	59.5	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	917.4	29.0
0°-40°	1476.3	46.6
0°-60°	2531.7	79.9
0°-90°	3168.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3168.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1217	1217	1217	1217	1217	
5°	1218	1213	1202	1212	1210	116
15°	1160	1156	1142	1150	1144	327
25°	1053	1047	1033	1034	1031	485
35°	911	904	891	884	879	570
45°	746	742	728	716	711	576
55°	566	565	552	540	535	507
65°	386	381	370	362	359	381
75°	204	200	197	192	188	218
85°	54	52	52	50	50	62
90°	0	0	0	0	0	

TEST NUMBER: P996222

CATALOG NUMBER: S123DRP-B775DB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1217.3	1217.3	1217.3	1217.3	1217.3
2.5°	1222.5	1218.3	1206.8	1217.3	1216.2
5°	1218.3	1213.1	1201.6	1212.0	1209.9
7.5°	1208.9	1203.7	1192.1	1201.6	1200.5
10°	1196.3	1191.1	1177.5	1186.9	1184.8
12.5°	1179.6	1175.4	1162.8	1169.1	1168.1
15°	1159.7	1155.5	1141.9	1150.3	1144.0
17.5°	1137.7	1132.5	1118.9	1125.2	1123.1
20°	1112.6	1106.3	1092.7	1096.9	1093.8
22.5°	1084.3	1078.1	1064.5	1067.6	1063.4
25°	1052.9	1046.7	1033.1	1034.1	1031.0
27.5°	1020.5	1014.2	999.6	1000.6	997.5
30°	984.9	979.7	965.0	965.0	957.7
32.5°	949.3	942.0	931.5	924.2	921.1
35°	910.6	904.3	890.7	884.4	879.2
37.5°	871.9	863.5	849.9	842.6	839.4
40°	831.0	824.8	810.1	801.7	797.6
42.5°	790.2	782.9	768.2	759.9	755.7
45°	746.3	742.1	728.5	715.9	710.7
47.5°	703.4	697.1	684.5	672.0	667.8
50°	659.4	654.2	640.6	629.0	622.8
52.5°	613.3	610.2	595.5	586.1	579.8
55°	566.2	565.2	551.6	540.1	534.8
57.5°	522.3	518.1	507.6	497.2	490.9
60°	474.1	473.1	460.5	451.1	445.9
62.5°	431.2	428.1	415.5	406.1	403.0
65°	386.2	381.0	370.5	362.1	359.0
67.5°	338.1	333.9	325.5	318.2	314.0
70°	295.2	288.9	282.6	275.3	270.0
72.5°	250.2	246.0	238.6	232.4	230.3
75°	204.1	199.9	196.8	191.5	188.4
77.5°	163.3	161.2	157.0	152.8	152.8
80°	123.5	120.4	118.3	117.2	117.2
82.5°	84.8	84.8	84.8	82.7	81.6
85°	54.4	52.3	52.3	50.2	50.2
87.5°	27.2	24.1	23.0	22.0	22.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)