

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1059803

Luminaire Tested: S123RDRP-H775D940-X4F0-XX-UDD-WVL-S

Issue Date: 8/7/2025

**Test Information**

Test Method: LM-79-2024  
Report Number: P1059803  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2406-143-67 )  
Test Lab: INNOVATION CENTER  
Issue Date: 8/7/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123RDRP-H775D940-X4F0-XX-UDD-WVL-S  
Description: DEFINE 3 SILVER REGRESSED DIRECT RECESSED HOUSING WITH WHITE STRAIGHT BLADE  
LOUVER WITH DIFFUSER  
HIGH PERFORMANCE LIGHT ENGINE  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1271.5 lumens  
Efficiency: N/A  
Efficacy: 54.1 lumens/watt  
Spacing Criteria (0/90/45): 0.93 / 1.12 / 1.1  
Luminous Opening: Rectangular (W 0.23' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 23.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1059803

CATALOG NUMBER: S123RDRP-H775D940-X4F0-XX-UDD-WVL-S

### Luminous Intensity Polar Plot





TEST NUMBER: P1059803

CATALOG NUMBER: S123RDRP-H775D940-X4F0-XX-UDD-WVL-S

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89					87				
2	102	94	88	83	99	92	87	82	89	84	80	86	82	78	83	80	77					75				
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67					65				
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59					57				
5	80	69	60	54	78	68	60	54	65	59	54	64	58	53	62	57	53					51				
6	75	63	54	48	73	62	54	48	60	53	48	58	52	47	57	51	47					45				
7	70	57	49	44	68	56	49	43	55	48	43	54	47	43	52	47	43					41				
8	65	53	45	39	64	52	45	39	51	44	39	50	43	39	48	43	39					37				
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	39	35					34				
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33					31				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8266	8266	8266
5°	8025	8132	8258
10°	7645	7842	8176
15°	7182	7493	8036
20°	6672	7074	7755
25°	6126	6575	7430
30°	5539	6053	7116
35°	4885	5500	6849
40°	4200	4959	6578
45°	3454	4467	6166
50°	3031	3981	5683
55°	2805	3396	5034
60°	2579	3121	4166
65°	2406	2867	3279
70°	2266	2606	2606
75°	2132	2395	2246
80°	2008	2177	1900
85°	1886	2115	1442

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 6166 cd/sqm



TEST NUMBER: P1059803

CATALOG NUMBER: S123RDRP-H775D940-X4F0-XX-UDD-WVL-S

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	65.1	5.1
10°-20°	174.5	13.7
20°-30°	236.6	18.6
30°-40°	247.3	19.5
40°-50°	214.5	16.9
50°-60°	159.6	12.6
60°-70°	102.4	8.1
70°-80°	54.9	4.3
80°-90°	16.6	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	476.1	37.4
0°-40°	723.5	56.9
0°-60°	1097.6	86.3
0°-90°	1271.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1271.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	704	704	704	704	704	
5°	681	692	690	695	701	64
15°	591	605	616	641	661	166
25°	473	488	508	541	574	217
35°	341	357	384	432	478	213
45°	208	224	269	327	371	164
55°	137	140	166	213	246	123
65°	87	94	103	110	118	86
75°	47	54	53	50	50	50
85°	14	17	16	13	11	16
90°	0	0	0	0	0	



TEST NUMBER: P1059803

CATALOG NUMBER: S123RDRP-H775D940-X4F0-XX-UDD-WVL-S

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	703.9	703.9	703.9	703.9	703.9
2.5°	696.5	706.4	699.8	699.8	700.6
5°	680.8	692.3	689.9	694.8	700.6
7.5°	661.8	674.2	675.0	686.6	694.8
10°	641.2	653.6	657.7	674.2	685.7
12.5°	616.4	630.5	637.9	658.5	675.0
15°	590.8	604.9	616.4	641.2	661.0
17.5°	563.6	577.6	592.5	620.6	642.0
20°	533.9	548.8	566.1	594.1	620.6
22.5°	503.4	519.1	537.2	567.7	597.4
25°	472.8	487.7	507.5	541.3	573.5
27.5°	440.7	456.3	477.0	514.1	550.4
30°	408.5	424.2	446.4	486.0	524.8
32.5°	375.5	391.1	415.1	459.6	501.7
35°	340.8	357.3	383.7	432.4	477.8
37.5°	307.8	323.5	353.2	406.8	454.7
40°	274.0	290.5	323.5	381.2	429.1
42.5°	241.0	257.5	296.2	354.0	401.0
45°	208.0	223.6	269.0	326.8	371.3
47.5°	182.4	193.9	243.4	297.9	342.5
50°	165.9	170.0	217.9	269.8	311.1
52.5°	151.0	154.3	189.8	241.8	278.9
55°	137.0	140.3	165.9	212.9	245.9
57.5°	123.0	127.1	147.7	183.2	212.9
60°	109.8	114.7	132.9	156.8	177.4
62.5°	98.2	104.0	118.0	132.9	146.9
65°	86.6	94.1	103.2	109.8	118.0
67.5°	75.9	84.2	89.1	90.8	91.6
70°	66.0	74.3	75.9	75.9	75.9
72.5°	56.1	65.2	63.5	62.7	61.9
75°	47.0	54.5	52.8	50.3	49.5
77.5°	38.0	44.6	42.1	40.4	38.0
80°	29.7	34.7	32.2	30.5	28.1
82.5°	22.3	25.6	23.1	21.5	19.0
85°	14.0	17.3	15.7	13.2	10.7
87.5°	7.4	9.9	8.3	7.4	4.1
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1059803  
 CATALOG NUMBER: S123RDRP-H775D940-X4F0-XX-UDD-WVL-S

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.13	15.61	14.49	15.92	16.24	16.88	18.36	17.25	18.68	18.99
	3H	15.84	17.16	16.21	17.49	17.85	17.90	19.23	18.28	19.56	19.92
	4H	16.50	17.74	16.90	18.09	18.47	18.27	19.51	18.67	19.86	20.24
	6H	17.00	18.15	17.41	18.51	18.91	18.52	19.67	18.93	20.04	20.43
	8H	17.18	18.27	17.60	18.66	19.06	18.59	19.69	19.02	20.08	20.48
	12H	17.30	18.35	17.73	18.73	19.16	18.63	19.67	19.06	20.06	20.49
4H	2H	14.90	16.15	15.30	16.50	16.88	17.15	18.40	17.55	18.75	19.13
	3H	16.83	17.86	17.24	18.26	18.66	18.41	19.44	18.82	19.84	20.24
	4H	17.64	18.57	18.07	18.98	19.42	18.89	19.82	19.33	20.24	20.68
	6H	18.28	19.09	18.74	19.53	19.99	19.27	20.08	19.73	20.52	20.98
	8H	18.51	19.26	18.97	19.71	20.17	19.38	20.14	19.85	20.58	21.05
	12H	18.68	19.35	19.16	19.83	20.30	19.46	20.13	19.94	20.61	21.08
8H	4H	17.96	18.71	18.42	19.16	19.62	19.08	19.84	19.55	20.28	20.75
	6H	18.75	19.37	19.25	19.87	20.34	19.57	20.20	20.07	20.69	21.17
	8H	19.08	19.64	19.59	20.15	20.64	19.75	20.31	20.26	20.82	21.31
	12H	19.35	19.85	19.86	20.34	20.91	19.88	20.38	20.39	20.87	21.43
12H	4H	17.98	18.65	18.46	19.13	19.60	19.10	19.77	19.58	20.25	20.72
	6H	18.80	19.36	19.32	19.88	20.36	19.61	20.17	20.12	20.68	21.17
	8H	19.20	19.69	19.71	20.19	20.75	19.84	20.33	20.35	20.83	21.39