

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1059193

Luminaire Tested: S123RDRP-S340D850-X4F0-XX-UDD-BVL-B

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2024
Report Number: P1059193
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2406-143-30)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDRP-S340D850-X4F0-XX-UDD-BVL-B
Description: DEFINE 3 BLACK REGRESSED DIRECT RECESSED HOUSING WITH BLACK STRAIGHT BLADE
LOUVER WITH DIFFUSER
CORE LIGHT ENGINE
Light Source: 5000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 326.7 lumens
Efficiency: N/A
Efficacy: 26.1 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 0.81 / 0.93
Luminous Opening: Rectangular (W 0.23' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 12.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1059193

CATALOG NUMBER: S123RDRP-S340D850-X4F0-XX-UDD-BVL-B

Luminous Intensity Polar Plot





TEST NUMBER: P1059193

CATALOG NUMBER: S123RDRP-S340D850-X4F0-XX-UDD-BVL-B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	87	85	84
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	83	80	78	76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63
6	83	73	66	61	81	72	66	61	70	65	60	69	64	60	67	63	60	58
7	78	68	61	56	77	67	60	56	66	60	56	64	59	55	63	58	55	53
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49
9	70	59	52	48	68	58	52	48	57	52	47	56	51	47	55	51	47	46
10	66	55	49	44	65	55	48	44	54	48	44	53	48	44	52	47	44	42

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3362	3362	3362
5°	3352	3293	3298
10°	3315	3138	3062
15°	3217	2920	2751
20°	3077	2644	2408
25°	2897	2335	2037
30°	2687	2007	1662
35°	2464	1659	1236
40°	2212	1300	791
45°	1930	950	329
50°	1600	564	126
55°	1179	235	94
60°	714	87	54
65°	192	50	25
70°	0	17	17
75°	0	0	23
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1930 cd/sqm



TEST NUMBER: P1059193

CATALOG NUMBER: S123RDRP-S340D850-X4F0-XX-UDD-BVL-B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.4	8.1
10°-20°	68.0	20.8
20°-30°	84.8	25.9
30°-40°	75.8	23.2
40°-50°	47.8	14.6
50°-60°	20.0	6.1
60°-70°	3.8	1.2
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	179.1	54.8
0°-40°	254.9	78.0
0°-60°	322.8	98.8
0°-90°	326.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	326.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	286	286	286	286	286	
5°	284	284	279	280	280	27
15°	265	258	240	230	226	74
25°	224	206	180	165	157	102
35°	172	147	116	95	86	107
45°	116	90	57	30	20	90
55°	58	40	12	5	5	52
65°	7	5	2	1	1	10
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P1059193

CATALOG NUMBER: S123RDRP-S340D850-X4F0-XX-UDD-BVL-B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	286.3	286.3	286.3	286.3	286.3
2.5°	285.8	286.3	283.5	286.3	286.7
5°	284.4	284.0	279.4	280.3	279.8
7.5°	281.7	280.3	272.0	270.1	269.2
10°	278.0	274.3	263.2	258.6	256.8
12.5°	272.0	266.9	252.6	245.2	242.5
15°	264.6	258.2	240.2	230.0	226.3
17.5°	255.8	246.6	226.3	215.3	209.7
20°	246.2	233.3	211.6	198.2	192.7
22.5°	234.6	220.3	195.9	181.6	175.6
25°	223.6	205.6	180.2	164.6	157.2
27.5°	209.7	190.8	163.6	147.5	139.7
30°	198.2	176.6	148.0	130.0	122.6
32.5°	184.4	161.8	131.8	112.0	105.1
35°	171.9	147.1	115.7	95.0	86.2
37.5°	158.6	132.8	99.6	77.9	69.6
40°	144.3	118.5	84.8	60.8	51.6
42.5°	131.4	104.2	70.1	45.2	36.0
45°	116.2	90.4	57.2	30.4	19.8
47.5°	102.3	77.4	43.3	17.1	10.6
50°	87.6	64.1	30.9	8.8	6.9
52.5°	72.4	51.2	20.3	6.0	5.5
55°	57.6	39.6	11.5	4.6	4.6
57.5°	43.3	28.6	6.0	3.7	3.2
60°	30.4	18.9	3.7	2.8	2.3
62.5°	17.5	11.1	2.8	1.8	1.8
65°	6.9	5.1	1.8	0.9	0.9
67.5°	0.5	1.4	0.9	0.5	0.5
70°	0.0	0.0	0.5	0.5	0.5
72.5°	0.0	0.0	0.5	0.5	0.5
75°	0.0	0.0	0.0	0.0	0.5
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1059193

CATALOG NUMBER: S123RDRP-S340D850-X4F0-XX-UDD-BVL-B

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.40	10.58	9.77	10.89	11.21	0.00	0.00	0.00	0.00	0.00
	3H	9.24	10.28	9.63	10.61	10.97	0.00	0.00	0.00	0.00	0.00
	4H	9.16	10.11	9.56	10.47	10.85	0.00	0.00	0.00	0.00	0.00
	6H	9.07	9.94	9.48	10.31	10.71	0.00	0.00	0.00	0.00	0.00
	8H	9.02	9.84	9.45	10.23	10.64	0.00	0.00	0.00	0.00	0.00
	12H	8.97	9.75	9.40	10.13	10.57	0.00	0.00	0.00	0.00	0.00
4H	2H	9.16	10.12	9.57	10.47	10.86	0.00	0.00	0.00	0.00	0.00
	3H	9.00	9.77	9.41	10.17	10.58	0.00	0.00	0.00	0.00	0.00
	4H	8.89	9.58	9.33	10.00	10.44	0.00	0.00	0.00	0.00	0.00
	6H	8.80	9.38	9.26	9.83	10.30	0.00	0.00	0.00	0.00	0.00
	8H	8.73	9.28	9.21	9.73	10.20	0.00	0.00	0.00	0.00	0.00
	12H	8.68	9.15	9.16	9.64	10.11	0.00	0.00	0.00	0.00	0.00
8H	4H	8.73	9.28	9.21	9.73	10.20	0.00	0.00	0.00	0.00	0.00
	6H	8.62	9.06	9.12	9.56	10.04	0.00	0.00	0.00	0.00	0.00
	8H	8.54	8.94	9.07	9.46	9.95	0.00	0.00	0.00	0.00	0.00
	12H	8.49	8.84	9.01	9.34	9.91	0.00	0.00	0.00	0.00	0.00
12H	4H	8.68	9.15	9.16	9.64	10.11	0.00	0.00	0.00	0.00	0.00
	6H	8.54	8.94	9.07	9.46	9.95	0.00	0.00	0.00	0.00	0.00
	8H	8.49	8.84	9.01	9.34	9.91	0.00	0.00	0.00	0.00	0.00