

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P996567

Luminaire Tested: S124DRP-B795DB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P996567
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-16)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DRP-B795DB2750-4F0-XX-W2A-D_4000K
Description: Define 4 Direct Perimeter with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3237.0 lumens
Efficiency: N/A
Efficacy: 90.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 35.9
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P996567

CATALOG NUMBER: S124DRP-B795DB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P996567

CATALOG NUMBER: S124DRP-B795DB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	117	117	117	117	114	114	114	114	107	107	107	101	101	101	95	95	95	95	95	95	92
1	105	100	95	91	102	97	93	89	91	88	84	86	83	80	81	79	77	77	77	77	74
2	95	86	79	73	92	84	77	71	79	73	68	74	70	66	70	67	63	63	63	63	60
3	87	75	67	60	83	73	65	59	69	62	57	65	60	55	62	57	53	53	53	53	50
4	79	66	57	50	76	65	56	49	61	54	48	58	52	47	55	49	45	45	45	45	43
5	73	59	50	43	70	58	49	42	55	47	41	52	45	40	49	44	39	39	39	39	37
6	67	53	44	37	64	52	43	37	49	42	36	47	40	35	45	39	34	34	34	34	32
7	62	48	39	33	60	47	38	32	45	37	32	43	36	31	41	35	30	30	30	30	28
8	58	44	35	29	56	43	35	29	41	33	28	39	32	28	37	31	27	27	27	27	25
9	54	40	32	26	52	39	31	26	38	30	25	36	29	25	34	29	24	24	24	24	22
10	50	37	29	24	49	36	29	23	35	28	23	33	27	23	32	26	22	22	22	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7742	7742	7742
5°	7780	7694	7754
10°	7747	7694	7764
15°	7692	7674	7746
20°	7603	7639	7732
25°	7499	7586	7701
30°	7388	7538	7668
35°	7261	7493	7673
40°	7164	7470	7685
45°	7013	7479	7748
50°	6892	7486	7836
55°	6772	7542	7936
60°	6573	7595	8132
65°	6360	7714	8390
70°	6108	7935	8795
75°	5763	8409	9647
80°	5443	9636	11533
85°	5268	13922	17908

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 87.5°

Luminance: 31014 cd/sqm

TEST NUMBER: P996567

CATALOG NUMBER: S124DRP-B795DB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.0	2.8
10°-20°	257.7	8.0
20°-30°	389.7	12.0
30°-40°	471.5	14.6
40°-50°	498.4	15.4
50°-60°	469.1	14.5
60°-70°	389.3	12.0
70°-80°	273.2	8.4
80°-90°	154.0	4.8
90°-100°	91.7	2.8
100°-110°	67.9	2.1
110°-120°	45.6	1.4
120°-130°	25.7	0.8
130°-140°	11.1	0.3
140°-150°	2.2	0.1
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	737.4	22.8
0°-40°	1208.9	37.3
0°-60°	2176.5	67.2
0°-90°	2992.9	92.5
90°-120°	205.2	6.3
90°-150°	244.1	7.5
90°-180°	244.0	7.5
0°-180°	3237.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	949	949	949	949	949	
5°	950	947	940	948	947	90
15°	911	912	909	919	918	257
25°	834	840	843	855	856	384
35°	729	742	753	768	771	457
45°	608	628	648	667	672	470
55°	476	499	530	552	558	424
65°	330	364	400	426	435	327
75°	183	222	267	297	306	194
85°	56	101	149	181	191	59
90°	17	60	105	136	145	12
95°	14	49	92	121	131	11
105°	10	31	70	97	105	11
115°	6	16	50	73	81	7
125°	4	3	30	50	56	4
135°	2	2	10	27	33	2
145°	1	0	0	6	11	1
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P996567

CATALOG NUMBER: S124DRP-B795DB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	949.4	949.4	949.4	949.4	949.4
2.5°	953.7	950.5	942.0	949.4	948.4
5°	950.5	947.3	939.9	948.4	947.3
7.5°	944.1	942.0	935.6	945.2	944.1
10°	935.6	934.5	929.2	938.8	937.7
12.5°	923.9	923.9	920.7	929.2	929.2
15°	911.2	912.2	909.0	918.6	917.5
17.5°	894.1	897.3	896.3	905.8	904.8
20°	876.1	879.3	880.3	891.0	891.0
22.5°	855.9	860.1	862.2	872.9	875.0
25°	833.5	839.9	843.1	854.8	855.9
27.5°	809.1	818.7	822.9	833.5	834.6
30°	784.6	793.1	800.6	812.3	814.4
32.5°	758.1	768.7	777.2	791.0	793.1
35°	729.4	742.1	752.7	767.6	770.8
37.5°	700.6	715.5	728.3	743.2	746.4
40°	673.0	686.8	701.7	717.7	721.9
42.5°	641.1	657.1	675.1	693.2	696.4
45°	608.1	628.3	648.5	666.6	671.9
47.5°	577.3	597.5	620.9	639.0	645.4
50°	543.3	566.7	590.1	611.3	617.7
52.5°	509.3	532.7	560.3	581.6	587.9
55°	476.3	498.6	530.5	551.8	558.2
57.5°	439.1	466.7	497.6	523.1	528.4
60°	403.0	430.6	465.7	490.1	498.6
62.5°	367.9	398.7	433.8	458.2	466.7
65°	329.6	363.6	399.8	426.3	434.8
67.5°	293.4	329.6	367.9	394.4	403.0
70°	256.2	292.4	332.8	361.5	368.9
72.5°	220.1	257.3	300.9	328.5	337.0
75°	182.9	222.2	266.9	296.6	306.2
77.5°	147.8	189.2	236.0	265.8	276.4
80°	115.9	158.4	205.2	237.1	245.6
82.5°	84.0	128.6	175.4	208.4	218.0
85°	56.3	101.0	148.8	180.7	191.4
87.5°	35.1	78.7	125.5	156.3	165.9
90°	17.0	59.5	105.3	136.1	144.6
92.5°	15.9	53.2	98.9	128.6	137.2
95°	13.8	48.9	92.5	121.2	130.8
97.5°	12.8	43.6	87.2	114.8	124.4
100°	11.7	39.3	80.8	109.5	117.0
102.5°	11.7	35.1	75.5	103.1	111.6
105°	9.6	30.8	70.2	96.8	105.3
107.5°	9.6	27.6	64.9	91.4	98.9
110°	8.5	23.4	60.6	85.1	93.6



TEST NUMBER: P996567

CATALOG NUMBER: S124DRP-B795DB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	7.4	20.2	55.3	78.7	87.2
115°	6.4	15.9	50.0	73.4	80.8
117.5°	6.4	12.8	44.7	67.0	75.5
120°	5.3	8.5	39.3	60.6	69.1
122.5°	5.3	5.3	34.0	55.3	62.7
125°	4.3	3.2	29.8	50.0	56.3
127.5°	4.3	3.2	24.5	43.6	51.0
130°	3.2	2.1	19.1	38.3	44.7
132.5°	3.2	2.1	14.9	33.0	39.3
135°	2.1	2.1	9.6	26.6	33.0
137.5°	2.1	1.1	5.3	21.3	26.6
140°	2.1	1.1	2.1	15.9	21.3
142.5°	1.1	1.1	0.0	11.7	15.9
145°	1.1	0.0	0.0	6.4	10.6
147.5°	1.1	0.0	0.0	1.1	5.3
150°	1.1	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)