

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1056033

Luminaire Tested: S124R3DRP-S350D950-X4F0-XX-UDD-F-W

Issue Date: 7/25/2025

Test Information

Test Method: LM-79-2024
Report Number: P1056033
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2503-402-7)
Test Lab: INNOVATION CENTER
Issue Date: 7/25/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124R3DRP-S350D950-X4F0-XX-UDD-F-W
Description: DEFINE 4, WHITE 3-INCH REGRESSED DIRECT RECESSED HOUSING WITH FROSTED LENS
CORE LIGHT ENGINE
Light Source: 5000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1124.0 lumens
Efficiency: N/A
Efficacy: 89.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.95 / 1.12
Luminous Opening: Rectangular (W 0.31' x L: 3.9' x H: 0')
CIE Type: Direct

Input Watts (W): 12.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1056033

CATALOG NUMBER: S124R3DRP-S350D950-X4F0-XX-UDD-F-W

Luminous Intensity Polar Plot





TEST NUMBER: P1056033

CATALOG NUMBER: S124R3DRP-S350D950-X4F0-XX-UDD-F-W

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	105	102	98	107	103	100	97	99	96	93	95	93	91	92	90	88	86
2	101	93	87	82	98	91	86	81	88	83	79	85	81	77	82	78	76	73
3	93	83	75	69	90	81	74	69	79	73	68	76	71	67	73	69	65	63
4	85	74	66	60	83	73	65	60	71	64	59	68	63	58	66	61	57	55
5	79	67	59	53	77	66	58	52	64	57	52	62	56	51	60	55	51	49
6	73	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43
7	68	56	47	42	67	55	47	42	53	46	41	52	46	41	51	45	41	39
8	64	51	43	38	62	51	43	38	49	42	37	48	42	37	47	41	37	35
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	41	35	31	29

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4989	4989	4989
5°	4950	4938	4935
10°	4921	4791	4730
15°	4869	4611	4470
20°	4805	4391	4146
25°	4727	4140	3768
30°	4634	3854	3383
35°	4535	3554	3011
40°	4433	3244	2665
45°	4325	2943	2342
50°	4192	2627	2022
55°	4065	2311	1837
60°	3920	1982	1703
65°	3745	1799	1590
70°	3477	1665	1502
75°	3150	1530	1418
80°	2749	1415	1334
85°	2110	1309	1217

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4325 cd/sqm



TEST NUMBER: P1056033

CATALOG NUMBER: S124R3DRP-S350D950-X4F0-XX-UDD-F-W

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.5	4.7
10°-20°	142.5	12.7
20°-30°	197.3	17.6
30°-40°	211.8	18.8
40°-50°	192.6	17.1
50°-60°	151.7	13.5
60°-70°	103.8	9.2
70°-80°	55.9	5.0
80°-90°	15.8	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	392.4	34.9
0°-40°	604.2	53.8
0°-60°	948.4	84.4
0°-90°	1124.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1124.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	564	564	564	564	564	
5°	558	564	556	554	556	53
15°	532	526	504	490	488	150
25°	485	465	424	394	386	223
35°	420	387	329	289	279	263
45°	346	302	235	195	187	267
55°	264	213	150	121	119	236
65°	179	128	86	76	76	177
75°	92	56	45	41	42	98
85°	21	14	13	12	12	25
90°	0	0	0	0	0	



TEST NUMBER: P1056033

CATALOG NUMBER: S124R3DRP-S350D950-X4F0-XX-UDD-F-W

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	564.3	564.3	564.3	564.3	564.3
2.5°	560.2	566.8	561.8	562.6	563.5
5°	557.7	563.9	556.4	553.5	556.0
7.5°	553.5	557.7	546.0	540.6	543.1
10°	548.1	548.9	533.6	525.7	526.9
12.5°	540.6	538.6	519.9	508.7	509.5
15°	531.9	526.1	503.7	490.0	488.3
17.5°	522.0	512.4	485.8	468.4	465.1
20°	510.7	497.9	466.7	444.3	440.6
22.5°	498.3	481.7	446.0	419.4	414.0
25°	484.6	464.7	424.4	393.6	386.2
27.5°	469.6	446.4	401.1	367.5	357.9
30°	453.9	427.3	377.5	341.3	331.4
32.5°	437.7	407.8	353.4	315.2	304.8
35°	420.2	387.4	329.3	289.4	279.0
37.5°	402.4	366.2	304.8	264.5	253.7
40°	384.1	345.1	281.1	239.6	230.9
42.5°	365.4	323.5	257.9	216.3	208.4
45°	345.9	301.9	235.4	194.7	187.3
47.5°	326.0	279.9	212.6	174.4	167.3
50°	304.8	257.9	191.0	154.5	147.0
52.5°	284.4	235.4	170.2	135.0	131.2
55°	263.7	213.4	149.9	120.8	119.2
57.5°	242.9	191.4	131.2	109.6	108.0
60°	221.7	169.8	112.1	98.0	96.3
62.5°	200.6	148.7	98.0	86.8	86.0
65°	179.0	127.9	86.0	76.4	76.0
67.5°	156.1	108.0	75.2	67.3	66.9
70°	134.5	88.0	64.4	58.1	58.1
72.5°	114.2	69.8	54.4	49.4	49.4
75°	92.2	56.1	44.8	41.1	41.5
77.5°	72.7	44.0	36.1	33.6	33.6
80°	54.0	32.8	27.8	25.7	26.2
82.5°	36.5	22.8	19.9	18.7	18.7
85°	20.8	14.1	12.9	12.0	12.0
87.5°	7.5	6.6	6.2	5.4	5.8
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1056033

CATALOG NUMBER: S124R3DRP-S350D950-X4F0-XX-UDD-F-W

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.72	18.25	17.09	18.56	18.88	12.50	14.03	12.87	14.34	14.66
	3H	18.50	19.87	18.88	20.20	20.56	14.11	15.48	14.49	15.81	16.17
	4H	19.17	20.46	19.57	20.81	21.19	14.75	16.03	15.15	16.38	16.76
	6H	19.68	20.87	20.09	21.24	21.63	15.24	16.43	15.66	16.80	17.19
	8H	19.84	20.98	20.27	21.37	21.77	15.42	16.55	15.84	16.94	17.34
	12H	19.94	21.03	20.37	21.41	21.84	15.54	16.62	15.97	17.00	17.43
4H	2H	16.82	18.11	17.22	18.46	18.83	13.22	14.51	13.62	14.86	15.23
	3H	18.77	19.84	19.18	20.23	20.64	15.03	16.10	15.44	16.50	16.90
	4H	19.52	20.49	19.95	20.90	21.34	15.77	16.73	16.20	17.15	17.58
	6H	20.16	21.00	20.61	21.44	21.90	16.38	17.22	16.84	17.66	18.12
	8H	20.38	21.16	20.84	21.60	22.07	16.60	17.38	17.06	17.83	18.29
	12H	20.53	21.23	21.01	21.71	22.18	16.76	17.47	17.25	17.94	18.42
8H	4H	19.58	20.36	20.04	20.81	21.27	16.15	16.94	16.62	17.38	17.85
	6H	20.28	20.93	20.77	21.42	21.90	16.89	17.53	17.38	18.03	18.50
	8H	20.55	21.13	21.06	21.64	22.13	17.17	17.76	17.69	18.27	18.75
	12H	20.76	21.28	21.27	21.77	22.33	17.42	17.93	17.93	18.43	18.99
12H	4H	19.57	20.27	20.05	20.75	21.22	16.21	16.91	16.69	17.39	17.86
	6H	20.27	20.85	20.78	21.36	21.85	16.97	17.55	17.48	18.06	18.55
	8H	20.58	21.09	21.09	21.59	22.15	17.32	17.83	17.83	18.32	18.89